

3 . CASSETTE TYPE : AUU36RCLX

3-1. FEATURE

■ MODELS : AUU36RCLX / AOU36RLX



■ FEATURES


● Easy maintenance

The control box is easily accessible for maintenance work
Wide opening for easy access.

Detachable, washable filter and intake grille.


Wide opening and long-life filter.

Long-life filter
High efficiency, long-life filter extends the cleaning cycle.




● Slim intake grille

Slim type intake grille can fit the ceiling after installation.




● Group controller

One remote controller can control up to 16 air conditioners.
All of the air conditioners will be operated with the same settings.




● Duct connection hole opening

Fresh air can be introduced through this opening.




● Conditioned air can be distributed by means of a distribution duct.



3-2. REMOTE CONTROLLER

3-2-1. WIRED REMOTE CONTROLLER


■ FEATURES




- * Various timer setup (ON / OFF / WEEKLY) are possible.
- * Equipped with weekly timer as standard function.
(2 times Start / Stop per day for a week)
- * When setting up a timer, operation mode and a temperature setup can be changed.
- * When a failure occurs, the error code is displayed. (Maximum of 16)
- * Error indication. (A maximum of 16 error histories are memorizable.)
- * Easy installation with a slim shape with no boldge in the back.
- * Built in room temperature sensor.

● High performance and compact size


Three functions are combined in one unit.



● Built-in timers



● Easy-to-understand operation




[Variable timer control]


The operation/display sections are zoned according to time and operation, enabling variable programming to match application.

● Simple installation


Components are compatible with standard switch boxes. Flat back construction allows equipment to be installed wherever it is needed.



FUNCTIONS



Display panel



- 1** START/STOP button
Pressed to start and stop operation.
- 2** Set Temperature button
Selects the setting temperature.
- 3** Master control button
Selects the operating mode(AUTO, HEAT, FAN, COOL, DRY).
- 4** Fan control button
Selects the fan speed (AUTO, LOW, MED, HIGH).
- 5** Energy save button
Turns the energy efficient mode on and off.
- 6** Thermo sensor button
Selects whether the room temperature is detected at the indoor unit (remote sensor) or the remote controller.
- 7** Timer mode (CLOCK ADJUST) button
Selects the timer mode (OFF TIMER, ON TIMER, WEEKLY TIMER)
Set the current time.
- 8** Day (DAY OFF) button
Temporarily cancels of one day timer.
- 9** Set back button
pressed select the set back timer.
- 10** Set time button
Pessed to select the set back timer.
- 11** Delete button
The schedule of a weekly timer is deleted.
- 12** Set button
Sets the date, hour, minute and on-off time.
- 13** Vertical air flow direction and swing button
Push for two seconds to change the swing mode
- 14** Operation lamp
Lights during operation and when the timer is on.
- 15** Timer and clock display
- 16** Operation mode display
- 17** Fan speed display
- 18** Central control display
- 19** Temperature display
- 20** Stand by display
Indicates during defrosting operation.
- 21** Vertical swing display
- 22** Energy save display
- 23** Thermo sensor display

SPECIFICATION

SIZE [H x W x D in. (mm)]	4-23/32 x 4-23/32 x 43/64 (120 x 120 x 17)
WEIGHT oz. (g)	5-21/32 (160)
CABLE LENGTH ft.(m)	33 (10)
POWER (V)	12

3-3. SPECIFICATIONS

CASSETTE TYPE
AUU36R

TYPE				CASSETTE MODELS		
				INVERTER HEAT PUMP		
MODEL NAME		INDOOR		AUU36RCLX		
		OUTDOOR		AOU36RLX		
POWER SOURCE				208/230V ~ 60Hz		
AVAILABLE VOLTAGE RANGE				187-253V ~ 60Hz		
CAPACITY	COOLING	RATED/MAX	kW	10.00 / 10.50		
			BTU/h	34,100 / 36,000		
	HEATING	RATED/MAX	kW	10.60 / 12.50		
			BTU/h	36,000 / 42,700		
INPUT POWER	COOLING	RATED/MAX	kW	4.22 / 4.35		
	HEATING	RATED/MAX		3.70 / 4.35		
CURRENT	COOLING	RATED/MAX	A	18.3 / 18.8		
	HEATING	RATED/MAX		16.1 / 18.8		
STARTING CURRENT			A	10.0		
SEER		COOLING		14.0		
HSPF		HEATING		8.5		
MOISTURE REMOVAL			pints/h (l/h)	8.5 (4.0)		
AIR CIRCULATION COOL/HEAT	INDOOR	High	CFM(m³/h)	942 (1600) / 942 (1600)		
		Med		824 (1400) / 824 (1400)		
		Low		677 (1150) / 677 (1150)		
		Quiet		-		
	OUTDOOR	High		2119 (3600) / 2236 (3800)		
		Low		-		
FAN SPEED COOL/HEAT	INDOOR	High	r.p.m	620 / 620		
		Med		540 / 540		
		Low		460 / 460		
		Quiet		-		
	OUTDOOR	High		850 / 900		
		Low		-		
FAN TYPE x Q'ty		INDOOR		TURBO × 1		
		OUTDOOR		PROPELLER × 1		
FAN MOTOR OUTPUT		INDOOR	W	100		
		OUTDOOR		100		
NOISE LEVEL (SOUND PRESSURE)	INDOOR	High	dB(A)	48.0 / 48.0		
		Med		45.0 / 45.0		
		Low		41.0 / 41.0		
COOL/HEAT	OUTDOOR				54.0 / 55.0	
COMPRESSOR	TYPE		DC TWIN ROTARY (INVERTER)			
	OUTPUT		W	1300		
	STARTING METHOD			Inverter		
HEAT EXCHANGER TYPE	INDOOR	Coil		Copper tube		
		Fin		Aluminium		
		Rows x Stages		2 × 12		
		Fin Pitch	FPI	20		
	Coil Dimensions		in.(mm)	9 - 29/32 × 38 - 3/16 × 1 - 1/16 (252 × 970 × 26.6) [× 2 pieces]		
	OUTDOOR	Coil		Copper tube		
		Fin		Aluminium		
		Rows x Stages		2 × 38		
Fin Pitch		FPI	20			
Coil Dimensions		in.(mm)	31 - 13/32 × 35 - 7/16 × 1 - 7/16 (798 × 900 × 36.38)			
CASING COLOR		INDOOR		White (5Y9/0.5NN)		
		OUTDOOR		Beige (10YR7.5/1.0NN)		
DIMENSIONS H × W × D	INDOOR	NET	in.(mm)	11 - 21/32 × 32 - 11/16 × 32 - 11/16 (296 × 830 × 830)		
	OUTDOOR			32 - 11/16 × 35 - 7/16 × 13 (830 × 900 × 330)		
	INDOOR	GROSS		17 - 29/32 × 41 - 23/32 × 40 - 11/32 (455 × 1060 × 1025)		
	OUTDOOR			38 - 3/16 × 41 - 11/32 × 17 - 17/32 (970 × 1050 × 445)		
WEIGHT	INDOOR	NET	lb. (kg)	82(37)		
	OUTDOOR			141(64)		
	INDOOR	GROSS		115(52)		
	OUTDOOR			154(70)		
PIPE	CONNECTION METHOD			FLARE		
	SIZE	LIQUID	in. (mm)	Φ 3/8 (9.52)		
		GAS		Φ 5/8 (15.88)		
	MAX LENGTH		ft. (m)		164 (50) [chargeless:49 (15)]	
MAX HEIGHT		ft. (m)		98 (30)		
REFRIGERANT		TYPE		R410A		
		CHARGE	lb. oz. (g)	4lb. 14oz. (2200)		
REFRIGERANT OIL		TYPE		POE		
OPERATION(OUTDOOR)		COOLING	°F (°C)	0 to 115 (- 18 to 46)		
		HEATING		14 to 75 (- 10 to 24)		
REMOTE CONTROLLER TYPE				WIRED		
DRAIN PIPE	MATERIAL			ABS		
	SIZE	mm (Reference in.)		Outer diameter 37.0 (1 - 15/32)		
				Inner diameter 32.0 (1 - 1/4)		

Note :
Specifications are based on the following conditions.
Power source of specifications : 230V
Cooling : Indoor temperature of 80.6°F(27°C)DB / 66.2°F(19°C)WB, and outdoor temperature of 95.0°F(35°C)DB/75.2°F(24°C)WB.
Heating : Indoor temperature of 68.0°F(20°C)DB / 59.0°F(15°C)WB, and outdoor temperature of 44.6°F(7°C)DB/42.8°F(6°C)WB.
Pipe length : 24ft. 7in.(7.5m),Height difference : 0 ft.(0m) [Outdoor unit - Indoor unit]


CASSETTE TYPE
AUU36R

3-4. DIMENSIONS

3-4-1. OUTDOOR UNIT

■ MODEL : AOU36R

Unit : in.(mm)




■ MOUNTING POSITION

When there are obstacles at the back or front sides.

When there are obstacles at the back, side(s), and top.

When there are obstacles at the back, side with the installation of more than one unit.








3-4-2. INDOOR UNIT

■ MODEL : AUU36R

Unit : in.(mm)


CASSETTE TYPE
AUU36R



CASSETTE TYPE
AUU36R

■ MOUNTING POSITION



Unit : in.(mm)



You can select 2-way setting

(A) Standard setting


(B) Slender setting



3-5. REFRIGERANT CIRCUIT

MODELS : AUU36R / AOU36R

CASSETTE TYPE
AUU36R



CASSETTE TYPE
AUU36R

TH_D : THERMISTOR(DISCHARGE TEMP.)
TH_O : THERMISTOR(OUTDOOR TEMP.)
TH_{P0} : THERMISTOR(PIPE TEMP.)
TH_C : THERMISTOR(COMPRESSOR TEMP.)

TH_R : THERMISTOR(ROOM TEMP.)
TH_{P1} : THERMISTOR(PIPE TEMP.)


3-6. WIRING DIAGRAMS

3-6-1. OUTDOOR UNIT

■MODEL : AOU36R

CASSETTE TYPE
AUU36R

CASSETTE TYPE
AUU36R




3-6-2. INDOOR UNIT

■MODEL : AUU36R

CASSETTE TYPE
AUU36R

CASSETTE TYPE
AUU36R



3-7. CAPACITY TABLE

■ MODELS : AUU36R / AOU36R

● COOLING

AFR	942
-----	-----

		Indoor temperature																	
		64°FDB			70°FDB			75°FDB			80°FDB			85°FDB			90°FDB		
		54°FWB			60°FWB			63°FWB			67°FWB			71°FWB			73°FWB		
Outdoor temperature	(°FDB)	TC	SHC	PI	TC	SHC	PI	TC	SHC	PI	TC	SHC	PI	TC	SHC	PI	TC	SHC	PI
	0	25.50	19.97	1.30	28.77	20.09	1.32	30.39	22.01	1.33	32.55	23.03	1.35	34.73	23.79	1.36	35.82	26.36	1.37
	14	24.71	19.14	1.51	27.87	19.25	1.53	29.44	21.09	1.55	31.54	22.07	1.56	33.65	22.79	1.58	34.70	25.26	1.59
	32	23.92	19.89	1.16	26.99	20.01	1.18	28.51	21.93	1.19	30.54	22.94	1.20	32.58	23.69	1.22	33.60	26.26	1.22
	41	25.00	19.76	1.33	28.20	19.88	1.35	29.79	21.79	1.37	31.92	22.79	1.38	34.05	23.54	1.40	35.11	26.09	1.40
	50	27.50	19.70	2.43	31.01	19.82	2.47	32.76	21.71	2.49	35.10	22.71	2.52	37.45	23.46	2.55	38.61	26.00	2.56
	59	29.31	20.58	2.10	33.06	20.70	2.13	34.93	22.68	2.15	37.42	23.73	2.18	39.92	24.51	2.20	41.17	27.16	2.21
	67	28.24	19.97	2.34	31.85	20.09	2.38	33.65	22.01	2.40	36.05	23.03	2.43	38.46	23.78	2.46	39.66	26.36	2.47
	77	28.69	20.27	3.07	32.36	20.39	3.13	34.18	22.34	3.15	36.62	23.38	3.19	39.07	24.14	3.22	40.29	26.76	3.24
	87	27.68	19.11	3.34	31.22	19.23	3.40	32.98	21.07	3.43	35.34	22.04	3.47	37.70	22.77	3.50	38.88	25.23	3.52
	95	28.20	19.22	4.19	31.81	19.34	4.27	33.60	21.19	4.30	36.00	22.17	4.35	38.41	22.90	4.40	39.61	25.38	4.42
	104	21.22	16.78	3.37	23.93	16.89	3.43	25.28	18.50	3.46	27.08	19.36	3.50	28.90	19.99	3.54	29.80	22.16	3.56
	115	14.72	13.96	2.41	16.60	14.04	2.45	17.54	15.38	2.47	18.79	16.09	2.50	20.05	16.62	2.53	20.67	18.42	2.54

AFR: Air flow rate(CFM) TC : Total capacity (kBTU) SHC: Sensible Heat capacity (kBTU) PI : Power Input (kW)

AFR	26.7
-----	------

		Indoor temperature																	
		17.78°CDB			21.11°CDB			23.89°CDB			26.67°CDB			29.44°CDB			32.22°CDB		
		12.22°CWB			15.56°CWB			17.72°CWB			19.44°CWB			21.67°CWB			22.78°CWB		
Outdoor temperature	(°CDB)	TC	SHC	PI	TC	SHC	PI	TC	SHC	PI	TC	SHC	PI	TC	SHC	PI	TC	SHC	PI
	-17.78	7.47	5.85	1.30	8.43	5.88	1.32	8.90	6.45	1.33	9.54	6.75	1.35	10.17	6.97	1.36	10.49	7.72	1.37
	-10.00	7.24	5.60	1.51	8.16	5.64	1.53	8.62	6.18	1.55	9.24	6.46	1.56	9.86	6.68	1.58	10.16	7.40	1.59
	0.00	7.01	5.83	1.16	7.90	5.86	1.18	8.35	6.42	1.19	8.94	6.72	1.20	9.54	6.94	1.22	9.84	7.69	1.22
	5.00	7.32	5.79	1.33	8.26	5.82	1.35	8.73	6.38	1.37	9.35	6.68	1.38	9.97	6.89	1.40	10.28	7.64	1.40
	10.00	8.05	5.77	2.43	9.08	5.80	2.47	9.60	6.36	2.49	10.28	6.65	2.52	10.97	6.87	2.55	11.31	7.62	2.56
	15.00	8.59	6.03	2.10	9.68	6.06	2.13	10.23	6.64	2.15	10.96	6.95	2.18	11.69	7.18	2.20	12.06	7.96	2.21
	19.44	8.27	5.85	2.34	9.33	5.88	2.38	9.86	6.45	2.40	10.56	6.74	2.43	11.27	6.97	2.46	11.62	7.72	2.47
	25.00	8.40	5.94	3.07	9.48	5.97	3.13	10.01	6.54	3.15	10.73	6.85	3.19	11.44	7.07	3.22	11.80	7.84	3.24
	30.56	8.11	5.60	3.34	9.15	5.63	3.40	9.66	6.17	3.43	10.35	6.46	3.47	11.04	6.67	3.50	11.39	7.39	3.52
	35.00	8.26	5.63	4.19	9.32	5.66	4.27	9.84	6.21	4.30	10.50	6.49	4.35	11.25	6.71	4.40	11.60	7.43	4.42
	40.00	6.21	4.92	3.37	7.01	4.95	3.43	7.40	5.42	3.46	7.93	5.67	3.50	8.46	5.86	3.54	8.73	6.49	3.56
	46.11	4.31	4.09	2.41	4.86	4.11	2.45	5.14	4.51	2.47	5.50	4.71	2.50	5.87	4.87	2.53	6.06	5.40	2.54

AFR: Air flow rate(m³/min) TC : Total capacity (kW) SHC: Sensible Heat capacity (kW) PI : Power Input (kW)

CASSETTE TYPE
AUU36R

CASSETTE TYPE
AOU36R

● HEATING

AFR	942
-----	-----

			Indoor temperature									
			60°FDB		65°FDB		70°FDB		75°FDB		78°FDB	
Outdoor temperature	(°FDB)	(°FWB)	TC	PI	TC	PI	TC	PI	TC	PI	TC	PI
	14	12	31.47	3.73	30.45	3.84	29.43	3.95	28.41	4.06	27.79	4.13
	23	19	36.33	3.99	35.15	4.10	33.97	4.22	32.79	4.34	32.08	4.41
	32	28	41.00	4.11	39.67	4.23	38.34	4.35	37.01	4.47	36.21	4.54
	41	37	42.50	4.11	41.12	4.23	39.74	4.35	38.36	4.47	37.53	4.54
	47	43	45.67	4.11	44.19	4.23	42.70	4.35	41.22	4.47	40.33	4.54
	50	47	47.10	4.11	45.57	4.23	44.04	4.35	42.51	4.47	41.59	4.54
	59	50	49.84	4.11	48.22	4.23	46.60	4.35	44.98	4.47	44.01	4.54
	68	59	44.84	3.31	43.38	3.40	41.93	3.50	40.47	3.60	39.59	3.66
	75	65	46.99	3.31	45.47	3.40	43.94	3.50	42.41	3.60	41.50	3.66

AFR: Air flow rate(CFM) TC : Total capacity (kBTU) PI : Power Input (kW)

AFR	26.7
-----	------

			Indoor temperature									
			15.56°CDB		18.33°CDB		21.11°CDB		23.89°CDB		25.56°CDB	
Outdoor temperature	(°CDB)	(°CWB)	TC	PI	TC	PI	TC	PI	TC	PI	TC	PI
	-10.00	-11.11	9.22	3.73	8.92	3.84	8.62	3.95	8.32	4.06	8.14	4.13
	-5.00	-7.22	10.64	3.99	10.30	4.10	9.95	4.22	9.60	4.34	9.40	4.41
	0.00	-2.22	12.01	4.11	11.62	4.23	11.23	4.35	10.84	4.47	10.61	4.54
	5.00	2.78	12.45	4.11	12.04	4.23	11.64	4.35	11.24	4.47	10.99	4.54
	8.33	6.11	13.38	4.11	12.94	4.23	12.50	4.35	12.07	4.47	11.81	4.54
	10.00	8.33	13.79	4.11	13.35	4.23	12.90	4.35	12.45	4.47	12.18	4.54
	15.00	10.00	14.60	4.11	14.12	4.23	13.65	4.35	13.18	4.47	12.89	4.54
	20.00	15.00	13.13	3.31	12.71	3.40	12.28	3.50	11.85	3.60	11.60	3.66
	23.89	18.33	13.76	3.31	13.32	3.40	12.87	3.50	12.42	3.60	12.15	3.66

AFR: Air flow rate(m³/min) TC : Total capacity (kW) PI : Power Input (kW)

3-8. CAPACITY COMPENSATION FOR PIPE LENGTH AND HEIGHT DIFFERENCE

■ MODELS : AUU36R / AOU36R

CASSETTE TYPE
AUU36R

CASSETTE TYPE
AOU36R

COOLING				PIPE LENGTH						
				5 m	7.5 m	15 m	20 m	30 m	40 m	50 m
				16 ft.	25 ft.	49 ft.	66 ft.	98 ft.	131 ft.	164 ft.
HEIGHT DIFFERENCE	Outdoor unit is bottom-side	30m	98ft.	-	-	-	-	0.960	0.935	0.913
		20m	66ft.	-	-	-	0.983	0.960	0.935	0.913
		10 m	33ft.	-	-	0.989	0.983	0.960	0.935	0.913
		7.5m	25ft.	-	1.000	0.989	0.983	0.960	0.935	0.913
		5m	16ft.	0.995	1.000	0.989	0.983	0.960	0.935	0.913
	Outdoor unit is up-side	0m	0ft.	0.995	1.000	0.989	0.983	0.960	0.935	0.913
		-5m	-16ft.	0.987	0.992	0.981	0.975	0.952	0.928	0.906
		-7.5m	-25ft.	-	0.988	0.977	0.971	0.948	0.924	0.902
		-10m	-33ft.	-	-	0.973	0.967	0.945	0.920	0.898
		-20m	-66ft.	-	-	-	0.952	0.929	0.905	0.884
		-30m	-98ft.	-	-	-	-	0.914	0.890	0.869

HEATING				PIPE LENGTH						
				5 m	7.5 m	15 m	20 m	30 m	40 m	50 m
				16 ft.	25 ft.	49 ft.	66 ft.	98 ft.	131 ft.	164 ft.
HEIGHT DIFFERENCE	Outdoor unit is bottom-side	30m	98ft.	-	-	-	-	0.906	0.885	0.872
		20m	66ft.	-	-	-	0.938	0.915	0.894	0.881
		10 m	33ft.	-	-	0.959	0.947	0.925	0.903	0.890
		7.5m	25ft.	-	0.993	0.962	0.950	0.927	0.905	0.892
		5m	16ft.	0.995	0.995	0.964	0.952	0.929	0.907	0.895
	Outdoor unit is up-side	0m	0ft.	1.000	1.000	0.969	0.957	0.934	0.912	0.899
		-5m	-16ft.	1.000	1.000	0.969	0.957	0.934	0.912	0.899
		-7.5m	-25ft.	-	1.000	0.969	0.957	0.934	0.912	0.899
		-10m	-33ft.	-	-	0.969	0.957	0.934	0.912	0.899
		-20m	-66ft.	-	-	-	0.957	0.934	0.912	0.899
		-30m	-98ft.	-	-	-	-	0.934	0.912	0.899

3-9. ADDITIONAL CHARGE CALCULATION

■ MODELS : AUU36R / AOU36R

REFRIGERANT TYPE		R410A
REFRIGERANT AMOUNT	lb. oz. (g)	4 lb. 14 oz. (2200)

● REFRIGERANT CHARGE

PIPE LENGTH	ft.	~ 49	66	98	131	164 (MAX)	0.43 oz./ft. (40g/m)
	m	~ 15	20	30	40	50 (MAX)	
ADDITIONAL CHARGE	lb. oz.	0 (Chargeless)	7.3 oz.	1 lb. 5.1 oz.	2 lb. 3.3 oz.	3 lb. 1.5 oz.	
	g	0 (Chargeless)	200	600	1000	1400	

CASSETTE TYPE
AUU36R

CASSETTE TYPE
AUU36R

3-10. OPERATION RANGE

Model		Mode	Operation Range		
Indoor unit	Outdoor unit		Indoor temperature	Indoor humidity	Outdoor temperature
AUU36R	AOU36R	Cooling Dry	64 to 88°F (18 to 31°C)	About 80% or less	0 to 115°F (-18 to 46°C)
		Heating	60 to 88°F (16 to 31°C)	-	14 to 75°F (-10 to 24°C)

CASSETTE TYPE
AUU36R




CASSETTE TYPE
AOU36R

3-11. FAN PERFORMANCE AND AIR FLOW



3-11-1. AIR VELOCITY DISTRIBUTION

■MODEL : AUU36R

4-WAY AIR OUTLET



2-WAY AIR OUTLET



3-11-2. AIR FLOW

■ MODELS : AUU36R / AOU36R

	FAN SPEED	NUMBER OF ROTATIONS (r.p.m)	AIR FLOW	
Indoor unit	HIGH	620	m ³ /h	1600
			l/s	444
			CFM	942
	MED	540	m ³ /h	1400
			l/s	389
			CFM	824
	LOW	460	m ³ /h	1150
			l/s	319
			CFM	677
Outdoor unit	HIGH	850	m ³ /h	3600
			l/s	1000
			CFM	2119





CASSETTE TYPE
AUU36R

CASSETTE TYPE
AOU36R

3-11-3. DUCT CONNECTION



MODEL : AUU36R

OUTLET AIR



*(1) L=16' 4-27/32" (5m)
*(2) L=9' 10-1/8" (3m)
*(3) L=3' 3-3/8" (1m)

FRESH AIR




3-12. NOISE LEVEL CURVE

3-12-1. OUTDOOR UNIT


■ COOLING

● MODELS : AOU36R





■ HEATING

● MODEL : AOU36R



■ SOUND LEVEL CHECK POINT

CASSETTE TYPE
AUU36R




CASSETTE TYPE
AUU36R

3-12-2. INDOOR UNIT


COOLING

MODELS : AUU36R




HEATING

MODEL : AUU36R




■ SOUND LEVEL CHECK POINT

CASSETTE TYPE
AUJ36R



CASSETTE TYPE
AUJ36R



3-13. ELECTRIC CHARACTERISTICS

■ MODELS : AUU36R / AOU36R

CASSETTE TYPE
AUU36R

CASSETTE TYPE
AOU36R

Model Name	Indoor unit		AUU36R	
	Outdoor unit		AOU36R	
Power Supply	Voltage	V	230	
	Frequency	Hz	60	
Rated Value	Mode		Cooling	Heating
	Current	A	18.3	16.1
	Input	kW	4.22	3.70
Max Operating Current		A	18.8	18.8
Starting Current		A	10	
*1) Wiring Spec.	Main Fuse (Circuit breaker) Current	A	30	
	Power Cable	AWG	12	
	*2)Limited wiring length	ft.	63	
Indoor Fan Motor	Input	kW	0.14	
	Full Load Amp.	A	0.63	
Outdoor Fan Motor	Input	kW	0.13	
	Full Load Amp.	A	0.59	

- *1) Wiring Spec. : Selected Sample
(Selected based on Japan Electrotechnical Standard and Codes Committee E0005)
- *2) Limited Wiring length : This is the wiring length in case voltage descent is less than 2%.
When the wiring length becomes long, please select the wiring of a more larger diameter.

3-14. SAFETY DEVICE

■ OUTDOOR UNIT

	PROTECTION FORM	AOU36R	
FUSE ON MAIN PCB	CURRENT FUSE	3.15A 250V	
		5A 250V	
FAN MOTOR PROTECTION	THERMAL PROTECTOR	302±9°F	105±5°C
COMPRESSOR PROTECTION	THERMAL PROTECTOR	OFF : 257°F ON : 176°F	OFF : 125°C ON : 80°C
HIGH PRESSURE PROTECTION	PRESSURE SWITCH	OFF : 609±15 PSI ON : 464±22 PSI	OFF : 4.2±0.1MPa ON : 3.2±0.15MPa

■ INDOOR UNIT

	PROTECTION FORM	AUU36R	
PCB FUSE	CURRENT FUSE	3.15A 250V	
FAN MOTOR PROTECTOR	THERMAL PROTECTOR	302±9°F	105±5°C

CASSETTE TYPE
AUU36R

CASSETTE TYPE
AUU36R


3-15. FUNCTION SETTING

3-15-1. INDOOR UNIT

INDOOR UNIT			
DIP SW	SW 1	1	Auto restart validity/invalidity
		2	Room temperature correct coefficient
		3	Room temperature correct coefficient
	SW 4	1	Forbidden
		2	Ceiling height setting
		3	
Rotary SW	SW 2		Indoor unit number setting
Jumper Wire		JM1	Forbidden
		JM2	Forbidden
		JM3	Forbidden

SWITCH POSITION

Indoor unit control circuit board



3-15-2. SWITCH FUNCTION (INDOOR UNIT)

■ DIP SWITCH SETTING

● SW1-1. Auto restart setting

Auto restart function can be selected by turning this switch ON/OFF.

AUTO RESTART SETTING

(◆ . . . Factory setting)

SW 1-1	SW state
OFF	Invalidity
ON	Validity

● SW1-2, 1-3. Room temperature correct coefficient of heating.

Decide the heating temperature correct coefficient value of heating.

TEMPERATURE CORRECTION

(◆ . . . Factory setting)

SW 1-2	SW 1-3	SW state		
		heating	dry	cooling
OFF	OFF	+3.6degF	-3.6degF	-3.6degF
ON	OFF	-3.6degF	-3.6degF	-3.6degF
OFF	ON	0 degF	0 degF	0 degF
ON	ON	+7.2degF	0 degF	0 degF

● SW4-1. Dip SW 4-1 setting forbidden

(◆ . . . Factory setting)

SW 4-1	OFF
--------	-----

● SW4-2, 4-3. Ceiling height setting

(◆ . . . Factory setting)

Ceiling height ft. (m)		DIP - SW4		
		1	2	3
8ft. 2-7/16in. to 9ft. 10-1/8in. (2.5 to 3.0)	Normal	-	OFF	OFF
9ft. 10-1/8in. to 11ft. 5-25/32in. (3.0 to 3.5)	High ceiling 1	-	ON	OFF
More than 11ft. 5-25/32in. (3.5)	High ceiling 2	-	OFF	ON
Less than 8ft. 2-7/16in. (2.5)	Low ceiling	-	ON	ON

If the setting for a low ceiling is selected, the capacity of the air conditioner decreases slightly.

■ ROTARY SWITCH SETTING (SW2)

This switch can be used when group control system.
Set the indoor unit address in the 0,1,-,15 order.

(◆ . . . Factory setting)

◆	SW 2	SW state
	0	Single
	1 - 15	Indoor unit address

■ JUMPER WIRE SETTING

JM 1, 2, 3 setting forbidden

(◆ . . . Factory setting)

◆	JM 1, 2, 3	SW state
	Connect	Forbidden
	Disconnect	


3-15-3. WIRED REMOTE CONTROLLER CIRCUIT BOARD

Wired remote controller		
DIP SW	1	Dual remote controller setting
	2	
	3	Group control setting
	4	Model setting
	5	Auto changeover setting
	6	Memory backup setting

SWITCH POSITION

Wired remote controller

Front case (back side)



3-15-4. WIRED REMOTE CONTROLLER

■ DIP SWITCH SETTING

● 1. SW setting

1-1 Dual remote controller setting

Set the remote controller DIP switch No.1 and 2 according to the following table.

(◆ . . . Factory setting)

Number of remote controller	Master unit		Slave unit	
	DIP-SW No.1	DIP-SW No.2	DIP-SW No.1	DIP-SW No.2
◆ 1 (Normal)	ON	OFF	—	—
2 (Dual)	OFF	OFF	ON	ON

1-2 Group control setting

Number of indoor unit connection (One/Multiple)

This is switched according to the number of connected indoor units.

(◆ . . . Factory setting)

DIP-SW No.3	Number of indoor unit
◆ OFF	One unit connection
ON	Multiple unit connection

1-3 Model setting

The system type of the outdoor unit can be selected by setting up DIP switch No.4 as follows.

(◆ . . . Factory setting)

DIP-SW No.4	Model
◆ OFF	Heat Pump model
ON	Cooling only model

1-4 Auto changeover setting

Selecting auto changeover validity / invalidity.

(◆ . . . Factory setting)

DIP-SW No.5	Auto changeover
OFF	Invalidity
◆ ON	Validity

1-5 Memory backup setting

Set to ON to use batteries for the memory backup.If batteries are not used, all of the settings stored in memory will be deleted if there is a power failure.

※ This function is wired remotecontrol only.

(◆ . . . Factory setting)

DIP-SW No.6	Memory backup
OFF	Invalidity
◆ ON	Validity

3-16. OPTIONAL PARTS

■ ADDITIONAL GRILLE UTG-AGEA-W

The additional grille hides the gap between the ceiling hole and the outlet grille.

Additional grille (optional parts)

