

SPECIFICATION SUBMITTAL SHEET



FEATURES

Sizes: ☐ 2 1/2" ☐ 3" ☐ 4" ☐ 6" ☐ 8" ☐ 10"

Pressure/temperature: 200 psi @ 150°F WOG
125 psi @ 450°F Steam

End connections: Flanged Class 125 lb

(Closure plug not furnished)

OPTIONS

(Suffixes can be combined)

- ☐ - with epoxy paint (standard)
- ☐ C - with FDA epoxy coating inside and out

SCREEN

SIZE inch	OPENINGS (dia.)	MATERIAL THICKNESS	HOLES PER sq(in)
2 1/2	0.045	0.020	225
3	0.045	0.020	225
4	0.062	0.020	98
6	0.062	0.020	98
8	0.125	0.020	29
10	0.125	0.032	29

APPLICATION


Designed for installation on potable water lines to protect downstream equipment from malfunction or premature failure due to build-up of sediment or debris.

STANDARDS COMPLIANCE

- MIL-S 16293F Type 2
 - Lead Plumbing Law* Certified by IAPMO R&T
- *(0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

MATERIALS

Main valve body	Cast Iron ASTM A 126 Class B
Access cover	Cast Iron ASTM A 126 Class B
Coatings	FDA Approved Epoxy Finish (FSC)
Screens	Perforated Stainless Steel, 300 Series




SIZE		DIMENSIONS (approximate)							WEIGHT	
		A		B		C	D*			
in	mm	in	mm	in	mm			in	mm	lbs.
2 1/2	65	10	254	8 1/4	210	1 1/4 NPT	6	152	35	16
3	80	10 1/2	267	9 1/4	235	1 1/4 NPT	6	152	45	20.5
4	100	15	381	12 1/2	318	2 NPT	9	229	61	27.5
6	150	18	457	14	356	2 NPT	10	254	165	75
8	200	24 1/4	616	17 3/4	451	2 NPT	11	279	239	108.5
10	250	29 1/2	749	21 1/4	540	2 NPT	14	356	394	178.5


*Vertical clearance for screen removal

FLOW CHARACTERISTICS

MODEL FS 2 1/2", 3" & 4" (STANDARD & METRIC)




MODEL FS 6", 8" & 10" (STANDARD & METRIC)



TYPICAL INSTALLATION


Local codes shall govern installation requirements. Unless otherwise specified, the assembly shall be mounted with sufficient clearance for maintenance in accordance with the manufacturers' instructions and the latest edition of the Uniform Plumbing Code. The installation shall be made so that no part of the unit can be submerged. Horizontal installation with the strainer cap facing downward is the preferred installation orientation; however the strainer will provide protection in any orientation

Capacity thru Schedule 40 Pipe (GPM)				
Pipe Size	5 ft/sec	7.5 ft/sec	10 ft/sec	15 ft/sec
2 1/2"	75	112	149	224
3"	115	173	230	346
4"	198	298	397	595
6"	450	675	900	1351
8"	780	1169	1559	2339
10"	1229	1843	2458	3687



DIRECTION OF FLOW ➡

OUTDOOR INSTALLATION



DIRECTION OF FLOW ➡

INDOOR INSTALLATION

SPECIFICATIONS

The Cast Iron "Y" type strainer shall be in compliance with MIL-S-16293F Type 2. The main body and access cover shall be cast iron (ASTM A 126 Class B) and available with or without an FDA approved epoxy coating inside and out. The integral strainer screen shall be accessible for cleaning without removing the device from the line. The Cast Iron "Y" type strainer shall be a WILKINS Model FS or Model FSC.

WILKINS a Zurn company, 1747 Commerce Way, Paso Robles, CA 93446 Phone: 805/238-7100 Fax: 805/238-5766

In Canada: ZURN INDUSTRIES LIMITED, 3544 Nashua Dr., Mississauga, Ontario L4V 1L2 Phone: 905/405-8272 Fax: 905/405-1292

Product Support Help Line: 1-877-BACKFLOW (1-877-222-5356) • Website: <http://www.zurn.com>