



P O L Y K E N 236

H V A C T A P E S

POLYKEN® 236

Premium Grade Duct Tape - Printed

APPLICATIONS


- Seal metal duct work.
- Seal fiberglass insulation.
- Cover thermal insulations.
- Home & general repair.

FEATURES & BENEFITS

- Heavy-duty duct tape.
- Aggressive adhesive.
- Excellent handling characteristics.
- Conforms well to irregular surfaces.
- Will not twist or curl during application.
- Tested in accordance with UL 723.

Printed "Polyken 236, Max. Temp
200°F" with 4.5" repeat.

CONSTRUCTION



PRODUCT DESCRIPTION

Single-Coated Construction

Backing:

- Polyethylene Coated Cloth

Adhesive:

- Natural Rubber Based

Colors:

- Black & Silver - Printed

TEST DATA

Test	Typical Value	Typical Value (Metric)	Test Method
Total Thickness	12 mils	0.300 mm	ASTM D 1000
Adhesion to Steel	36 oz./in.	40.3 g/mm	PSTC-1
Adhesion to Backing	28 oz./in.	31.30 g/mm	PSTC-1
Tensile Strength	28 lb./in.	0.502 kg/mm	ASTM D 1000
Maximum Performance Temperature	200 D F		
Flame Spread	5		
Smoke Developed	5		

Typical values are not intended to be used for specification development. Technical data is believed to be true and accurate. We recommend the purchaser test the fitness for use for all applications.

Tyco
Adhesives

CORPORATE HEADQUARTER

25 FORGE PARKWAY
FRANKLIN, MA 02038
1-800-343-7875
Fax: 1-800-328-4822

www.tycoadhesives.com

A tyco INTERNATIONAL LTD. COMPANY