

Angle Hose Valves

UL, ULC and FM Approved



Description

Angle hose valves feature all brass* construction with forged or cast bodies for rigidity and light weight. Typical uses are in rack assemblies or any other application which requires a listed fire hose valve. Available in rough brass or polished chrome finish with a red hand wheel. **UL, ULC and FM Approved. Rated 300psi**

Installation

Install in accordance with customary installation practices. Use an approved thread sealant such as PipeFit Thread Sealing Paste with PTFE on the male threads to which the valve is being installed.

DO NOT OVER TIGHTEN. Over tightening of the valve during installation to the male pipe threads may crack or deform the valve body. Only use tools suitable for the installation of this product. Do not use pipe wrench extenders to increase leverage on pipe wrenches. This may result in valve damage as well as personal injury.

Specifications

Material:

Cast or forged Brass*

Body

Finish:

Rough Brass

*Polished Chrome

Threads:

2½" FNPT x FNPT

FNPT x MNST*

MBCT

MQST

MONT

MPHX

MTEM

MCLV

2½" GRV x FNPT

GRV x MNST

1½" FNPT x FNPT

FNPT x MNST

Friction loss is less than 3 psi thru an equivalent length of pipe per UL Standards.

*Contains lead. Not for use in water systems intended for human consumption.



Fire Protection Products, Inc

6241 Yarrow Dr., Suite A, Carlsbad, CA 92011-1541

For questions: 1 800 344-1822 • 1 800 344-3775 fax • www.fpfi.com