

38-200 SERIES

ATMOSPHERIC TYPE VACUUM BREAKER

Job Name:	Contractor:
Job Location:	P.O. Number:
Engineer:	Representative:
Tag:	Wholesale Distributor:

SPECIFICATIONS

The $\frac{1}{4}$ " $-\frac{3}{4}$ " Atmospheric Type Vacuum Breakers shall be Apollo 38-200 Series. The device is designed to prevent contamination of potable water due to back-siphonage. The 38-200 Series is not designed for backpressure conditions or continuous pressure applications longer than 12 hours in a 24-hour period and should only be installed in areas where spillage of water could not cause damage.


FEATURES

- Compact and easy to maintain
- Suitable for hot or cold water service
- · Corrosion-resistant forged brass body
- MADE IN THE USA

MATERIAL SPECIFICATIONS

Part Name	Material
Body	Forged Brass
Seat Disc	Silicone
Float	Polypropylene
Cap and Guide	Noryl [®]
Canopy	Chrome-plated Steel
Screw	Zinc-plated Steel

ORDERING INFORMATION



BODY STYLE

- **□ 0** Normal (90° Flow)
- ☐ 3 Deck Mounted ("U" Flow)

SIZE

- *Note: Deck-mounted available sizes are 1/4" & 3/8" only

FINISH

- 1 Rough Brass
- □ 3 Rough Chrome
- ☐ 6 Polished Chrome

APPROVALS

ASSE® 1001. ANSI® A112.1.1. CSA® B64.1.1 and IAPMO


PERFORMANCE RATING

Maximum Operating Pressure 125 psi Temperature Range up to 212 °F



DIMENSIONS (in.)

Size	Α	В	С	Wt. (lb.)	
1/4"	1 1/8	2 %	1	.51	
3/8"	1 1/8	2 %	1	.48	
1/2"	1 1/4	2 %	1 1/4	.55	
3/4"	1 ½	3	1 ½	.63	
* 1/4" *	3/4	2 ½	1 ½	.26	
* 3/8" *	7/8	2 ½	1 3/4	.31	



FLOW CURVES

