



P O L Y K E N 252

I N D U S T R I A L T A P E S

POLYKEN® 252

Professional Grade Duct Tape - Printed


APPLICATIONS

- Sealing metal duct work and fiberglass insulation.
- General purpose packaging.
- Home and general repair.

FEATURES & BENEFITS

- Metallized poly-coated cloth backed tape.
- Specially formulated pressure sensitive adhesive.
- High tensile strength, adhesion, and tack.
- Designed for sealing flexible ducts, insulation and other aluminum-colored surfaces.
- Extremely conformable.
- Will not twist or curl during application.
- Tested in accordance with UL 723.
- Printed "Polyken 252 Meets UL 723 Max Temp 200°F".

CONSTRUCTION



PRODUCT DESCRIPTION

Single-Coated Construction

Backing:

- Polyethylene Coated Cloth

Adhesive:

- Natural Rubber Based

Colors:

- Metallic - Printed

TEST DATA

Test	Typical Value	Typical Value (Metric)	Test Method
Total Thickness	11 mils	0.280 mm	ASTM D 1000
Adhesion to Steel	30 oz./in.	33.6 g/mm	PSTC-1
Adhesion to Backing	30 oz./in.	33.0 g/mm	PSTC-1
Tensile Strength	25 lb./in.	0.44 kg/mm	ASTM D 1000
Maximum Performance Temperature	200 D F		
Flame Spread	10		
Smoke Developed	5		

Typical values are not intended to be used for specification development. Technical data is believed to be true and accurate. We recommend the purchaser test the fitness for use for all applications.

Tyco
Adhesives

CORPORATE HEADQUARTERS

25 FORGE PARKWAY
FRANKLIN, MA 02038
1-800-343-7875

Fax: 1-800-328-4822

www.tvcoadhesives.com

A tyco INTERNATIONAL LTD. COMPANY