





ITEM	QTY	ITEM NO	DRAWING	PART NAME	MATERIAL
1	2	58408		1 SW PROTECTOR	POLYETHYLENE
2	1	58147	9205	BEARING RING	AMPCO ALUM BRONZE
3	1	20552	40502	BODY	A105
4	1	30201	40504	BONNET	A105
5	4	50221	60684A	FINISHED HEX NUT	F594 304SS
6	1	55008	45706C	GASKET	316/GRAFOIL
7	1	32625	40508	GATE	A351 GR CF8M
8	1	35016	36891	HANDWHEEL	MALLEABLE IRON
9	1	50006	17964	HANDWHEEL NUT	A105
10	4	50038	45417C	HEX HD BOLT	A193 GR B7
11	1	40481	38233	NAME PLATE(BLUE)	ALUMINUM
12	1	55176		PACKING	FLEXIBLE GRAPHITE
13	1	34072	35047	PACKING GLAND	A105
14	2	32117	40507	SEAT RING	A182 T316L HF
15	1	32797	40506	STEM	A182 T316
16	2	50129	21912	STUD BOLT	F593 304SS
17	1	58452		TACK WELD	(RMPWPS555)
18	1	34013	35045	YOKE	A105
19	1	58098	17961	YOKE NUT	A582 TYPE 416

NOTE:
PRESS SEATS PER RMPVFSP024
COLOR CODED AND TAGGED PER RMPVFSTD004
GATE VALVE TO BE TESTED PER API-598 PER RMPVFLT003

X.XX Inches
[XX,X] MM

WEIGHT	8.4 LBS	3.79 Kg
Cv FACTOR	20.3	

CNS	57468
REV	22
BY	R. Jackson
DATE	11-7-2003

DWN BY	JOE CECIL
CHK BY	S.R.
RVD BY	
DATE	4-2-62
SCALE	1.125

22

SERIES No: SW12111F8M-06	
ITEM No: 200692	
RATING: 1975 PSI • 100 F	SPECS: API 602/ASME B16.34
BODY A105 SEAT 316 HF DISC 316 STEM 316	
FLOWERVE Vogt Valves	
SULPHUR SPRINGS, TEXAS, USA	
1 GATE VALVE - FORGED STEEL	
-OS&Y - BOLTED BONNET - BOLTED GLAND -	
5" RENEWABLE SEATS - LOOSE SLOTTED GATE	
SOCKET WELD ENDS -CLASS 800	
40405-2D	