

Whole House Well water filter F-300-85



The F-300-85 whole house filter system is specially configured for your unique well water needs at the best price — satisfaction guaranteed.



The Aquasana F-300-85 Rhino Whole House Filter System treats and significantly reduces the bacterial contaminants and local pollutants specific to well water. Enjoy clean water, rich in minerals and low in contamination, from every faucet in your home for just pennies a day.



Our unique five-stage filtration process reduces organic compounds like pesticides and herbicides, treats bacterial contamination, and reduces 97% of the chlorine in your water — all for a low price.




The system is easy to install with the help of a licensed plumber, requires no back-flushing, and requires only minimal electricity (to power the UV filter). System maintenance is easy: replace the filter tanks every 300,000 gallons (about every three years for the average three-to four-bathroom household), and most people can do it without a plumber's assistance.

Choose an Aquasana whole house well water filter and rest easy knowing that you made the smartest decision about the water in your home.

Made in the USA.

Whole House Well water filter F-300-85

What's inside



Pure Satisfaction

All Aquasana products offer a 90-day 100% satisfaction guarantee. (This system includes a three-year warranty, which covers defects in materials and workmanship.) If for any reason you are not satisfied with your purchase, contact the dealer you purchased from for a full refund (upon return of the product.)

This filter system is designed and tested for use with genuine Aquasana parts, including replacement filters and all hardware. Use of parts from other manufacturers may result in loss of contaminant reduction performance, system damage or failure. Use of parts from other manufacturers will also void your warranty. Contact your Ferguson store for replacement parts. This unit must be installed by a licensed plumber to validate the warranty.

Specifications

Model: F-300R-85
 Replacement filters:
 Main tanks: F-300-85 UV Bulb: AQ-UV-LAMP
 Pre-filter: EQ-PFC.20 Post-Filter: EQ-PFC.35
 Rated service flow: 7 gpm
 Max working pressure: 20-75 psi
 Max operating temperature: 40-90° F
 Recommended capacity: 300,000 gal
 Available in ¾" or 1" install kits

A double manifold system is available for homes larger than 3-4 bathrooms.

