

Low profile hot water baseboard radiation



The compact baseboard with quality features

Slant/Fin. Fine/Line15 COMPACT BASEBOARD RADIATION More professional heating contractors install Slant/Fin baseboard than any other brand!

Fine/Line 15 baseboard is designed for fast, simple installation from the moment you open the first carton to when you snap on the last accessory. Fine/Line 15 baseboard features include a high performance heating element, sure grip support brackets and low profile reinforced enclosure. You can count on cost-effective installations that look good for years and years.

Fine/Line 15 installs fast. Pre-cut lengths from 2' to 12' are fully assembled and packed in heavy-duty, multi-wall

reinforced cartons to protect the baseboard from shipping damage. You can figure your runs in half-foot increments using the 3½ length, and then make up odd inches with the telescoping accessories. Corners, end caps, piano-hinged wall trims and filler sleeves snap positively in place to reduce installation time and enhance appearance. The Nu-White baked enamel finish complements any decor or may be painted to match other room accents.

Just 7 inches high, but it towers!

Hot water baseboard heating preferred by 88% of homeowners surveyed!

Research shows that of homeowners who have experienced both warm air heating and hot water heating, 88% prefer the comfort, health benefits and cleanliness of hot water baseboard heating.


Ducted warm air heating

- Drafty, uneven heating
- Dirty ducts breed and spread germs
- Noisy Difficult to zone
- Less efficient

Builders and owners of better homes choose Slant/Fin hydronic boilerbaseboard heating. A Slant/Fin hot water baseboard perimeter system surrounds you with quiet, draft-free heating comfort.

Slant/Fin hot water heating

- Gentle, even heating from floor to ceiling
- Germs don't breed/spread
- Quiet Easy to zone
- More efficient



High heating efficiency! Better built!

Low profile!



Factory assembled for fast package-to-wall installation using screw gun, nails or T-shot nailing tool.



High performance heating element with selfadjusting expansion cradle rides on heavy-duty support bracket.



Computer-assisted manu quality and fit, length-to-

Made by Slant/Fin. Better in design, engineering and performance.



Sure-grip support brackets keep the front panel rigidly in place to avoid "pop-off". Bracket is manufactured from heavy gauge steel, shaped by a series of progressive die strikes which multiply the strength of the metal alone. The bracket becomes a powerful "spine" for the entire unit, holding cover, element and damper vane securely in place.




1/2" or 3/4" high performance heating elements.

Choice of element size broadens range of applications and can help reduce installation costs. Double bent aluminum fins increase heating surface, reinforce each other and help stop expansion noise. Maximum heat output. Fins won't loosen. Plated steel end fins protect aluminum fins from damage.



Strong enclosure holds its shape under rugged use. The unique channeled front panel resists twisting and adds lateral strength. Front panel and onepiece bottom, back and top panels are formed from prime, cold rolled, rephosphorized heavy gauge steel. Precision accessories snap in place and stay in place.



No-noise expansion cradles. Self-adjusting expansion cradles of smooth plastic are clipped to fins of element and positioned over support brackets. Eliminates noisy metal-to-metal contact with bracket and enclosure. Ridges on both sides of cradle bottom and unique bracket flag prevent cradle from slipping off bracket.



Contractor friendly. Enclosure, bracket and accessories are designed with the

sories are designed with the contractor in mind. Optional 180° vented or non-vented return bend aligns return tubing to run above the heating element. Hinged accessories telescope laterally for precise fit while providing flip-up access to tubing.



Fully modulating damper helps control temperature in each room individually. Unique corrosion resistant pivot and damper mounting assembly provide the straightest, most responsive damper available. It comes fully assembled on every foot of Fine/Line 15. Adjusts easily from fully open to fully closed or any setting in-between.



facturing ensures consistent length and job-to-job.



Front cover locks into a unique support bracket hook. Swings down and snaps in place. Avoids "pop-off".



Neat fitting accessories give the job a finished look. Splice plate sets are included free with lengths 5' and longer.

Fine/Line 15 hot water baseboard radiation accessories:

NON-HINGED WALL TRIM

No. 15-WT-7FL—6³/₄" floor length

No. 15-WT-2-2

No. 15-WT-4-41/2"

No. 15-WT-675-63/4"

Packing: 2 per box

Please specify part number and name when ordering.



HINGED END CAP No. 15-LECH-LEFT No. 15-RECH-RIGHT 4" wide with pianohinged door. Allows 3" adjustment. Packing: 2 per box SLOTTED (not shown) No. 15-LESH-LEFT



HINGED WALL TRIM No. 15-WTH 4" wide with pianohinged front panel; fits either end Packing: 2 per box



INSIDE CORNER No. 15-IC-90-90° No. 15-IC-135-135° 33/4" wide at top (25/16" for 135°), with piano-hinged front. Packing: 2 per box

2" SPLICE

PLATE SET

Included free with

every baseboard

unit 5' and over.



OUTSIDE CORNER

No. 15-OC-135-135°

4½" wide, one-piece unit.

No. 15-OC-90-90°

No. 15-FS-No. 15-FS-14-14" Covers gaps from 1" to 6" or 1" to 12". Includes top, front, back, damper. Packing: 1 per envelope.



NON-HINGED END CAP No. 15- LECN-LEFT No. 15-RECN-RIGHT 2¹/₂" solid metal Packing: 2 per box

No. 15-RESH-RIGHT

Ratings:

Fine/Line 15 Series

(Hot water ratings, BTU/HR per linear ft. with 65°F entering air)


ELEMENT	WATER FLOW	PRESSURE DROP‡	110°F	120°F	130°F	140°F	150°F	160°F	170°F	180°F	190°F	200°F	210°F	215°F	220°F
NO. 15-75E Baseboard with 3/4" element †	1 GPM	47	140*	190*	240*	290*	350	420	480	550	620	680	750	780	820
	4 GPM	525	150*	200*	260*	310*	370	440	510	580	660	720	790	820	870
NO. 15-50 Baseboard with 1/2 ["] element †	1 GPM	260	150*	200*	260*	300*	370	430	490	550	610	680	740	770	800
	4 GPM	2880	160*	210*	270*	330*	390	450	520	580	640	720	780	810	850

‡ Milinches per foot. † Nominal

Ratings at 140 F and lower temperatures determined by multiplying 150 F rating by the applicable factor specified in Table E in the I=B=R Testing and Rating Standard for Baseboard radiation.

NOTE: Ratings are for element installed as per drawing shown in "Dimensional Data" window (open "Dimensional Data" window to view) with damper open, with expansion cradles. Ratings are based on active finned length (5" to 6" less than overall length)and include 15% heating effect factor. Ratings are also based on 3/4" or 1/2" nominal copper tubing with 2-5/8" x 2-1/8" x .009" aluminum fins bent to 2-19/64" x 2-1/8" (15-75E) or 2-1/8" x 2-9/32" (15-50) spaced 55 per linear foot (unpainted.) Use 4 gpm ratings only when flow is known to be equal to or greater than 4 gpm; otherwise, 1 gpm ratings must be used.

Dimensional and installation data:





©Slant/Fin 2010. Printed in U.S.A. 1110. Publication No. 15-10

SLANT/FIN CORPORATION, Greenvale, N.Y. 11548 Phone: (516) 484-2600 · FAX: (516) 484-5921 · www.slantfin.com Canada: Slant/Fin LTD/LTEE, Mississauga, Ontario • www.slantfin.ca

Ordering data: COMPLETE BASEBOARD PACKAGE

FILLER

SLEEVE

No. 15-75E (with ³/₄" element) No. 15-50 (with 1/2" element) Carton contains fully assembled baseboard, complete with damper vane, heating element and expansion cradles. 2" splice plate set packed with lengths 5' and over. 10' and 12' foot assemblies contain two separate elements.

LENGTHS: 2', 3', 3½', 4', 5', 6', 7', 8', 10', 12'

COLOR Nu-White baked enamel finish

No. 15-D ENCLOSURE ONLY PACKAGE Same as No. 15-75E and 15-50, but WITH-OUT heating element or expansion cradles.

No. E-75E 3/4" ELEMENT ONLY No. E-50 1/2" ELEMENT ONLY Heating element with expansion cradles; NO enclosure. Packed in individual sleeves. LENGTHS: 2', 3', 3¹/₂', 4', 5', 6', 7', 8'

Specifications:

HEATING ELEMENT: Furnish and install E-75E (E-50) baseboard heating element as manufactured by Slant/Fin Corp., consisting of 3/4" or 1/2" nominal copper tubing, with 2/5/" x 21/8" x .009" aluminum fins, bent to 21%4" x 21/8" or 25%" x 21%", spaced 55 per linear foot. End fins are of plated steel for extra ruggedness. Polypropylene expansion cradles shall be clipped to element, centered over each support bracket, and shall protect element from contact with support brackets or enclosure.

COVER ASSEMBLY: Furnish and install 15-75E (15-50) baseboard cover assembly as manufactured by Slant/Fin Corp., consisting of back panel, front panel, damper vane and support brackets (electro-galvanized), formed of cold rolled steel. Edges of back panel shall be formed to provide channels to receive support brackets. Top edge of front panel shall be formed to provide a full-length hinge, interlocking with each support bracket. Damper vane shall modulate fully and retain any setting through its arc. All cover components shall be painted in Nu-White thermosetting polvester enamel.