



ELITE Series

LED Dimmable 7W MR16 Lamp

LED Dimmable MR16 25,000 Hours average rated life, 12 & 120 Volts

Applications:

Ideal for dimmable MR16 flood and spot applications.


- + Track Lights
- + Recessed Downlights
- + Display Lights
- + Outdoor Fixtures that Protect Lamps from the Elements



Features

Benefits

High lumen output	Replaces 50W halogen MR16
Up to 85% less energy than halogen alternatives	Instant energy savings
Smooth, uniform dimming	Set the perfect mood & atmosphere
Long life	Minimizes replacement and maintenance costs
Very low heat generation	Perfect for sensitive display lighting such as art galleries.
Excellent Color Consistency and CRI	Enhances colors of focal point while maintaining uniformity throughout lighting installation from lamp to lamp.
Low weight	Track or down light installations are not strained by excess weight.
Shatter resistant	Lower the risk of injury and breakage



Catalog Number

Notes

Type



Specifications

Input Line Voltage:	12V AC/DC & 120V
Input Power	7W
Input Line Frequency	50/60HZ
Lamp Life (Rated)	25,000 hrs
Minimum Starting Temp	-30°C
Maximum Operating Temp	40°C
CCT	24K, 27K, 30K, 41K
CRI	82
Beam Angles	20 & 40

Lens Angles



Warranties and Certifications:	Item #	Description	Voltage	Wattage	Replacement	Lumens	LPW	CBCP est.	Beam Angle	CCT	CRI	M.O.L. (inches)	Diameter (inches)	Case Quantity	
 3 YEAR WARRANTY	120V GU10 MR16														
	LED7MR16GU1024KNFL	Dimmable 7W GU10 MR16 - 2400K, 40°	120	7	50	500	71.4	TBD	40	2400K	82	2.5	2	12	
	LED7MR16GU1024KNFL	Dimmable 7W GU10 MR16 - 2400K, 20°	120	7	50	500	71.4	TBD	20	2400K	82	2.5	2	12	
	LED7MR16GU1027KNFL	Dimmable 7W GU10 MR16 - 2700K, 20°	120	7	50	500	71.4	TBD	20	2700K	82	2.5	2	12	
	LED7MR16GU1027KNFL	Dimmable 7W GU10 MR16 - 2700K, 40°	120	7	50	500	71.4	TBD	40	2700K	82	2.5	2	12	
	LED7MR16GU1030KNFL	Dimmable 7W GU10 MR16 - 3000K, 20°	120	7	50	500	71.4	TBD	20	3000K	82	2.5	2	12	
	LED7MR16GU1030KNFL	Dimmable 7W GU10 MR16 - 3000K, 40°	120	7	50	500	71.4	TBD	40	3000K	82	2.5	2	12	
	LED7MR16GU1041KNFL	Dimmable 7W GU10 MR16 - 4100K, 20°	120	7	50	525	75.0	TBD	20	4100K	82	2.5	2	12	
	LED7MR16GU1041KNFL	Dimmable 7W GU10 MR16 - 4100K, 40°	120	7	50	525	75.0	TBD	40	4100K	82	2.5	2	12	
Specification Notes:	12V MR16														
	LED712VMR1624KNFL	Dimmable 7W 12V MR16 - 2400K, 20°	12	7	50	500	71.4	TBD	20	2400K	82	2	2	12	
	LED712VMR1624KFL	Dimmable 7W 12V MR16 - 2400K, 40°	12	7	50	500	71.4	TBD	40	2400K	82	2	2	12	
	LED712VMR1627KNFL	Dimmable 7W 12V MR16 - 2700K, 20°	12	7	50	500	71.4	TBD	20	2700K	82	2	2	12	
	LED712VMR1627KFL	Dimmable 7W 12V MR16 - 2700K, 40°	12	7	50	500	71.4	TBD	40	2700K	82	2	2	12	
	LED712VMR1630KNFL	Dimmable 7W 12V MR16 - 3000K, 20°	12	7	50	500	71.4	TBD	20	3000K	82	2	2	12	
	LED712VMR1630KFL	Dimmable 7W 12V MR16 - 3000K, 40°	12	7	50	500	71.4	TBD	40	3000K	82	2	2	12	
	LED712VMR1641KNFL	Dimmable 7W 12V MR16 - 4100K, 20°	12	7	50	525	75.0	TBD	20	4100K	82	2	2	12	
	LED712VMR1641KFL	Dimmable 7W 12V MR16 - 4100K, 40°	12	7	50	525	75.0	TBD	40	4100K	82	2	2	12	
	120V PAR16														
	LED7P1624KNFL	Dimmable 7W PAR16 - 2400K, 20°	120	7	50	500	71.4	TBD	20	2400K	82	3	2	12	
	LED7P1624KFL	Dimmable 7W PAR16 - 2400K, 40°	120	7	50	500	71.4	TBD	40	2400K	82	3	2	12	
	LED7P1627KNFL	Dimmable 7W PAR16 - 2700K, 20°	120	7	50	500	71.4	TBD	20	2700K	82	3	2	12	
	LED7P1627KFL	Dimmable 7W PAR16 - 2700K, 40°	120	7	50	500	71.4	TBD	40	2700K	82	3	2	12	
	LED7P1630KNFL	Dimmable 7W PAR16 - 3000K, 20°	120	7	50	500	71.4	TBD	20	3000K	82	3	2	12	
LED7P1630KFL	Dimmable 7W PAR16 - 3000K, 40°	120	7	50	500	71.4	TBD	40	3000K	82	3	2	12		
LED7P1641KNFL	Dimmable 7W PAR16 - 4100K, 20°	120	7	50	525	75.0	TBD	20	4100K	82	3	2	12		
LED7P1641KFL	Dimmable 7W PAR16 - 4100K, 40°	120	7	50	525	75.0	TBD	40	4100K	82	3	2	12		

