FIGURE 7202

BEAM CLAMPS



MI BEAM C-CLAMP


The FNW Figure 7202 malleable iron beam C-Clamp is designed for attaching a hanger rod to the bottom flange of a beam. The hanger rod should make contact with the beam flange to ensure full engagement.

FEATURES

- Finish: plain or zinc plated
- Material: malleable iron, ASTM A47 Grade 32510
- Wide throat
- Per: MSS SP-58, type 23
- Hanger rod not included







REFERENCE CHART

| Catalog Number | Finish | Rod Size | Max Load (lbs.) | Dimensions (in.) | | | | Wt. (oz.) |
|----------------|-------------|----------|--------------------|------------------|------|------|------|------------|
| | | | | Α | В | С | D | VVI. (UZ.) |
| FNW7202PC | Plain | 3/8"-16 | 400 | 1.75 | 0.63 | 1.75 | 0.75 | 3.6 |
| FNW7202ZC | Zinc plated | 3/8"-16 | 400 | 1.75 | 0.63 | 1.75 | 0.75 | 3.6 |
| FNW7202PD | Plain | 1/2"-13 | 400 | 1.75 | 0.63 | 1.75 | 0.75 | 4.09 |
| FNW7202ZD | Zinc plated | 1/2"-13 | 400 | 1.75 | 0.63 | 1.75 | 0.75 | 4.09 |
| FNW7202PE | Plain | 5/8"-11 | 530 | 2.00 | 0.75 | 2.00 | 0.75 | 8.54 |

Note: Do not overtighten the set screw or the clamp can be damaged. The set screw should be finger tight, then given approximately an additional 1/4 to 1/3 turn. The recommended set screw torque is 5 ft-lbs (60 in-lbs).