#### B351L - Steel C-Clamp With Locknut (TOLCO Fig. 64)


**Size Range:** <sup>3</sup>/8"-16 thru <sup>7</sup>/8"-9 rod

#### Material: Steel

**Function:** For attachment to I-beams, channels, and wide flange beams where the thickness does not exceed <sup>3</sup>/4" (19.0mm). Hardened set screw secures "C" Clamp to beam.

**Approvals:** B351L (<sup>3</sup>/8"-16 - <sup>3</sup>/4"-10), is Underwriters Laboratories Listed. Conforms to Federal Specification WW-H-171E & A-A-1192A, Type 23 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58, Type 23.

**Finish:** Plain. Contact B-Line for alternative finishes and materials. **Note:** When retaining strap is required, order B3362 thru B3365 separately. See page 29.



Order By: Part number and finish

Part No.	Rod Size		B ()		C ()		D ()	Lo	sign bad	Pipe Si	num Iron ze Per UL		k. Wt./100
	A	in.	(mm)	in.	(mm)	in.	(mm)	Lbs.	(kN)	in.	(mm)	Lbs.	(kg)
<b>B351L-<sup>3</sup>/</b> 8	<sup>3</sup> /8"-16	2 <sup>3</sup> /8"	(60.3)	2 <sup>3</sup> /8"	(60.3)	3/4"	(19.0)	300	(0.89)	4"	(100)	41	(18.6)
B351L- <sup>1</sup> /2	<sup>1</sup> /2"-13	2 <sup>3</sup> /8"	(60.3)	2 <sup>3</sup> /8"	(60.3)	3/4"	(19.0)	380	(1.69)	6"	(150)	41	(18.6)
B351L- <sup>5</sup> /8	<sup>5</sup> /8"-11	2 <sup>3</sup> /8"	(60.3)	2 <sup>1</sup> /4"	(57.1)	3/4"	(19.0)	550	(2.44)	6"	(150)	60	(27.2)
B351L- <sup>3</sup> /4	<sup>3</sup> /4"-10	2 <sup>3</sup> /8"	(60.3)	2 <sup>1</sup> /4"	(57.1)	3/4"	(19.0)	630	(2.80)	6"	(150)	71	(32.2)
B351L- <sup>7</sup> /8	<sup>7</sup> /8"-9	3"	(76.2)	31/4"	(82.5)	1"	(25.4)	1200	(5.34)			184	(83.4)

Note: See page 27 for recommended setscrew torque.

#### B3036L - Malleable Iron C-Clamp With Locknut

**Size Range:** <sup>3</sup>/8"-16 thru <sup>3</sup>/4"-10 rod

Material: Malleable Iron

Pipe Hangers & Supports


**Function:** Designed for attaching a hanger rod to the flange of a beam.

**Approvals:** B3036L is Underwriters Laboratories Listed. Complies with Federal Specification WW-H-171E & A-A-1192A Type 23 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58 Type 23.

Finish: Plain or Electro-Galvanized

**Order By:** Part number and finish. When retaining strap is required, order B3362 thru B3365 separately. See page 29.





Part No.	Rod Size		В		C		esign .oad		um Iron :e Per UL	Approx	. Wt./100
	Α	in.	(mm)	in.	(mm)	Lbs.	(kN)	in.	(mm)	Lbs.	(kg)
B3036L- <sup>3</sup> /8	<sup>3</sup> /8"-16	1 <sup>3</sup> /4"	(44.4)	1 <sup>3</sup> /4"	(44.4)	300	(0.89)	4"	(100)	41	(18.6)
B3036L-1/2	<sup>1</sup> /2"-13	1 <sup>3</sup> /4"	(44.4)	1 <sup>3</sup> /4"	(44.4)	380	(1.69)	5"	(125)	41	(18.6)
B3036L- <sup>5</sup> /8	<sup>5</sup> /8"-11	2"	(50.8)	1 <sup>7</sup> /8"	(47.6)	530	(2.36)	6"	(150)	60	(27.2)
B3036L- <sup>3</sup> /4	<sup>3</sup> /4"-10	2"	(50.8)	2"	(50.8)	530	(2.36)	6"	(150)	71	(32.2)

Note: See page 27 for recommended setscrew torque.

### B3362, B3363, B3364, B3365 - Retaining Strap

Size Range: 6" (152.4mm) to 12" (304.8mm) lengths

Material: Steel (Stainless Steel available) Finish: Pre-Galvanized


**Function:** Designed for use with B351L

and B3036L C-Clamps. **Order By:** Part number, length 'L', (add 1" (25.4) minimum to flange width), and finish.

Note: Requires field forming on beam.

Flanç in.	ge Width (mm)	Len in.	gth L (mm)
3"-5"	(76-127)	6"	(152.4)
5"-7"	(127-178)	8"	(203.2)
7"-9"	(178-228)	10"	(254.0)
9"-11"	(228-279)	12"	(304.8)

Material Thickness 12 Gauge (2.7)



#### B3037 - Z-Purlin Malleable C-Clamp

Material: Malleable Iron

**Function:** Designed for attaching a <sup>3</sup>/8"-16 hanger rod to the bottom flange of a Z-purlin.

**Approvals:** Underwriters Laboratories Listed for up to 4" (100mm) pipe. Conforms to Federal Specification WW-H-171E & A-A-1192A, Type 23 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58, Type 23.


Finish: Plain or Electro-Galvanized

Order By: Part number and finish.

Weight: Approx. Wt./100 90 Lbs. (40.8kg)

Design Load: 400 Lbs. (1.78kN)

Note: See page 27 for recommended setscrew torque.





### B3031-3/8 - Light Duty Malleable C-Clamp

#### Material: Malleable Iron

**Function:** Designed for attaching a <sup>3</sup>/8"-16 hanger rod to the top or bottom flange of a beam or bar joist when setscrew is in the down position as shown.

**Approvals:** Underwriters Laboratories Listed for up to 4" pipe. Conforms to Federal Specification WW-H-171E & A-A-1192A, Type 19 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58, Type 19.


Finish: Plain or Electro-Galvanized

**Order By:** Part number and finish. When retaining strap is required, order Fig. 69 separately. See Page 37.

Weight: Approx. Wt./100 25 Lbs. (11.3kg)

Design Load: 350 Lbs. (1.55kN)

Note: See page 27 for recommended setscrew torque.



#### B3033 - Wide Jaw Reversible C-Clamp (TOLCO Fig. 68)

Size Range: 3/8"-16 thru 3/4"-10 rod

Material: Cast Malleable Steel with hardened cup point set screw and jam nut

**Function:** For attachment to structural shapes requiring wider throat especially under roof with bar joist construction.


This clamp may be used with the set screw in the up or down position.

**Approvals:** Underwriters Laboratories Listed **(cULus)** and Factory Mutual Engineering Approved **(FM)**. Conforms to Federal Specification WW-H-171E Type 19 & A-A-1192A, Type 19 & 23 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58, Type 19 & 23.


Finish: Plain. Contact B-Line for alternative finishes and materials.

Order By: Part number, rod size and finish

**Note:** Do not over tighten set screw.




Throat Opening 1<sup>1</sup>/4" (31.7) for B3033-<sup>3</sup>/8 & <sup>1</sup>/2 1<sup>5</sup>/16<sup>III</sup> (33.3) for B3033-<sup>5</sup>/8 & <sup>3</sup>/4









nent	

Part No.	Rod Size	E	3		C	I	)	•	ı Load w Up	ith Sets Dov		Maxim Pipe Siz			orox. ./100
	Α	in.	(mm)	in.	(mm)	in.	(mm)	Lbs.	(kN)	Lbs.	(kN)	in.	(mm)	Lbs.	(kg)
<b>B3033-</b> 3/8	<sup>3</sup> /8"-16	21/4"	(57.1)	2"	(50.8)	1 <sup>1</sup> /8"	(28.6)	610	(2.71)	610	(2.71)	4"	(100)	54	(24.5)
<b>B3033-</b> 1/2	<sup>1</sup> /2"-13	2 <sup>5</sup> /16"	(58.7)	2 <sup>3</sup> /16"	(55.6)	1 <sup>1</sup> /4"	(31.7)	750	(3.33)	1130	(5.02)	8"	(200)	51	(23.1)
<b>B3033-</b> 5/8	<sup>5</sup> /8"-11	2 <sup>5</sup> /8"	(66.7)	2 <sup>1</sup> /2"	(63.5)	1 <sup>3</sup> /8"	(34.9)	750	(3.33)	1130	(5.02)	8"	(200)	70	(31.7)
<b>B3033-</b> <sup>3</sup> /4	<sup>3</sup> /4"-10	2 <sup>11</sup> /16"	(68.3)	2 <sup>1</sup> /2"	(63.5)	1 <sup>7</sup> /16"	(36.5)	750	(3.33)	1130	(5.02)	10"	(250)	98	(44.4)

Note: See page 27 for recommended setscrew torque.

All dimensions in charts and on drawings are in inches. Dimensions shown in parentheses are in millimeters unless otherwise specified.



Beam Clamps

#### B3034 - C-Clamp

**Size Range:** <sup>3</sup>/8"-16 thru <sup>3</sup>/4"-10 rod

Material: Cast Malleable Steel with hardened cup point set screw and jam nut


**Function:** Recommended for hanging from steel beam where flange thickness does not exceed <sup>3</sup>/4" (19.0mm).

**Features:** May be used on top or bottom flange of the beam. Beveled lip allows hanging from top flange where clearance is limited. may be installed with the set screw in the up or down position. Offset design permits unlimited rod adjustment by allowing the rod to be threaded completely through the clamp. The rear window design permits inspection of thread engagement.

**Approvals:** Underwriters Laboratories Listed and Factory Mutual Engineering Approved for 3/8"-16 and 1/2"-13 rod sizes. Conforms to Federal Specification WW-H-171E & A-A-1192A, Type 19 & 23 and Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58, Type 19 & 23. 3/8"-16 is **(cULus)** Listed to support up to 4" (100mm) pipe with the set screw in the down position, up to 3" (75mm) pipe with the set screw in the up position. 1/2"-13 is **(cULus)** Listed to support up to 8" (200mm) pipe with the set screw in the up position.

Finish: Plain. Contact B-Line for alternative finishes and materials.

Order By: Part number and finish



B3034-3/8" and B3034-1/2" sizes Attach only as shown. C B Throat Opening 3/4" (19.0) (Rod Size) Hanger Rod Not Included Set Screw and Locknut Included Top Flange Attachment Applications 習 Bottom Flange Attachment Applications

Part No.	Rod Size	E	3	(	C		D		Design Load with Up		screw vn	Maximum Iron Pipe Size Per UL		Approx. Wt./100	
	Α	in.	(mm)	in.	(mm)	in.	(mm)	Lbs.	(kN)	Lbs.	(kN)	in.	(mm)	Lbs.	(kg)
<b>B3034-</b> <sup>3</sup> /8	<sup>3</sup> /8"-16	1 <sup>5</sup> /8"	(41.3)	2"	(50.8)	7/8"	(19.0)	610	(2.71)	610	(2.71)	4"	(100)	30	(13.6)
<b>B3034-</b> 1/2	<sup>1</sup> /2"-13	1 <sup>13</sup> /16"	(46.0)	2 <sup>3</sup> /16"	(55.6)	1 <sup>3</sup> /16"	(30.2)	750	(3.33)	1130	(5.02)	8"	(200)	47	(21.3)
<b>B3034-</b> 5/8	<sup>5</sup> /8"-11	1 <sup>3</sup> /4"	(44.5)	2 <sup>1</sup> /8"	(54.0)	1 <sup>1</sup> /4"	(31.7)	750	(3.33)	1130	(5.02)			58	(26.3)
<b>B3034-</b> <sup>3</sup> /4	<sup>3</sup> /4"-10	2"	(50.8)	21/4"	(57.2)	1 <sup>1</sup> /4"	(31.7)	750	(3.33)	1130	(5.02)			77	(35.0)

Note: See page 27 for recommended setscrew torque.



### Fig. 68S - Reversible Malleable Beam Clamp <sup>3</sup>/4" (19.0mm) Throat Opening Fig. 68W - Reversible Malleable Beam Clamp 1<sup>1</sup>/4" (31.7mm) Throat Opening (bottom of page)

#### Size Range:

3/8"-16 rod sizes thru 7/8"-9 rod sizes

() TOLCO

Material: Cast Malleable Steel with hardened cup point set screw and jam nut

**Function:** Recommended for hanging from steel beam where flange thickness does not exceed  $^{3}/_{4}$ " (19.0mm) on Fig. 68S or  $1^{1}/_{4}$ " (31.7mm) on Fig.68W.

**Features:** May be used on top or bottom flange of beam. Beveled lip allows hanging from top flange where clearance is limited. May be installed with set screw in up or down position. Offset design permits unlimited rod adjustment by allowing the rod to be threaded completely through the clamp. The rear window design permits inspection of thread engagement.

**Approvals:** Factory Mutual Engineering Approved. Underwriters Laboratories Listed. Conforms to Federal Specification WW-H-171E, Type 23 and Manufacturers Standardization Society SP-58, Type 19.

Fig. 68S-<sup>3</sup>/<sub>8</sub> is cULus Listed to support up to 4" (100mm) pipe with the set screw in the down position and up to 3" (80mm) pipe with the set screw in the up position. Fig. 68S-<sup>1</sup>/<sub>2</sub> is cULus Listed to support up to 8" (200mm) pipe with the set screw in the down position and up to 6" (150mm) pipe with the set screw in the up position. Fig. 68W-<sup>3</sup>/<sub>8</sub> is cULus Listed to support up to 4" (100mm) pipe with the set screw in the down position and up to 4" (100mm) pipe with the set screw in the up position. Fig. 68W-<sup>1</sup>/<sub>2</sub> is cULus Listed to support up to 6" (150mm) pipe with the set screw in the down position and up to 6" (150mm) pipe with the set screw in the up position. Fig. 68W-<sup>1</sup>/<sub>2</sub> is cULus Listed to support up to 6" (150mm) pipe with the set screw in the down position and up to 6" (150mm) pipe with the set screw in the up position. Factory Mutual Engineering approved only with the set screw in the down position.

**(OSHPD)**. For additional load spacing and placement information relating OSHPD projects, please refer to the Seismic Restraint System Guidelines.

Finish: Plain. Contact B-Line for Electro-Galvanized or HDG finishes.

Order By: Part number and finish








Part No.	Rod Size A	in.	3 (mm)		C in. (mm)	[ in.	) (mm)	in.	E (mm)	F in.	(mm)	Max Re Set Sci Lbs.		Max Re Set Scre Lbs.		App Wt./ Lbs.	
68S- <sup>3</sup> /8	<sup>3</sup> /8"-16	1 <sup>9</sup> /16"	(39.7)	3/4"	(19.0)	1 <sup>1</sup> /8"	(28.6)		(11.1)	7/8"	(22.2)	610	(2.71)	610	(2.71)	32	(14.5)
68S-1/2	<sup>1</sup> /2"-13	1 <sup>5</sup> /8"	(41.3)	3/4"	(19.0)	1"	(25.4)	7/16"	(11.1)	1 <sup>1</sup> /8"	(28.6)	750	(3.33)	1130	(5.02)	54	(24.5)
68S- <sup>5</sup> /8	<sup>5</sup> /8"-11	1 <sup>9</sup> /16"	(39.7)	3/4"	(19.0)	1"	(25.4)	<sup>9</sup> /16"	(14.3)	1 <sup>1</sup> /8"	(28.6)	750	(3.33)	1130	(5.02)	50	(22.7)
68S- <sup>3</sup> /4	<sup>3</sup> /4"-10	1 <sup>3</sup> /4"	(44.4)	3/4"	(19.0)	1 <sup>1</sup> /8"	(28.6)	<sup>9</sup> /16"	(14.3)	1 <sup>1</sup> /4"	(31.7)	750	(3.33)	1130	(5.02)	81	(36.7)
68S- <sup>7</sup> /8	<sup>7</sup> /8"-9	1 <sup>3</sup> /4"	(44.4)	3/4"	(19.0)	1 <sup>1</sup> /8"	(28.6)	<sup>9</sup> /16"	(14.3)	1 <sup>5</sup> /16"	(33.3)	750	(3.33)	1130	(5.02)	75	(34.0)

#### Fig. 68W

Part	Rod Size	I	B		C in.	[	)		E	F		Max Re Set Sci			c. Load w Down	App Wt./	
No.	A	in.	(mm)	in.	(mm)	in.	(mm)	in.	(mm)	in.	(mm)	Lbs.	(kN)	Lbs.	(kN)	Lbs.	(kg)
68W- <sup>3</sup> /8	<sup>3</sup> /8"-16	1 <sup>9</sup> /16"	(39.7)	1 <sup>1</sup> /4"	(31.7)	1 <sup>1</sup> /8"	(28.6)	<sup>7</sup> /16"	(11.1)	7/8"	(22.2)	610	(2.71)	610	(2.71)	41	(18.6)
68W-1/2	<sup>1</sup> /2"-13	<b>1</b> <sup>9</sup> /16"	(39.7)	1 <sup>1</sup> /4"	(31.7)	1"	(25.4)	5/8"	(15.9)	1 <sup>1</sup> /8"	(28.6)	750	(3.33)	1130	(5.02)	66	(29.9)
68W- <sup>5</sup> /8	<sup>5</sup> /8"-11	1 <sup>1</sup> /2"	(38.1)	1 <sup>1</sup> /4"	(31.7)	1"	(25.4)	<sup>9</sup> /16"	(14.3)	1 <sup>1</sup> /8"	(28.6)	750	(3.33)	1130	(5.02)	68	(30.8)
68W- <sup>3</sup> /4	<sup>3</sup> /4"-10	1 <sup>3</sup> /4"	(44.4)	1 <sup>1</sup> /4"	(31.7)	1 <sup>1</sup> /8"	(28.6)	3/8"	(19.5)	1 <sup>1</sup> /4"	(31.7)	750	(3.33)	1130	(5.02)	110	(49.9)
68W- <sup>7</sup> /8	<sup>7</sup> /8"-9	1 <sup>3</sup> /4"	(44.4)	1 <sup>1</sup> /4"	(31.7)	1 <sup>1</sup> /8"	(28.6)	<sup>9</sup> /16"	(14.3)	1 <sup>5</sup> /16"	(33.3)	750	(3.33)	1130	(5.02)	98	(44.4)

Note: See page 27 for recommended setscrew torque.

All dimensions in charts and on drawings are in inches. Dimensions shown in parentheses are in millimeters unless otherwise specified.




A (Rod Size) Hanger Rod Not Included

Fig. 68S

Set Screw and Locknut Included

Set Screw and Locknut Included

D = Depth of Throat







### Fig. 65 - Reversible Steel C-Type Beam Clamp <sup>3</sup>/4" (19.0mm) Throat Opening Fig. 65XT - Reversible Steel C-Type Beam Clamp <sup>3</sup>/4" (19.0mm) Throat Opening (bottom of page)

#### Size Range:

Fig. 65 -  $\frac{1}{2}$ "-13 rod sizes, and  $\frac{5}{8}$ "-11 rod sizes Fig. 65XT -  $\frac{3}{8}$ "-16 rod size (see below) TOLCO

Material: Steel with hardened cup point set screw and jam nut

**Function:** Recommended for hanging from steel beam where flange thickness does not exceed 3/4" (19.0mm).

**Features:** All steel construction eliminates structural deficiencies associated with casting type beam clamps. May be used on top or bottom flange of beam. (Beveled lip allows hanging from top flange where clearance is limited.) May be installed with set screw in up or down position. Offset design permits unlimited rod adjustment by allowing the rod to be threaded completely through the clamp. Open design permits inspection of thread engagement.

**Approvals:** Underwriters Laboratories Listed in the USA **(UL)** and Canada **(cUL)**. Exceeds requirements of the National Fire Protection Association (NFPA), pamphlet 13,

<sup>3</sup>/8"-16 rod will support <sup>1</sup>/2" (15mm) thru 4" (100mm) pipe

<sup>1</sup>/2"-13 rod will support <sup>1</sup>/2" (15mm) thru 8" (200mm) pipe

Included in the Seismic Restraints Catalog approved by the State of California Office of Statewide Health Planning and Development **(OSHPD)**. For additional load spacing and placement information relating OSHPD projects, please refer to the Seismic Restraint System Guidelines.

Finish: Plain. Contact B-Line for alternative finishes and materials.

Order By: Part number and finish

Fig. 65 Patent #4,570,885

Part	Rod Size	В		C	C		כ	E		
No.	A	in.	(mm)	in.	(mm)	in.	(mm)	in.	(mm)	
<b>65-</b> 1/2	<sup>1</sup> /2"-13	1 <sup>1</sup> /2"	(38.1)	3/4"	(19.0)	1"	(25.4)	<sup>9</sup> /16"	(14.3)	
<b>65-</b> <sup>5</sup> /8	<sup>5</sup> /8"-11	1 <sup>1</sup> /2"	(38.1)	3/4"	(19.0)	1"	(25.4)	<sup>9</sup> /16"	(14.3)	

Part	F	3	Mac Re	c. Load *	Approx.	Wt./100
No.	in.	(mm)	in.	(mm)	in.	(mm)
<b>65-</b> 1/2	<b>1</b> <sup>1</sup> /4"	(31.7)	1130	(5.02)	55	(24.9)
<b>65-</b> 5/8	1 <sup>1</sup> /4"	(31.7)	1130	(5.02)	55	(24.9)

\* Maximum loads for clamp with set screw in up or down position.

**Note:** See page 27 for recommended setscrew torque.

### Fig. 65XT-<sup>3</sup>/8 - Beam Clamp

**Feature:** Extruded holes allow for more thread engagement of threaded rod and set screw.

Weight: Approx. Wt./100 - 28.0 Lbs. (12.7kg)


Design Load: 730 Lbs (3.25kN)

Finish: Plain or Electro-Galvanized

Order By: Part number and finish


**Approvals:** Underwriters Laboratories Listed and FM Approved for uo to 4" (100mm) pipe.

Note: See page 27 for recommended setscrew torque.



Component of State of California OSHPD Approved Seismic Restraints System





Set Screw and Locknut Included







#### Fig. 66 - Reversible Steel C-Type Beam Clamp 1<sup>1</sup>/4" (31.7mm) Throat Opening

**Size Range:** <sup>3</sup>/<sub>8</sub>"-16, <sup>1</sup>/<sub>2</sub>"-13 rod sizes, and <sup>5</sup>/<sub>8</sub>"-11 rod sizes **Material:** Steel with hardened cup point set screw and jam nut

 $^{3}$ /8"-16 rod will support  $^{1}$ /2" (15mm) thru 4" (100mm) pipe  $^{1}$ /2"-13 rod will support  $^{1}$ /2" (15mm) thru 8" (200mm) pipe

Finish: Plain. Contact B-Line for alternative finishes and materials.

the Seismic Restraint System Guidelines.

thickness does not exceed 11/4" (31.7mm).

inspection of thread engagement.

Order By: Part number and finish

Function: Recommended for hanging from steel beam where flange


**Features:** All steel construction eliminates structural deficiencies associated with casting type beam clamps. May be used on top or bottom flange of beam. (Beveled lip allows hanging from top flange where clearance is limited.) May be installed with

set screw in up or down position. Offset design permits unlimited rod adjustment by allowing the rod to be threaded completely through the clamp. Open design permits

**Approvals:** Underwriters Laboratories Listed in the USA **(UL)** and Canada **(cUL)**. Exceeds requirements of the National Fire Protection Association (NFPA), pamphlet 13,

Included in the Seismic Restraints Catalog approved by the State of California Office of Statewide Health Planning and Development (OSHPD). For additional load spacing and placement information relating OSHPD projects, please refer to

Component of State of California OSHPD Approved Seismic Restraints System





	6	20	
4	N		
	đ	1	

Part	Rod Size	I	3	C	;		D		E
No.	Α	in.	(mm)	in.	(mm)	in.	(mm)	in.	(mm)
<b>66-</b> <sup>3</sup> /8	<sup>3</sup> /8"-16	1 <sup>3</sup> /16"	(30.2)	1 <sup>1</sup> /4"	(31.7)	1"	(25.4)	<sup>7</sup> /16"	(11.1)
<b>66-</b> <sup>1</sup> /2	<sup>1</sup> /2"-13	1 <sup>1</sup> /2"	(38.1)	1 <sup>1</sup> /4"	(31.7)	1"	(25.4)	<sup>9</sup> /16"	(14.3)
<b>66-</b> <sup>5</sup> /8	<sup>5</sup> /8"-11	1 <sup>1</sup> /2"	(38.1)	1 <sup>1</sup> /4"	(31.7)	1"	(25.4)	<sup>9</sup> /16"	(14.3)

Part F		-		c. Load *	Approx. Wt./100		
No.	in.	(mm)	in.	(mm)	in.	(mm)	
<b>66-</b> <sup>3</sup> /8	1"	(25.4)	610	(2.71)	28	(12.7)	
<b>66-</b> 1/2	1 <sup>1</sup> /4"	(31.7)	1130	(5.02)	55	(24.9)	
<b>66-</b> <sup>5</sup> /8	1 <sup>1</sup> /4"	(31.7)	1130	(5.02)	55	(24.9)	

\* Maximum loads for clamp with set screw in up or down position.

Note: See page 27 for recommended setscrew torque.



# Fig. 67SS - Stainless Steel Reversible C-Type Beam Clamp <sup>3</sup>/4" (19.0mm) Throat Opening Fig. 68SS - Stainless Steel Reversible C-Type Beam Clamp Wide Mouth

Size Range: 3/8"-16 and 1/2"-13 rod sizes

Material: Stainless Steel (Type 316 or 304)

**Function:** Recommended for hanging from steel beams where flange thickness does not exceed 3/4" (19.0mm) for Fig. 67SS or  $1^{1}/4$ " (31.7mm) for Fig. 68SS.


**Features:** All steel construction eliminates structural deficiencies associated with casting type beam clamps. May be used on top or bottom flange of beam. May be installed with set screw in up or down position. Offset design permits unlimited rod adjustment by allowing the rod to be threaded completely through the clamp.


**Approvals:** Underwriters Laboratories Listed in the USA **(UL)** and Canada **(cUL)**. Conforms to Manufacturers Standardization Society ANSI/MSS SP-69 & SP-58, Type 19. Meets or exceeds requirements of the National Fire Protection Association (NFPA), pamphlet 13.

<sup>3</sup>/8"-16 rod will support <sup>1</sup>/2" (15mm) thru 4" (100mm) pipe <sup>1</sup>/2"-13 rod will support <sup>1</sup>/2" (15mm) thru 8" (200mm) pipe


Parlan Ban Dat number and stabilized stability of

Order By: Part number and stainless steel type.





TOLCO



## Fig. 67SS

Beam Clamps

Part No.	Rod Size A	Pipe in.	e Size (mm)	l in.	3 (mm)	C in.	; (mm)	C in.	) (mm)	l in.	E (mm)
67SS- <sup>3</sup> /8	<sup>3</sup> /8"-16	<sup>1</sup> /2" - 4"	(15 - 100)	3"	(76,2)	7/8"	(22.2)	1"	(25.4)	1 <sup>5</sup> /8"	(41.3)
67SS-1/2	<sup>1</sup> /2"-13	5" - 8"	(125 -200)	3"	(76,2)	7/8"	(22.2)	1"	(25.4)	1 <sup>5</sup> /8"	(41.3)

Part No.	F in. (mm)		in.	G (mm)	Test in.	Test Load in. (mm)		Approx. Wt./100 in. (mm)		
67SS- <sup>3</sup> /8	1 <sup>5</sup> /8"	(41.3)	1 <sup>1</sup> /8"	(28.6)	1500	(6.67)	84	(38.1)		
67SS-1/2	1 <sup>5</sup> /8"	(41.3)	1 <sup>1</sup> /8"	(28.6)	4050	(18.01)	170	(77.1)		



#### Fig. 68SS

Part	Rod Size	Pipe Size		Rod Size Pipe Size B		C		D		Е	
No.	Α	in.	(mm)	in.	(mm)	in.	(mm)	in.	(mm)	in.	(mm)
68SS- <sup>3</sup> /8	<sup>3</sup> /8"-16	<sup>1</sup> /2" - 4"	(15 - 100)	2 <sup>1</sup> /16"	(52.4)	1 <sup>1</sup> /8"	(28.6)	3/4"	(19.0)	1 <sup>1</sup> /4"	(31.7)
68SS-1/2	<sup>1</sup> /2"-13	5" - 8"	(125 -200)	2 <sup>1</sup> /4"	(57.1)	1 <sup>1</sup> /4"	(31.7)	<sup>13</sup> /16"	(20.6)	1 <sup>1</sup> /4"	(31.7)

Part	F	=	Test	t Load	Approx. Wt./100		
No.	in.	(mm)	in.	(mm)	in.	(mm)	
68SS- <sup>3</sup> /8	2"	(50.8)	1500	(6.67)	84	(38.1)	
68SS-1/2	2 <sup>1</sup> /4"	(57.1)	4050	(18.01)	170	(77.1)	

Note: See page 27 for recommended setscrew torque.



