




**Z9A-E45S**  
**45° ELBOW**  
**THREADED X SPIGOT FOR ACID WASTE**

TAG \_\_\_\_\_

Dimensional Data (inches and [ mm ]) are Subject to Manufacturing Tolerances and Change Without Notice



Dimensions In Inches			
Nominal Pipe Size	C	E	L
1-1/2 [38]	11/16 [22]	1-15/16 [49]	1-3/4 [44]
2 [50]	25/32 [20]	2-1/4 [57]	1-31/32 [50]
3 [76]	1-3/4 [44]	4-5/32 [106]	3-3/4 [95]
4 [102]	2-3/16 [56]	4-13/32 [112]	4-5/16 [110]
6 [152]	2 [51]	4-5/32 [105]	4-5/32 [105]

**ENGINEERING SPECIFICATION:**  
 ASTM-F1412, F.R.P.P.-210 ZURN  
 Z9A-E45S 45° ELBOW  
 THREADED X SPIGOT FLAME  
 RETARDANT POLYPROPYLENE FITTING.

**PIPE SIZE**

1-1/2, 2, 3, 4, 6 [Sch 40 + Sch 80]

(Specify size/type) **CONNECTION**

- \_\_\_\_\_ -M Mechanical joint seal
- \_\_\_\_\_ -F Fusion lock seal

\*REGULARLY FURNISHED UNLESS OTHERWISE SPECIFIED

<b>REV. B</b>	<b>DATE: 11/04/03</b>	<b>C.N.NO. 91573</b>
<b>DWG. NO. 63075</b>	<b>PRODUCT NO. Z9A-E45S</b>	