

# BourdonTube Pressure Gauge Type 111.10, ABS Plastic or Painted Steel Case Standard Series - Lower Mount

WIKA Datasheet APM 111.10

# **Applications**

- Hydraulic and pneumatic systems
- Pumps, compressors, water systems, regulators
- Suitable for fluid medium which does not clog connection port or corrode copper alloy

# **Special features**

- Copper alloy wetted parts
- ABS plastic or painted steel case
- Lower Mount (LM) process connection



**Size** (All sizes not stocked) 1½", 2", 2½" and 4" (40, 50, 63, and 100 mm)

# **Accuracy class**

+ 3/2/3% of span (ASME B40.1 Grade B)

#### **Bourdon Tube**

Material: copper alloy 30"Hg (Vac) to 600 psi C-type 800psi to 6000 psi helical type

#### Movement

Copper Alloy

#### Dial

White plastic with stop pin (1½", 2", 2½") White aluminum with stop pin (4") Black or black and red lettering

# **Pointer**

Black ABS plastic (1½", 2", 2½", 4" LM) (2 and 2½" LM - black aluminum); non-adjustable

#### Case

Black ABS plastic

#### Bezel

None (11/2", 2", 21/2", & 4")



#### **Bourdon Tube Pressure Gauge Type 111.10**

#### Window

Snap-in acrylic (11/2", 2", 21/2", & 4")

## **Standard Scales**

1½" psi, psi/kg/cm²

2" psi, psi/kpa, psi/kg/cm<sup>2</sup>

2½" psi, psi/kpa, psi/kg/cm² 0/100% of linear, 0/10 sq. rt. 4" psi, psi/kpa, psi/kg/cm² 0/100% of linear, 0/10 sq. rt.

#### Ranges (All ranges not stocked)

Vacuum/Compound to 30"Hg / 0/ 200psi

Pressure from 15psi to 6000psi

or other equivalent units of pressure or vacuum

Receiver scales 3...15psi

# **Working Range**

Steady: 3/4 of full scale value Fluctuating: 2/3 of full scale value Short time: full scale value

## **Operating Temperature**

Ambient: -40°F to 140°F (-40°C to 60°C)

Media: max. 140°F (+60°C)

#### Temperature error

Additional error when temperature changes from reference temperature of 68°F (20°C) +0.4% for every 18°F (10°C) rising or falling. Percentage of span.



# **Optional Extras**

- Accuracy + 2/1/2% of span (ASME B40.1 Grade A)
- Slip-fit or friction ring
- Case with blow-out plug
- Glass window
- Black painted steel case
- Stainless steel case
- Brass polished case and friction ring (2½" only)
- Special case colors
- Special connections (limited to wrench flat area)
- Cleaned for oxygen service
- Nickel plated connection
- Medical specification
- Rubber cover (2", 21/2")
- Custom dial layout
- Other pressure scales available: Bar, kPa, MPa, kg/cm<sup>2</sup> and dual scales
- DIN standards
- Red set pointer on aluminum dial or on snap-on window
- External adjust red drag pointer (2½" only) (max. hand)

Note: ¹Press-fit brass restictor standard for 111.10B, 1000psi to 6000psi

# Standard versions Standard versions

Type 111.10

W
12
0.47
14
0.55
14
0.55
14
0.55
(

Type 111.10B (brass case version)

Size									
		Α	B <sup>1</sup>	С	D	E	L	Т	W
2.5"	mm	63	52	27	61.5	9.5	10		14
	in	2.48	2.05	1.06	2.42	0.37	0.39	1/4"	0.55

 $<sup>^{\</sup>rm 1}$  To reduce 1/4" connection to 1/8", subtract 0.08 in. (2 mm) from  ${\bf B}$  dimension

Page 2 of 2

WIKA Datasheet APM 111.10 · 02/2005

#### Ordering information

Pressure gauge model / Nominal size / Scale range / Size of connection / Optional extras required Specifications and dimensions given in this leaflet represent the state of engineering at the time of printing. Modifications may take place and materials specified may be replaced by others without prior notice.



WIKA Instrument Corporation

1000 Wiegand Boulevard Lawrenceville, GA 30043 1-888-WIKA-USA /770-513-8200 (in GA) Fax 770-338-5118 info@wika.com www.wika.com