# 100E-400E, 600E, 1000E & 1600E

ELECTRIC ACTUATORS



## ELECTRIC QUARTER-TURN ACTUATORS

FNW offers electric actuators for quarter-turn valves such as ball, plug and butterfly valves. Actuators can be supplied with numerous options, including, but not limited to, electro-mechanical brakes (200E and larger), auxiliary position switches, feedback potentiometers, 4-20mA and 0-10Vdc positioners, alternate motor voltages, spring return action, and explosion-proof housings. Contact FNW with your specific application needs.

### FEATURES

#### 100E, 200E, 300E, & 400E

- -40°F to 150° temperature range (Optional heater required below 0°F)
- CSA certified NEMA 4 enclosure
- Single 1/2" NPT conduit entry
- 300 Series stainless steel output drive
- 300 Series stainless steel captive enclosure fasteners
- ISO standard bolting and drive dimensions
- Friction brake standard
- Non-declutching manual override (400E has declutching manual override hand wheel)
- Dome position indicator
- Permanently lubricated
- Mountable in any position
- Thermally bonded polyester powder coated

# FEATURES

#### 600E, 1000E, & 1600E

- -40°F (with standard heater activated) to 140° temperature range
- CSA certified enclosure conforms to NEMA 1, 2, 3, 3R, 4, 4X and 12
- Motor thermal overload protection
- Dual 1/2" NPT conduit entries
- Heater & thermostat
- Hardened steel spur gear and output drive
- Captive hex head enclosure fasteners
- ISO standard bolting and drive dimensions
- Declutching manual override with indicator
- Permanently lubricated
- Mountable in any position
- Polyester coated



	Standared Specifications	Model Number						
		100E	200E	300E	400E	600E	1000E	1600E
	Output Torque (in-Ibs)	100	200	300	400	600	1000	1600
	Cycle Time (Seconds)	2.5	5	5	10	15	15	30
	Duty Cycle (120VAC)	25%	25%	25%	25%	30%	100%	100%
	Lock Rotor Current (Amps)	0.55A	0.75A	0.99A	0.75A	0.57A	0.69A	0.35A
	Weight (lbs)	6	10	10	18	18	18	18



We reserve the right to modify or improve the designs or specifications of our products at any time without notice.



# **100E-400E, 600E, 1000E & 1600E** ELECTRIC ACTUATORS



### ELECTRIC QUARTER-TURN ACTUATORS

#### Model 100E Dimensions DOMEINDICATOR 0.25 0.91 MANUAL OVERRIDE ALLOW 2.5" CLEARANCE FOR COVER REMOVAL 1/2-14 NPT 4.72 1.31 1.47 2.39 2.87 5.75 0 à Ø 1.97 B.C 1/4-20 x 0.44 (deep) (x4) 4.13 Ø 1.42 B.C 10-24 x 0.44 (deep) (x4) $^{\circ}$ 0.43 (0.39 deep) DOMEINDICATOR 1 0.375 Model 200E & 0.91 MANUAL **300E** Dimensions ALLOW 3" CLEARANCE FOR COVER REMOVAL 5.39 1/2-14 NPT 2.43 1.00 6.88 2.88 Ø Ø 1.42 B.C. Ø 5/16-18 x 0.5 (deep) (x4) 0

Ø 1.97 B.C

Ø 2.76 B.C.

6

Ø

o

୍ଚି

4.25

Ø 1/4-20 x 0.44 (deep) (x4)


Ø 10-24 x 0.44 (deep) (x4)

1.75




### ELECTRIC QUARTER-TURN ACTUATORS

#### **Model 400E Dimensions**



#### Model 600E to 1600E Dimensions



# 100E-400E, 600E, 1000E & 1600E ELECTRIC ACTUATORS



### ELECTRIC QUARTER-TURN ACTUATORS

#### Model 100E to 400E **Standard Wiring Diagram**

Model 600E to 1600E

