



## ONE-LOK™ MODEL SLDEH WEDGE HARNESS RESTRAINT FOR DUCTILE IRON PIPE







## **PRODUCT SPECIFICATIONS**

MATERIAL:

• Gland body, wedge inserts, break-off top actuating bolts and split back-up ring are

manufactured of high strength ductile iron in accordance with ASTM A536, Grade 65-45-12.

Wedge inserts are heat-treated to a hardness of 370 BHN minimum.

**SIZE RANGE:** • 3" through 36"

**DIMENSION:** • Conform to ANSI/AWWA C151/A21.51 standard

PRESSURE RATINGS: • Sizes 3"-16" carry a 350 psi WWP and sizes 18"-36" carry a 250 psi WWP while

providing a minimum 2:1 factor of safety.

**COATING:** • Asphaltic black enamel

• Electro-deposition "CORRSAFE™" available upon request. For further information-

please refer to our CORRSAFE Product Information sheet at http://www.sigmaco.

com/pipe-restraint-product coatings-linings/

**APPROVALS:** • Wedge glands are Underwriters Laboratories' Listed in sizes 3" – 36" and Factory

Mutual approved in sizes 3" - 12". Split glands are Underwriters Laboratories' List-

ed & Factory Mutual approved in sizes 3"-16".

**DEFLECTION:** • 5° for 3"-12", 2° for 14"-16", 1-1/2° for 18"-24" and 1° for 30"-36"

**TRACEABILITY:** • Gland body, wedge inserts, break-off top actuating bolts and split back-up ring are

individually cast with exact heat code information.

**INSTALLATION:** • In accordance with manufacturer's recommendation and applicable AWWA stan-

dards.

