

For Residential and Commercial Applications

Job Name		Engineer / Architect	
Job Location		Wholesaler	
Submittal Date		Contractor	

V8-**A Speedi Plumb® Vinyl Faucet Connectors - Female Iron Pipe Inlet

Use: For use in potable water distribution systems in accessible locations only

Design Features:

- **No kink hose.** The specially engineered reinforced PVC hose provides unique flexibility to prevent kinking and crimping
- **Greater strength and durability** with a tighter weave and two-layer bonded construction, outperforms conventional vinyl connectors
- **Longer wing nuts** ease installation for speedier connections
- **Nitrile rubber washers** provide a large pliable sealing surface and ensures a long lasting water tight connection
- **8-sided pneumatic crimp** provides greater dependability for realible nut-to-hose connections
- **100% Compliant** to California and Vermont "low-lead" requirements



Operating Specifications:

Temperature: 40° - 140° F, intermittent to 180° F

Pressure: 125 psi maximum

Tubing Diameter: 0.300" I.D. (0.500" O.D.)




MATERIAL SPECIFICATIONS

Hose	PVC with polyester braid reinforcement
Barb	Compliant brass
Ferrule	Zinc plated 1008 steel
Nut	Polypropylene or C36000 brass, chrome plated*
Washer	Nitrile rubber
F.I.P. Nut	C36000 bras, chrome plated

* Where Specified

Part Listing:

<input type="checkbox"/>	V8-12A F	1/2" F.I.P. x 1/2" F.I.P. x 12" length
<input type="checkbox"/>	V8-12AM F	1/2" F.I.P. x 1/2" F.I.P. metal nut x 12" length
<input type="checkbox"/>	V8-16A F	1/2" F.I.P. x 1/2" F.I.P. x 16" length
<input type="checkbox"/>	V8-16AM F	1/2" F.I.P. x 1/2" F.I.P. metal nut x 16" length




This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

BrassCraft®

V8-**A Speedi Plumb® Vinyl Faucet Connectors - Female Iron Pipe Inlet

Part Listing (con't):

- | | | |
|--------------------------|-----------|--|
| <input type="checkbox"/> | V8-20A F | 1/2" F.I.P. x 1/2" F.I.P. x 20" length |
| <input type="checkbox"/> | V8-20AM F | 1/2" F.I.P. x 1/2" F.I.P. metal nut x 20" length |
| <input type="checkbox"/> | V8-36A F | 1/2" F.I.P. x 1/2" F.I.P. x 36" length |
| <input type="checkbox"/> | V8-36AM F | 1/2" F.I.P. x 1/2" F.I.P. metal nut x 36" length |



PART DIMENSIONS (Inches)	
Model	DIM. A
V8-12A	12.00 / 13.00
V8-12AM	12.00 / 13.00
V8-16A	16.00 / 17.00
V8-16AM	16.00 / 17.00

PART DIMENSIONS (Inches)	
Model	DIM. A
V8-20A	20.00 / 21.00
V8-20AM	20.00 / 21.00
V8-36A	36.00 / 37.00
V8-36AM	36.00 / 37.00

Listings & Certifications:

- IAPMO listed to ASME A112.18.6-2003 (File # 0452)
- CSA listed to ASME A112.18.6-2003 / CSA B125 (File # 204593)
- CSA approved to California Health & Safety Code 116875 and Vermont Bill S.152 (Project # 2174785)



This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

BrassCraft®