

# 36" Gas Cooktop

The patented dual-stacked burner design of Wolf gas cooktops uses its upper-level burner for maximum heat transfer. Merely turn down the knob and the lower-tier burners delivers fine-tuning control and true simmer. The sealed burners and deep recess of the seamless drawn pan make clean up a snap. Wolf gas cooktops are available in natural or LP gas.



## **FEATURES**

- Stainless steel top construction.
- Five dual-stacked, sealed burners with automatic reignition on all settings.
- One large 15,000 Btu sealed burner with 950 Btu delivered at simmer.
- One medium 12,000 Btu sealed burner with 950 Btu delivered at simmer.
- Three small 9,200 Btu sealed burners with 300 Btu delivered at simmer.
- Individual spark ignition system.
- True simmer setting on all burners.
- Illuminated control panel with two-tiered control knobs.
- Low-profile cast iron continuous burner grates with matte porcelain finish.
- Seamless drawn burner pan.

### **ACCESSORIES**

- Filler strip for installation of multiple cooktops or modules.
- One-piece wok grate and single burner grate.

Accessories are available through your authorized Wolf dealer. For local dealer information, visit the find a showroom section of our website, wolfappliance.com.



Model CT36G/S

This appliance is certified by Star-K to meet strict religious regulations in conjunction with specific instructions found on www.star-k.org.

## **DUAL-STACKED BURNERS**








Full-flame setting.



## 36" Gas Cooktop

## **OVERALL DIMENSIONS**



Unit dimensions may vary by  $\pm 1/8$ ".

### **SPECIFICATIONS**

Overall Width	36"
Overall Height	4"
Overall Depth	21"

**Burner Rating** 

- (1) 15,000 Btu with 950 Btu delivered at simmer
- (1) 12,000 Btu with 950 Btu delivered at simmer
- (3) 9,200 Btu with 300 Btu delivered at simmer

Countertop Cut-Out Width 35"

Countertop Cut-Out Depth 19<sup>1</sup>/<sub>4</sub>"

Electrical Requirements 120 V AC, 60 Hz 15 amp circuit

Power Cord 6' cord with grounded plug Gas Rating 54,600 Btu

67 lbs

# **INSTALLATION NOTES**


Shipping Weight

A Wolf 36" built-in single oven may be installed below the 36" gas cooktop. Refer to specifications for built-in ovens.

For LP gas installations above 8,600' a high altitude conversion kit is required. For natural gas installations above 10,250', contact your authorized Wolf dealer.

Complete installation specifications can be found on our website, wolfappliance.com.


### INSTALLATION SPECIFICATIONS



\*Minimum clearance from cooktop cut-out to combustible materials up to 18" (457) above countertop.

NOTE: Gas and electrical location applies only to installation with built-in oven.

## Countertop Cut-Out Dimensions



Dimensions in parentheses are in millimeters unless otherwise specified.