

<image><image><image><image><image><image><image><image><image><image><image><image><image><image><image><image><image><image><image><image><image><image>

Hose & Supply Boxes 8120 Series Hose Valves

Hose Valves

Acorn Hose Valves are recommended for installation in interior and exterior locations not subject to freezing. Hose valves have heavy rough brass body with machined brass vandal-resistant lock shield bonnet and are furnished with a removable wheel handle. Valves close with the pressure and feature a replaceable cartridge which contains all wearing parts including the seat. Inlet is 3/4" NPT female. Outlet is 3/4" male hose thread. Vacuum breaker models prevent contamination of potable water supply. Vacuum breakers are atmospheric type and conform to the requirements of ASSE Standard 1011. Check local code authority for vacuum breaker requirements.

-SSLF Stainless Steel Lead Free machined, cast stainless steel body with a rough finish and meets lead free requirements where the wetted surface of this product contacted by water contains less than 0.25% lead. Optionally available with models 8120 and 8121 only.

Installation. 8120 and 8121 models have flanges and are used for installation on walls of buildings. 8125, 8126, 8130 and 8131 models are normally installed on supply pipes 6" to 36" high. 8135 and 8136 models are installed flush with surface in planter boxes, etc.

GUIDE SPECIFICATION

Provide and install Acorn Hose Valves model (specify model number) cartridge-operated hose valve with lock shield bonnet and removable key handle. Interior wall hose valves shall be polished chrome finish. Exterior valves shall be rough chrome-plated.

Page 1 H.8120

Revised: 06/17/11

Hose & Supply Boxes 8120: Hose Valves

BASE MODEL NUMBER (Must Specify)

HOSE VALVE

BENT NOSE WITH FLANGE			
8120	Less Vacuum Breaker		
8120-SSLF	Stainless Steel Lead Free, Less Vacuum		
	Breaker		
8121	With Vacuum Breaker		
3121-SSLF	Stainless Steel lead Free, With Vacuum Breaker		

BENT NOSE

□ 8125 Less Vacuum Breaker□ 8126 With Vacuum Breaker

STRAIGHT NOSE

🗋 8130	Less Vacuum Breaker			
🗋 8131	With Vacuum Breaker			


INVERTED NOSE

1 8135	Less Va	cuum	Breaker


8136 With Vacuum Breaker




- □ CP Chrome-Plated Polished,
 - (N/A with optional -SSLF Stainless Steel Lead Free)
- CR Chrome-Plated Rough, (N/A with Optional -SSLF Stainless Steel Lead Free)



SCALE 2X



Please visit www.acorneng.com





1


 $2\frac{1}{4}$


(57)

8131











3. Vacuum Breaker.

Important: Installation instructions and current rough-in are furnished with each fixture. Do not rough in without certified dimensions. Dimensions are subject to manufacturer's tolerance of plus or minus 1/4" and change without notice. Acom assumes no responsibility for use of void or superseded data. © Copyright 2008 Acom Engineering Company					
Selection Summary	Approved for Manufacturing				
Model No. & Option	CompanyTitle				
Quantity	Signature Date				
Page 2 H	.8120 Revised: 06/17/11				

Acorn Engineering Company • 15125 Proctor Avenue • P.O. Box 3527 • City of Industry, CA 91744-0527 U.S.A. Tel: (800) 488-8999 • (626) 336-4561 • Fax: (626) 961-2200 • www.acorneng.com • E-mail: info@acorneng.com





MODELS: 8130

NOTES:

- 1. Removable Wheel Loose Key Handle.
- 2. Hose Connection.