

Fasteners and Flange Gasket Sets for the Water, Gas and Municipal Industries.

Benefits

- Factory applied protection, no need to pack and wrap joints and fittings after installation
- All bolts, nuts and washers are fully coated, no exposed or unprotected metal areas
- Exceptional long-term corrosion protection
- Meets the standards of WIS 4:52:03
- Flange gasket sets provide the gasket and correct quantity and size of bolts, nuts and washers for each application ensuring correct fitment every time
- Extensive stocks of standard Flange Bolt Sets are available providing short lead times and high levels of customer service
- Non-standard materials, coatings and sizes are available on request





Technical help

For further technical data, product specifications and general information please contact our Customer Service Department at the telephone number shown below.



The UPE range of flange bolt sets is extensive and can be tailored to suit customers' exact needs.

UPE offer complete flange gasket sets consisting of a gasket and the appropriate number of fasteners for the size of flange. These flange gasket sets are supplied bagged and clearly labelled enabling the correct gasket with the correct size and number of bolts, nuts and washers to be selected every time a connection is to be made.



Technical data

Material

Bolts: Mild steel, grade 4.6 Nuts: Mild steel, grade 4.6 Washers: Mild steel, grade 4.6

Alternative grades and materials are available on request

Gaskets

Water: EPDM EN681 Gas: Nitrile EN682

For pressures exceeding NP25 a 'ceramic' gasket can be supplied. Please contact the UPE Customer Service Team on the number shown below for further details

Coating: Sheraplex

Sheraplex is a duplex process -

Stage 1: Sherardized layer (Average coating to 30µm)

Stage 2: Inorganic barrier layer (Average coating to 12µm)

Combined: Sheraplex coating (Average coating to 42µm)

Sizes

Bolts: M10 to M56

In lengths 25mm to 300mm

Gaskets: Full face, 2 lug and IBC In sizes 50mm to 2,200mm

Safety

As with all industrial products it is important to take adequate safety precautions such as the use of adequate protective clothing like gloves, overalls, eye protection and safety footwear during installation, use and maintenance of this product.

Tel: +44 (0)1675 437 900 e-mail: wwinfo@tyco-valves.com

General application

The UPE range of fasteners have been developed to meet the requirements of the water, gas and municipal industries.

The protective coating offers all the benefits of a combination of a substantial sacrificial protection layer and a barrier layer. Both these layers combine to withstand exposure to the most extreme of environments.

Fasteners

Bolts, nuts and washers are supplied in steel to grade 4.6 as standard with the option of alternative grades and materials available on request. The duplex coating process consists of a Sherardized layer to an average thickness of 30µm and a subsequent Inorganic barrier to a thickness of 12µm. This approved coating meets the requirement of WIS 4-52-03.

Gaskets

UPE offer three types of gasket pattern:

Full Face,
 2 Lug,
 IBC

Other special gaskets can be supplied to exact customer requirements.

All gaskets are supplied in either EPDM or Nitrile rubber to a thickness of 3mm and are available as BS4504 (closed bore) and BS4865 (open bore). All EPDM gaskets supplied are fully WRAS approved for contact with potable water and conform to the requirements of BS2494.

Fax: +44 (0)1675 437 909 www.tycowaterworks.com

2

Sheraplex



Benefits

- Long term environmental protection
- Minimum 1000 hours salt spray test to ASTMB117
- Repeatable torque tension control to BS7371 part 2
- Uniform diffusion zinc/iron alloy coating plus organic barrier layer, useful for protecting irregularly shaped components
- Substrate has a high degree of wear resistance to withstand abrasion and handling
- No hydrogen embrittlement

The Sheraplex process is a duplex one. It utilises the excellent sacrificial corrosion protection of the Sherardizing process combined with a final, external coating in the form of an inorganic barrier layer. The characteristic matt textured surface of the Sherardizing process also provides an excellent key to the organic barrier layer, so enhancing the performance of both processes.

The first stage in the Sheraplex process is Sherardizing. This is a diffusion process where the items to be coated are heated in the presence of Zinc Dust. The process is normally carried out in a slowly rotating container at temperatures ranging from 320°C to 500°C. The resulting zinc/iron alloy coating is then zinc phosphated. This provides a clean, passivated, matt grey coating which closely follows the contours of the base material, giving a uniform coating on even the most intricatly shaped items.

The second stage of the process is the application of an organic barrier layer. This second layer is applied by either a dip/spin or a spray process, the coating is then cured at 200°C. This gives a uniform and complete coverage of coating, allowing the intricate shape of the bolt threads to be fully coated.



Range

The UPE range of stocked Flange Gasket Sets comprise of an EPDM gasket supplied with the correct number of bolts, nuts and washers (2 washers per bolt) Nuts, bolts and washers are Sheraplex coated to WIS 4-52-03

Stocked PN 16 Flange Gasket Sets											
Nominal pipe size	OD of Flange	Bolt Hole Details			Bolt Size		(Usin	Spanner Size Across flats			
	(mm)	PCD (mm)	Number	Dia. (mm)	Dia.	Length (mm)	at10 bar	at 16 bar	at 20 bar*	at 25 bar*	(mm)
DN 50	165	125	4	19	M16	70 or 90	70	70	75	75	24
DN 80	200	160	8	19	M16	70 or 90	70	70	75	75	24
DN 100	220	180	8	19	M16	70 or 90	75	80	80	80	24
DN 150	285	240	8	23	M20	70 or 100	115	120	125	135	30
DN 200	340	295	12	23	M20	70 or 100	110	115	120	130	30
DN 250	400	355	12	28	M24	90 or 110	155	165	175	180	36
DN 300	455	410	12	28	M24	90 or 110	165	180	190	210	36
DN 350	520	470	16	28	M24	90 or 110	160	175	185	200	36
DN 400	580	525	16	31	M27	110	200	220	235	270	41
DN 450	640	585	20	31	M27	110	195	215	230	260	41
DN 500	715	650	20	34	M30	110	240	270	295	345	46
DN 600	840	770	20	37	M33	120	305	365	425	505	50

Notes

- The need to seal flanged gasket sets at pressures greater than the flange PN rating will only arise for the purposes of on site hydrostatic testing. Flanged gasket sets should not be operated at these higher values other than for such testing
- Bolt lengths are approximate
- Details relate to connecting ductile Iron flanges using 3mm gaskets

Fasteners for Water and Gas Pipe Fittings

Fasteners and Flange Gasket Sets

Flange Tables to EN 1515-1

The following information concerning pressure ratings relates to temperatures between -10 and +100 $^{\circ}\text{C}.$

The following information should act as a general guideline only. For full information relating to this and additional flange data, please refer to the UPE Customer Service team on the number shown on the reverse of this data sheet.

PN 6 and PN 10 Flange Tables														
Nominal Bore (mm)	PN 6							PN 10						
	Flange Dimensions (mm)				Bolt Dims.		Fla	nge Dime	Bolt Dims.					
	Dia. (mm)	Thick (mm)	PCD (mm)	No. of holes	Dia.	Length (mm)	Dia. (mm)	Thick (mm)	PCD (mm)	No of holes	Dia.	Length (mm)		
40	130	16	100	4	M12	55	150	16	110	4	M16	55		
50	140	16	110	4	M12	55	165	18	125	4	M16	65		
65	160	16	130	4	M12	55	185	18	145	4	M16	65		
80	190	16	150	4	M16	65	200	20	160	8	M16	70		
100	210	18	170	4	M16	65	220	20	180	8	M16	70		
125	240	20	200	8	M16	70	250	22	210	8	M16	70		
150	265	20	225	8	M16	70	285	22	240	8	M20	70		
175	-	-	-	-	-	-	315	24	270	8	M20	75		
200	320	22	280	8	M16	70	340	24	295	8	M20	75		
250	375	24	335	12	M16	70	395	26	350	12	M20	80		
300	440	24	395	12	M20	70	445	26	400	12	M20	80		
350	490	26	445	12	M20	80	505	28	460	16	M20	80		
400	540	28	495	16	M20	80	565	32	515	16	M24	90		
450	595	30	550	16	M20	90	615	36	565	20	M24	105		
500	645	30	600	20	M20	90	670	38	620	20	M24	105		
600	755	32	705	20	M24	90	780	42	725	20	M27	120		


PN 16 and PN 25 Flange Tables														
Nominal Bore (mm)	PN 16							PN 25						
	Flange Dimensions (mm)				Bolt Dims.		Fla	nge Dime	Bolt Dims.					
	Dia. (mm)	Thick (mm)	PCD (mm)	No. of holes	Dia.	Length (mm)	Dia. (mm)	Thick (mm)	PCD (mm)	No of holes	Dia.	Length (mm)		
40	150	16	110	4	M16	55	150	20	110	4	M16	70		
50	165	18	125	4	M16	65	165	20	125	4	M16	70		
65	185	22	145	8	M16	65	185	22	145	8	M16	70		
80	200	20	160	8	M16	70	200	24	160	8	M16	75		
100	220	20	180	8	M16	70	235	26	190	8	M20	80		
125	250	22	210	8	M16	70	270	28	220	8	M24	80		
150	285	22	240	8	M20	70	300	30	250	8	M24	90		
175	315	24	270	8	M20	75	330	28	280	12	M24	80		
200	340	24	295	12	M20	75	360	30	310	12	M24	90		
250	405	26	355	12	M24	80	425	40	370	12	M27	90		
300	460	28	410	12	M24	80	485	38	430	16	M27	110		
350	520	32	470	16	M24	90	555	42	490	16	M30	125		
400	580	36	525	16	M27	100	620	46	550	16	M33	140		
450	640	40	585	20	M27	120	670	52	600	20	M33	140		
500	715	44	650	20	M30	125	730	58	660	20	M33	155		
600	840	52	770	20	M33	140	845	66	770	20	M36	165		



Bolt Tightening Sequence

When assembling flanges follow the recommended numbered sequence set out below.

Once fully assembled the flange bolts should be fully tightened to the required torque setting suited to operating pressure and temperature conditions, again following the recommended numbered sequence set out below.



4

Associated Products









Tyco Waterworks
Edison Road
Hams Hall Distribution Park
Coleshill, Birmingham
B46 1AB United Kingdom
Telephone: +44 (0)1675 437 900
Facsimile: +44 (0)1675 437 909

e-mail: wwinfo@tyco-valves.com web: www.tycowaterworks.com

UPE Underpressure Tees offer the customer a robust and flexible means of taking flanged connections of between 80mm and 1200mm diameter off water and gas mains.

The universal tolerance and elastomeric seals ensure a leak free connection on all rigid pipe materials within the stated tolerance, including Ductile Iron, Cast Iron, Steel and uPVC.

The UPE Universal and Engineered range of couplings and flange adaptors can be used for almost any plane-ended rigid pipe material from 40_{mm} to 2,200_{mm} pipe nominals. This flexibility combined with each fittings ability to accommodate a wide variety of pipe sizes makes the UPE Universal fitting a versatile and economical product to use.

A full range of automatic control valves are available from Tyco Waterworks. Within this collection is the HydroStab range of Control Valves. The HydroStab valve can be supplied in the form of a pressure reducing valve, a pressure regulating valve or a pressure sustaining valve depending on customer requirements.

These valves are coated on both internal and external surfaces with epoxy to a thickness of 150 microns and provide many years of trouble free use and operation.

The soft sealing gate valve from Tyco Waterworks is a high performance and reliable valve for water distribution networks manufactured to BS 5163. The valve is fully coated on both internal and external surfaces with epoxy to a thickness of 150 microns and will provide many years of trouble free use and operation.



The UPE Converter Slide Valve is an effective, full bore construction valve, that will allow underpressure drilling operations to be performed on pressures up to 10 bar.

The UPE Slide Valve flanges are to BS4504, NP16 and each one is supplied complete with studs, nuts and washers. Stud length can be specified, either long for use with PE stud flanges or short for standard metal flanges. Please state needs when ordering.