

For Residential and Commercial Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

Series 3005A

Dielectric Unions

Sizes: 1/2" – 3/4" (15 – 20mm)

Series 3005A Dielectric Unions feature a male iron pipe thread to solder connection. These unions are designed to be installed between pipe made from dissimilar metals to prevent accelerated corrosion and deterioration in the piping system due to galvanic and stray current.

Features

- Male iron pipe thread to solder connection
- Designed and manufactured to the highest quality standards
- Individually factory certified to withstand a minimum of 600 volts on a dry line with no flashover
- Rated to 180°F (82°C) at 250psi (17.2 bar)

Specifications


A dielectric union shall be installed where indicated on the plans. The union shall feature a male iron pipe thread to solder connection. The union shall be a Watts Regulator Company Series 3005A.

Materials

Gray Iron	ASTM A48-83
Malleable Iron Parts	ASTM A-197-79
Steel Parts	ASTM A108
Brass Parts	ASTM B-16
Bronze Parts	ASTM B-584
Zinc Parts	ASTM B633-85
Standard Gasket A	Buna-N
Optional Gasket B	EPDM

Options

GB - Optional EPDM gasket for use in steam or hot water applications up to 300°F (149°C) at 50psi (3.4 bar).



3005A

Standards


Meet federal specifications for tensile strength and thread end connections

Pressure — Temperature

Maximum Pressure: 250psi (17.2 bar)

Maximum Temperature: 180°F (82°C)

Dimensions — Weights



SIZE (DN)		DIMENSIONS				WEIGHT	
		A		B			
in.	mm	in.	mm	in.	mm	oz.	gm.
1/2	15	1 1/2	38	2 5/8	67	13.3	377
3/4	20	1 5/8	41	3	76	8.6	244

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: 815 Chestnut St., No. Andover, MA 01845-6098; www.watts.com
Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; www.wattscanada.ca

ES-3005A 0805



Water Safety & Flow Control Products