

Three-way Brass Valve

1/4" IPS UL/ULC Listed*
300 psi



Description

The 1/4" IPS three-way female threaded valve is used to facilitate the installation of sprinkler system pressure gauges. The valve provides for one inlet and two outlets. This design allows for replacement of the system gauge without shutting down the water supply to the sprinkler system. This design also allows Authority's Having Jurisdiction to test system pressure with an additional gauge through the second outlet. (The second outlet is normally plugged during installation with a 1/4" IPS pipe plug.)

Installation

Installation of the three-way valve can be accomplished with normal field installation tools. Make sure the valve is installed according to the flow indication arrow that has been cast into the valve body. The most common installation allows for a 1/4" IPS nipple between the valve and the water supply being measured. This assures there will be adequate spacing for the sprinkler system gauge from the riser. Use either PTFE Pipe

Thread Sealing Tape or a suitable pipe thread sealant such as **PipeFit® Thread Sealant Paste with PTFE** when installing the valve. **DO NOT OVERTIGHTEN THREADS. OVERTIGHTENING MAY CAUSE VALVE FAILURE.**

*UL/ULC Listed 2R97

Specifications

Materials:

Seat - Brass
Body - Brass
Handwheel - Iron

Sizes:

1/4" IPS

Working Pressure:

400 WOG