


**Z505****12-1/4 [311] HEAVY DUTY DRAIN****SPECIFICATION SHEET****TAG** _____

Dimensional Data (inches and [mm]) are Subject to Manufacturing Tolerances and Change Without Notice



A Pipe Size In.[mm]	Approx. Wt. Lbs.[kg]	Grate Open Area Sq. In. [cm ²]
2,3,4,6 [51,76,102,152]	38 [17]	30 [194]
8 [203]	40 [18]	

ENGINEERING SPECIFICATION: ZURN Z505

12-1/4" [311mm] Diameter top drain. Dura-Coated cast iron body with bottom outlet, seepage pan and combination membrane flashing clamp and frame for heavy duty deep flange slotted grate.

OPTIONS (Check/specify appropriate options)**PIPE SIZE**

3,4,6 [76,102,152]
3,4,6 [76,102,152]
2,3,4,6,8 [51,76,102,152,203]
2,3,4,6,8 [51,76,102,152,203]
2,3,4 [51,76,102]

(Specify size/type) OUTLET

_____ IC Inside Caulk
_____ IG Inside Gasket
_____ IP Threaded
_____ NH No-Hub
_____ NL Neo-Loc

'E' BODY HT. DIM.

5-1/4 [133]
5-1/4 [133]
3-3/4 [95]
5-1/4 [133]
4-5/8 [117]

PREFIXES

_____ Z D.C.C.I. Body and Top*
_____ ZB D.C.C.I. Body with Polished Bronze Top (Add 3/16 [5] to 2 [51] Dim. and 3/4 [20] to 12-1/4 [311] Dim.)
_____ ZN D.C.C.I. Body with Polished Nickel Bronze Top (Add 3/16 [5] to 2 [51] Dim. and 3/4 [20] to 12-1/4 [311] Dim.)

SUFFIXES

_____ -AR Acid Resisting Epoxy Coated Cast Iron
_____ -D Dome Grate
_____ -DG Duresist Grate
_____ -F Extension Frame
(Specify Total Height Req'd.)
_____ -G Galvanized Cast Iron
_____ -HP Heel-Proof Grate
_____ -HT Square Hinged Grate
_____ -P Trap Primer Connection
_____ -S Secondary Strainer
_____ -SA Stabilizer Assembly (See Z1036)
_____ -SC Solid Cover
_____ -SS Stainless Mesh Liner for Bucket
_____ -T Square Top
_____ -TC Neo-Loc Test Cap Gasket
(2,3,4 [51,76,102] NL Bottom Outlet Only)
_____ -TS Top Secured with Slotted Screws
_____ -V Backwater Valve (See Z1099)
_____ -VP Vandal-Proof Secured Top
_____ -Y Sediment Bucket
_____ -90 90° Threaded Side Outlet Body
(2,3,4,6 [51,76,102,152] Only)

* Regularly furnished unless otherwise specified.