# For Residential and Commercial Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative
	SKII

# High BTU Stainless Steel Gas Connectors

The high BTU gas connector connector was specifically designed for applications with a significant BTU requirement.

#### **Features**

- Tubing Annealed, 304 stainless steel (ASTM A240)
- Flare nuts: Brass or plated steel
- Adapters: Brass or plated steel
- Optional coating Heavy-duty, antimicrobial, hot-dipped gray PVC (41, 51 & 61 series). Coating will not hold a flame.
- Approved for indoor/outdoor use with stationary gas appliances/equipment.
- Operating temperature with adapters: -40°F to 150°F
- 100% leak tested
- Exclusive No-Neck® design increases flexibility
- More corrugations per inch increase flexibility and extend service life
- When installing a new appliance or when an existing appliance is moved to a new location a NEW gas connector must be per manufacturer's installation instructions and product standards.
- Designed for occasional movement after installation. Repeated bending, flexing or extreme vibration must be avoided. Normal operation of a clothes dryer, rooftop HVAC unit or SIMILAR OUTDOOR APPLIANCE DOES NOT constitute extreme vibration or movement.
- Eliminates the need for pipe nipples, 90's and elbows.
- Pre-fabricated gas connector means no field threading, cutting or assembly of CSST fitting and tubing.
- Available with hot-dipped PVC coating with antimicrobial agent, SafetyShield yellow coating (40C Series), or Stainless Steel.







**40C Series**Yellow Coated
Stainless Steel
Gas Connector



**41, 51 & 61 Series**Gray PVC Coated
Stainless Steel
Gas Connector







# **Certifications and Approvals**

- ANSI Z21.24/CSA 6.10 Connectors for Gas Appliances
- ANSI Z21.75/CSA 6.27 Connectors for Outdoor Appliances and Manufactured Homes
- City of New York MEA #376-92-M
- Approved by the Commonwealth of Massachusetts Board of State Examiners of Plumbers and Gas Fitters – connector length may not exceed 48".

#### WARNING

All installations must completely comply with all Dormont manufacturing company warnings and instructions, national, state and local codes and all applicable ansi standards.

Dormont product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Dormont Technical Service. Dormont reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Dormont products previously or subsequently sold. Refer to the owner's manual for warranty information.



## Minimun Flow Capacity

Connector Minimum Flow Capacity – **For Natural Gas** (per ANSI Z21.24/CSA 6.10 & ANSI Z21.75/CSA 6.27) Straight Length Capacity – BTU per Hr 0.64 SG., 1000 BTU per Cu. Ft. at 0.5 inch Water Column Pressure Drop

CONFIGURATION			CONNECTOR LENGTH [INCHES]							
SERIES	Nominal OD	Nominal ID	12	18	24	30	36	48	60	72
	in	in	in	in	in	in	in	in	in	in
40/41/40C	1	3/4	349,000	318,500	290,900	270,500	255,900	215,000	197,400	173,900
50/51	1-1/4	1	698,000	637,000	581,800	545,200	515,900	442,700	398,900	347,800
60/61	1-1/2	1-1/4	1,204,000	1,139,000	1,075,000	1,010,500	946,000	817,500	725,500	634,000

Connector Minimum Flow Capacity – **For LP Gas** (per ANSI Z21.24/CSA 6.10 & ANSI Z21.75/CSA 6.27) Straight Length Capacity – BTU per Hr 1.55 SG., 2500 BTU per Cu. Ft. at 0.5 inch Water Column Pressure Drop

CONFIGURATION			CONNECTOR LENGTH [INCHES]							
SERIES	Nominal OD	Nominal ID	12	18	24	30	36	48	60	72
	in	in	in	in	in	in	in	in	in	in
40/41/40C	1	3/4	558,400	509,600	465,440	432,800	409,440	344,000	315,840	278,240
50/51	1-1/4	1	1,116,000	1,019,200	930,880	872,320	825,440	708,320	638,240	556,480
60/61	1-1/2	1-1/4	1,926,400	1,822,400	1,720,000	1,616,800	1,513,600	1,308,000	1,160,800	1,014,400

## **Additional Testing**

- UL2200-2015: Stationary Engine Generator Assemblies Section 66B Vibration Test.
- UL536: Flexible Metal Hose Section 7 Vibration Test.

## **Applications**

- Boilers
- Gas Meters
- Furnaces
- Commercial Water Heaters
- Gas packs/Rooftop HVAC units
- Tankless Water Heater
- Stationary Standby Generators (NOT for use with Portable Generators): Connector Length ≥ 14 inches

#### NOTICE

The minimum flow capacity values in the charts are at 0.5" w.c. pressure drop (inlet pressure minus outlet pressure). If your gas system has more available pressure drop then a general rule of thumb approximate calculation is as follows:

Minimum Flow Capacity @ your pressure drop = Square Root (your pressure drop/0.5) x value from chart

Example: What is the approximate minimum flow capacity (natural gas) of the Dormont 40 Series x 24" @ 1" wc pressure drop?

Answer: Square Root (1/0.5) x 290,900 = 411,395 BTU/hr



USA: Tel: (800) 367-6668 • Fax: (724) 733-4808 • Dormont.com
Canada: Tel: (905) 332-4090 • Fax: (905) 332-7068 • Dormont.ca
Latin America: Tel: (52) 81-1001-8600 • Fax: (52) 81-8000-7091 • Dormont.com

ES-D-HIghBTU 1610 © 2016 Dormont