
GATE 1184

BRONZE

300 lb. SWP-1000 lb. WOG† • Heavy Duty Service Solid Wedge Disc • Rising Stem • Stainless Seat • Gland Packed **Union Bonnet • Threaded Ends**

Wear-resistant stainless seat rings are securely expanded into the body to assure trouble-free service. Normal seating wear is restricted to the bronze wedge and can be easily replaced.



SPECIFICATIONS

1184	Conforms to: MSS SP-80. Type 2,			
	Class 300, Threaded Ends.			
MATERIALLIOT				

MATERIAL LIST

NO.	PART	MATERIAL	SPECIFICATION	
1	Body	Bronze	ASTM B 61	
2	Bonnet	Bronze	ASTM B 61	
3	Wedge Disc	Bronze	ASTM B 61	
4	Stem	Bronze	ASTM B 61	
5	Union Bonnet Nut	Bronze	ASTM B 61	
6	Seat Ring	St. Steel	ASTM A 240 TY304	
7	Gland	Brass	ASTM B 124 C37700	
8	Packing Nut	Brass	ASTM B 283 C37700	
9	Handwheel	Mall. Iron	Commercial	
10	Identification Plate	Aluminum	Commercial	
11	Handwheel Nut	Brass	Commercial	
12	Packing	Graphite	Commercial	

DIMEN						
UNITS	SIZE	Α	В	С	Cv	
Inches	1/4	1.81	5.13	2.25	5.6	
mm	6.35	46.05	130.18	57.15	3.0	
Inches	3/8	1.88	5.13	2.25	10.7	
mm	9.53	47.63	130.18	57.15	10.7	
Inches	1/2	2.25	5.50	2.50	17.6	
mm	12.70	57.15	139.70	63.50		
Inches	3/4	2.50	6.25	2.75	32.0	
mm	19.05	63.50	158.75	69.85		
Inches	1	3.00	7.19	2.75	54.0	
mm	25.40	76.20	182.58	69.85		
Inches	1 1/4	3.38	8.56	3.25	97.0	
mm	31.75	85.73	217.50	82.55		
Inches	1 1/2	3.50	9.63	3.75	135.0	
mm	38.10	88.90	244.48	95.25		
Inches	2	3.75	11.75	4.25	230.0	
mm	50.80	95.25	298.45	107.95		
Inches	2 1/2	4.63	14.50	4.75	337.0	
mm	63.50	117.48	368.30	120.65	337.0	
Inches	3	5.00	16.75	5.50	536.0	
mm	76.20	127.00	425.45	139.70	556.0	

† Non-Shock

Rev. 4





The information presented on this sheet is correct at the time of publication. Milwaukee Valve reserves the right to change design, and/or material specifications without notice. For the Installation, Operation and Maintenance Manual (IOM) see the engineering section on our website. For the most current information access www.milwaukeevalve.com

www.milwaukeevalve.com