

<b>B</b>	<div style="display: flex; justify-content: space-between; align-items: center;"> <div style="width: 30%;"> <p><b>SMITH® JAY R. SMITH MFG. CO.®</b>          DIVISION OF SMITH INDUSTRIES, INC.          POST OFFICE BOX 3237          MONTGOMERY, ALABAMA 36109-0237 (USA)          TEL: 334-277-8520 FAX: 334-272-7396 www.jrsmith.com</p> </div> <div style="width: 30%; text-align: center;"> <p>MEMBER OF:</p> </div> <div style="width: 30%; text-align: center;"> <p>MEMBER OF:</p> </div> </div>					<b>LOCATION</b>																																																																					
	<h2 style="margin: 0;">SMITH SPEEDI-SET REINFORCED NEOPRENE GASKET</h2>																																																																										
<b>SIZE</b>	<b>A</b>																																																																										
	<b>DRAWING NUMBER</b> S9508																																																																										
<b>SCALE:</b>	<b>NONE</b>																																																																										
<b>DATE:</b>	<b>12-8-94</b>																																																																										
<b>APPROVED BY:</b>	<b>BS</b>																																																																										
<b>CHECKED BY:</b>	<b>WMS</b>																																																																										
<b>DRAWN BY:</b>	<b>EMB</b>																																																																										
<b>FIGURE NUMBER</b>	<b>9508</b>																																																																										
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA																																																																											
<div style="display: flex;"> <div style="width: 60%;"> <p><b>FUNCTION:</b> Used with Smith Suffix-L "Speedi-Set" Drains, etc. to form a speedi-set push-on connection with all piping materials, including service weight, extra heavy and NO-HUB soil pipe, steel and plastic pipe. Heavy duty steel reinforcing rings molded integral with gasket ensure positive pipe and gasket stop at and after assembly for a totally reliable connection seal.</p> </div> <div style="width: 40%; text-align: center;"> </div> </div>																																																																											
<table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <thead> <tr> <th colspan="3">FIG. NO. 9508</th> <th colspan="5">NOMINAL</th> </tr> <tr> <th>SIZE</th> <th></th> <th>PART NO.</th> <th>A</th> <th>B</th> <th>C</th> <th>D</th> <th>E</th> </tr> </thead> <tbody> <tr> <td>02" (50)</td> <td>SW</td> <td>36042-94-6</td> <td>1 3/4(44)</td> <td>2 15/16(75)</td> <td>2 1/32(52)</td> <td>2 9/16(65)</td> <td>3 1/2(89)</td> </tr> <tr> <td>02" (50)</td> <td>XH</td> <td>36062-94-6</td> <td>1 7/8(48)</td> <td>2 15/16(75)</td> <td>2 1/32(52)</td> <td>2 9/16(65)</td> <td>3 1/2(89)</td> </tr> <tr> <td>03" (75)</td> <td>SW</td> <td>36043-94-6</td> <td>2 3/4(70)</td> <td>3 15/16(100)</td> <td>3(76)</td> <td>3 5/8(92)</td> <td>4 3/8(111)</td> </tr> <tr> <td>03" (75)</td> <td>XH</td> <td>36063-94-6</td> <td>2 3/4(70)</td> <td>3 15/16(100)</td> <td>3 1/16(78)</td> <td>3 5/8(92)</td> <td>4 3/8(111)</td> </tr> <tr> <td>04" (100)</td> <td>SW</td> <td>36044-94-6</td> <td>3 3/4(95)</td> <td>4 15/16(125)</td> <td>4 1/16(103)</td> <td>4 11/16(119)</td> <td>5 5/8(143)</td> </tr> <tr> <td>04" (100)</td> <td>XH</td> <td>36064-94-6</td> <td>3 3/4(95)</td> <td>4 15/16(125)</td> <td>4 3/16(106)</td> <td>4 11/16(119)</td> <td>5 5/8(143)</td> </tr> </tbody> </table>												FIG. NO. 9508			NOMINAL					SIZE		PART NO.	A	B	C	D	E	02" (50)	SW	36042-94-6	1 3/4(44)	2 15/16(75)	2 1/32(52)	2 9/16(65)	3 1/2(89)	02" (50)	XH	36062-94-6	1 7/8(48)	2 15/16(75)	2 1/32(52)	2 9/16(65)	3 1/2(89)	03" (75)	SW	36043-94-6	2 3/4(70)	3 15/16(100)	3(76)	3 5/8(92)	4 3/8(111)	03" (75)	XH	36063-94-6	2 3/4(70)	3 15/16(100)	3 1/16(78)	3 5/8(92)	4 3/8(111)	04" (100)	SW	36044-94-6	3 3/4(95)	4 15/16(125)	4 1/16(103)	4 11/16(119)	5 5/8(143)	04" (100)	XH	36064-94-6	3 3/4(95)	4 15/16(125)	4 3/16(106)	4 11/16(119)	5 5/8(143)
FIG. NO. 9508			NOMINAL																																																																								
SIZE		PART NO.	A	B	C	D	E																																																																				
02" (50)	SW	36042-94-6	1 3/4(44)	2 15/16(75)	2 1/32(52)	2 9/16(65)	3 1/2(89)																																																																				
02" (50)	XH	36062-94-6	1 7/8(48)	2 15/16(75)	2 1/32(52)	2 9/16(65)	3 1/2(89)																																																																				
03" (75)	SW	36043-94-6	2 3/4(70)	3 15/16(100)	3(76)	3 5/8(92)	4 3/8(111)																																																																				
03" (75)	XH	36063-94-6	2 3/4(70)	3 15/16(100)	3 1/16(78)	3 5/8(92)	4 3/8(111)																																																																				
04" (100)	SW	36044-94-6	3 3/4(95)	4 15/16(125)	4 1/16(103)	4 11/16(119)	5 5/8(143)																																																																				
04" (100)	XH	36064-94-6	3 3/4(95)	4 15/16(125)	4 3/16(106)	4 11/16(119)	5 5/8(143)																																																																				
<div style="display: flex; justify-content: space-between;"> <div style="width: 60%;"> <p><b>INSTALLATION:</b> The Speedi-Set reinforced neoprene gasket is normally factory assembled in drain outlet. For field assembly, coat interior of drain outlet with soil pipe joint lubricant and push gasket into place until it "Bottoms Out" on the external stop. Then apply the lubricant to gasket interior, place drain over pipe and push on until pipe end contacts the gasket's internal stop to complete the connection. If pipe is oversize, it may be necessary to tap the drain in place. In such cases, a wood block is recommended to avoid damage to casting.</p> </div> <div style="width: 35%;"> <p><b>NOTE:</b> Use an adhesive lubricant with plastic pipe.          SW = SERVICE WEIGHT PIPE          XH = EXTRA HEAVY AND PLASTIC PIPE  <b>MATERIAL:</b> NEOPRENE PER ASTM -C564-85</p> <p><b>NOTE:</b> Dimensions shown in parentheses are in millimeters.</p> </div> </div>																																																																											
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 10%; text-align: center;">REV.</td> <td style="width: 15%; text-align: center;">DATE</td> <td style="width: 35%; text-align: center;">DESCRIPTION</td> <td style="width: 10%; text-align: center;">BY</td> <td style="width: 10%; text-align: center;">CKD. BY</td> <td style="width: 10%; text-align: center;">WEIGHT POUNDS</td> <td style="width: 10%; text-align: center;">VOLUME CUBIC FEET</td> <td style="width: 10%; text-align: center;">FIGURE NUMBER <b>9508</b></td> </tr> <tr> <td style="text-align: center;">B A</td> <td style="text-align: center;">04/19/00 12-5-95</td> <td style="text-align: center;">Changed Metric Equivalents Added Millimeters</td> <td style="text-align: center;">JJ EMB</td> <td style="text-align: center;">BS BS</td> <td></td> <td></td> <td></td> </tr> </table>												REV.	DATE	DESCRIPTION	BY	CKD. BY	WEIGHT POUNDS	VOLUME CUBIC FEET	FIGURE NUMBER <b>9508</b>	B A	04/19/00 12-5-95	Changed Metric Equivalents Added Millimeters	JJ EMB	BS BS																																																			
REV.	DATE	DESCRIPTION	BY	CKD. BY	WEIGHT POUNDS	VOLUME CUBIC FEET	FIGURE NUMBER <b>9508</b>																																																																				
B A	04/19/00 12-5-95	Changed Metric Equivalents Added Millimeters	JJ EMB	BS BS																																																																							