
## **Tapered High Efficiency Takeoff**





## **Technical Data**

- Pre-sealed with gasket made of EPDM rubber and proprietary co-polymer
- Zero VOCs
- Galvanized Steel (ASTM A653 and A924)
- G-60 Galvanized Coating (ASTM A653 and ASTM A90)
- Available in Specialty Metals:
  - G-90 Galvanized Steel
  - Aluminum (ASTM B209 Alloy 3003 Temper H14)
  - 304 Stainless Steel (ASTM A480 2B Finish)
- Pressure Rating: Designed per SMACNA Third Edition 2005 Section 4.8 Figure 4-6 Branch Connections
- Dimensional Tolerance: ± 1/4"

- **A.** HETOs now come standard with sealed joints! The riveted seam on the collar and boot, as well as the co-latch seam between the collar and boot are sealed with the GreenSeam integral gasket. Unsealed fittings are available upon request.
- **B.** Non-dampered HETOs are supplied with a 3/8" knockout. Dampered HETOs are supplied with 24GA. damper blades and Ductmate's proprietary low-leakage hardware. See Appendix A.

Product Availability											
Size (Ød)	Gauge Availability		Quantity		Dimension						
	26 Ga.	24 Ga.	Layer	Skid	Α	В	С	D			
4"	Yes	-	35	210	10 ½"	7"	4"	1 ½"			
5"	Yes	Yes	30	180	10 ½"	9"	5"	2 ½"			
6"	Yes	Yes	30	180	10 ½"	9"	5"	2"			
7"	Yes	Yes	18	120	10 ½"	11	5	2 ½"			
8"	Yes	Yes	20	120	11 ½"	12"	6"	2 ½"			
9"	Yes	Yes	20	120	11 ½"	13"	7"	2 ½"			
10"	Yes	Yes	12	72	11 ½"	14"	8"	2 ½"			
12"	Yes	Yes	9	54	11 ½"	16"	10"	3"			
14"	Yes	Yes	6	36	12"	18"	12"	3"			
16"	-	Yes	4	24	13"	20"	14"	3"			
18"	-	Yes	4	24	13"	22"	16"	3"			
20"	-	Yes	4	24	13"	24	18	3"			

Dampered fittings are available with  $1\frac{1}{2}$ " or 2" Stand-Off. See Appendix B on page 27.

Part Number Schematic										
Example: HTS1510GA26D38 = Tapered HETO for 10" Pipe in 26Ga. Galvanized Steel, with a Solid Rod Damper and 11/2" Stand-Off										
HT Tapered High Efficiency Take- Off	\$15 Stand-Off \$15 - 1½" \$2 - 2" (Opt. on Dampers Only)	Tapered HETO Diameter (Ød)	GA Material GA-Galvanized (Std.) AL - Aluminum S4 - 304 S.S	<b>26</b> Gauge GA - 26, 24 AL - 32 S4 - 26	D Damper (Opt.)	38 3/8" Solid Rod (Opt. on Dampers Only) See Appendix C on page 28.				

<sup>\*</sup> Items in green denote available options