



## Electric Fryer Module

The accurate temperature control of the Wolf fryer module will enable you to seal in that great flavor of the food without absorbing any unnecessary grease. The extremely deep fryer can handle large portions of small food items or even a whole chicken. The Wolf fryer module comes with one large and two small fryer baskets.



Model IF15/S shown installed with model IG15/S electric grill module and model CT15G/S gas cooktop.

### FEATURES

- Integrated design allows for installation of multiple cooktops or modules.
- Stainless steel top construction.
- Hidden 2600-watt heating element.
- Illuminated electronic touch controls with graduated control lighting.
- Large 1<sup>1</sup>/<sub>4</sub> gallon capacity tub.
- Three baskets included — one large and two small side by side, each with wire basket hanger.
- Low-profile lid.
- Melt feature for shortening or lard.
- Independent digital timer.
- Digital temperature readout and preheat indicator.
- Easy manual locking drain capability.
- Recommended for installation with any Wolf framed electric cooktop or the Wolf electric grill module.

### ACCESSORIES

- Filler strip for installation of multiple cooktops or modules.

Accessories are available through your authorized Wolf dealer. For local dealer information, visit the find a showroom section of our website, [wolfappliance.com](http://wolfappliance.com).



Model IF15/S



Electronic touch controls.



Technical drawing showing the front and back views of the sink with dimensions:

- Front View Dimensions:
  - Overall Height: 21" (533)
  - Overall Width: 15" (381)
  - Drain Outlet Height: 6" (152)
  - Drain Outlet Width: 1 1/2" (13)
  - Side Panel Height: 7 1/2" (191)
  - Side Panel Width: 1" (25)
- Back View: Shows the mounting bracket and drain outlet connection.

8/10