


JONESPEC® FLOOR DRAINS



ADJUSTABLE FINISHED AREA FLOOR DRAIN

- Recommended for finished floor areas where a membrane is generally used.
- Designed for foot traffic and light cart applications.
- Complete with cast iron body and clamp collar and adjustable nickel bronze strainer assembly.

Body Type	Model Number	Dimensions in Inches [mm]					Box Qty.
		Pipe Conn.	A	B	C	D	
No-Hub	FD-2290-NH2	2" [51]	7-7/8" [200]	5-3/16" [132]	1" [25] Min. 1-1/2" [38] Max.	3-1/8" [79]	4
	FD-2290-NH3	3" [76]	7-7/8" [200]	5-3/16" [132]	1" [25] Min. 1-1/2" [38] Max.	3-1/8" [79]	4
	FD-2290-NH4	4" [102]	7-7/8" [200]	5-3/16" [132]	1" [25] Min. 1-1/2" [38] Max.	3-1/8" [79]	4
Push-On	FD-2290-PO2	2" [51]	7-7/8" [200]	5-3/16" [132]	1" [25] Min. 1-1/2" [38] Max.	3-5/8" [92]	4
	FD-2290-PO3	3" [76]	7-7/8" [200]	5-3/16" [132]	1" [25] Min. 1-1/2" [38] Max.	3-5/8" [92]	4
	FD-2290-PO4	4" [102]	7-7/8" [200]	5-3/16" [132]	1" [25] Min. 1-1/2" [38] Max.	3-5/8" [92]	4

Options

Suffix	Description
-CP	Chrome Plated
-P	1/2" [13] Trap Primer Connection
-R6	6" [152] Diameter Nickel Head Assembly
-R7	7" [178] Diameter Nickel Head Assembly
-R8	8" [203] Diameter Nickel Head Assembly
-VP	Vandal Proof