

Valves Technical

True Union 2000 Standard Ball Valves



Sample Engineering Specification

All thermoplastic ball valves shall be True Union 2000 Standard type manufactured to ASTM F 1970 and constructed from PVC Type I, ASTM D 1784 Cell Classification 12454 or CPVC Type IV, ASTM D 1784 Cell Classification 23447. All O-rings shall be EPDM or FKM. All valves shall have Safe-T-Shear® stem with O-ring stem seal. All handles shall be polypropylene. All union nuts shall have Buttress threads. All seal carriers shall be Safe-T-Blocked®. All EPDM valves shall be certified by NSF® International for use with potable water. All 1/2" - 2" valves shall be pressure rated to 235 psi, all 2-1/2" - 4" and all flanged valves to 150 psi for water @ 73°F, as manufactured by Spears® Manufacturing Company.

Quick-View Valve Selection Chart

Valve	O-ring		Pressure					
Size	Material	Socket	Threaded	SR Threaded	Flanged	Spigot	Rating	
1/2	EPDM	3629-005	included	3621-005SR	3623-005	3627-005		
1/2	FKM	3639-005	included	3631-005SR	3633-005	3637-005		
3/4	EPDM	3629-007	included	3621-007SR	3623-007	3627-007	235 psi	
3/4	FKM	3639-007	included	3631-007SR	3633-007	3637-007	Non-Shock Water	
1	EPDM	3629-010	included	3621-010SR	3623-010	3627-010	@ 73°F	
'	FKM	3639-010	included	3631-010SR	3633-010	3637-010		
1-1/4	EPDM	3629-012	included	3621-012SR	3623-012	3627-012	(Flanged	
1-1/4	FKM	3639-012	included	3631-012SR	3633-012	3637-012	150 psi Non-Shock)	
1-1/2	EPDM	3629-015	included	3621-015SR	3623-015	3627-015	Water	
1-1/2	FKM	3639-015	included	3631-015SR	3633-015	3637-015	@ 73°F	
2	EPDM	3629-020	included	3621-020SR	3623-020	3627-020		
2	FKM	3639-020	included	3631-020SR	3633-020	3637-020		
2-1/2	EPDM	3622-025	3621-025	3621-025SR	3623-025	3627-025		
2-1/2	FKM	3632-025	3631-025	3631-025SR	3633-025	3637-025	150 psi	
3	EPDM	3622-030	3621-030	3621-030SR	3623-030	3627-030	Non-Shock	
3	FKM	3632-030	3631-030	3631-030SR	3633-030	3637-030	Water	
4	EPDM	3622-040	3621-040	3621-040SR	3623-040	3627-040	@ 73°F	
4	FKM	3632-040	3631-040	3631-040SR	3633-040	3637-040		

^{1:} For CPVC valve, add the letter "C" to the part number (e.g., 3629-005C, 3621-005CSR)

Features — PVC, CPVC

Economical, low profile quarter-turn shutoff valve is excellent for general purpose and many O.E.M applications. PVC and CPVC valves are available in IPS sizes 1/2" through 4" with socket, regular thread, SR threaded (Special Reinforced), flanged or spigot end connectors.


- Chemical & Corrosion Resistant PVC or CPVC Construction
- Interchangeable with all True Union 2000 Valves, Mates with Union 2000 Pipe Unions
- · High Impact Polypropylene Handle
- · Schedule 80 Full-Port Design
- · Strong, Buttress Thread Union Nuts
- Spears® Single O-ring Safe-T-Shear® Stem Design
- · Spears® Safe-T-Blocked® Seal Carrier
- · Replaceable PTFE/HDPE Floating Seat Design
- EPDM or FKM O-rings
- Sizes 1/2" 2" pressure rated to 235 psi @ 73°F
- Sizes 2-1/2" 4" and all flanged pressure rated to 150 psi @ 73°F
- EPDM valves NSF® Certified for Potable Water use
- · Suitable for Vacuum Service
- Assembled with Silicone-Free, Water Soluble Lubricants
- Manufactured to ASTM F 1970

Optional Accessories*

- Retro-Fit End Connector Sets for Valve Replacement
- Split-Nut Repair Kits for Union Nut Replacement
- · Supplemental End Connectors
- Round Safety Handles
- · Stem Extension Kits
- · Square Operator Nuts
- Multi Mount Valve/ Actuation Mounting Kits
- · Mini-Mount Actuation Mounting Kits
 - * See "BALL VALVE ACCESSORIES" section for details of individual products.

Valves Technical True Union 2000 Standard Ball Valves





Replacement Parts

No.	Component	Qty.	Material
1	Seal Carrier	1	PVC/CPVC
2	Body	1	PVC/CPVC
3	Carrier O-ring	1	EPDM/FKM
4	Stem Bearing 1,2	1	PP
5	Stem	1	PVC/CPVC
6	Handle	1	PP
7	Stem O-ring	1	EPDM/FKM
8	Ball	1	PVC/CPVC
9	Seat	2	PTFE/HDPE
10	Union Nut	2	PVC/CPVC
11	End Connector O-ring	2	EPDM/FKM
12	End Connector	2	PVC/CPVC

^{1:} O-Ring up to 2"

Dimensions, Weights, Operating Torque & C_v Values

Nominal	А	В			С		D	E	F	G	Approx. Wt. (Lbs.)		Oper. ² Torque	C _v ³ Values		
Size		Soc/Thd	Spigot	Socket	Thread	Spigot					PVC	CPVC	(in. lbs.)	Soc/Thd/Spig	Flanged	
1/2	1-7/8	2-7/16	2-7/8	4-3/16	3-13/16	4-5/8	1-5/8	2-1/2	3-1/2	2-31/32	.33	.35	12	29	18	
3/4	2-1/4	2-3/4	3-1/4	4-3/4	4-1/4	5-1/4	2	3	3-7/8	3-5/16	.51	.54	20	63	39	
1	2-1/2	2-7/8	3-1/2	5-1/8	4-11/16	5-3/4	2-5/16	3-7/16	4-1/4	3-5/8	.71	.75	25	120	73	
1-1/4	3-1/16	3-1/4	3-13/16	5-3/4	5-3/16	6-5/16	2-13/16	3-9/16	4-5/8	3-31/32	1.12	1.17	35	243	151	
1-1/2	3-1/2	3-1/2	4	6-1/4	5-7/16	6-3/4	3-1/16	3-7/8	5	4-3/8	1.47	1.53	45	357	223	
2	4-1/4	4-3/4	5-13/16	7-3/4	6-3/4	8-1/4	3-3/4	5	6	5-1/4	2.62	2.75	94	599	395	
2-1/2	6-3/16	7-1/8	7-13/16	10-5/8	8-1/2	11-3/8	5-1/2	7-5/8	7	6-9/16	10.49	7.70	120	856	579	
3	6-3/16	7-5/32	7-13/16	10-15/16	9-3/4	11-9/16	5-1/2	7-5/8	7-1/2	6-7/8	11.22	7.81	120	1416	974	
4	7-3/4	7-13/32	8-1/4	11-15/16	10-1/4	12-3/4	6-1/8	9	9-1/16	7-1/2	18.46	12.48	336	2865	1952	

Temperature Pressure Rating

Sys Tem	100 (38)	110 (43)	120 (49)	130 (54)	140 (60)	150 (66)	160 (71)	170 (77)	180 (82)	190 (88)	200 (93)	210 (99)		
Valve Pressure Rating psi (MPa)	1/2" - 4"	PVC	235 (1.62)	211 (1.45)	150 (1.03)	75 (.52)	50 (.34)	-0- (-0-)						
		CPVC	235 (1.62)	219 (1.51)	170 (1.17)	145 (1.00)	130 (.90)	110 (.76)	90 (.62)	80 (.55)	70 (.48)	60 (.41)	50 (.34)	-0- (-0-)
	6" and 8"	PVC	150 (1.03)	135 (.93)	110 (.76)	75 (.52)	50 (.34)	-0- (-0-)						
		CPVC	150 (1.03)	140 (.97)	130 (.90)	120 (.83)	110 (.76)	100 (.70)	90 (.62)	80 (.55)	70 (.48)	60 (.41)	50 (.34)	-0- (-0-)

^{2:} PTFE Thrust Bearing: 2-1/2", 3" & 4"
3: An additional O-ring is used behind each seat on 2-1/2" or larger.

^{1:} Valve Lay Length
2: Torque required at valve maximum internal pressure rating, 5ft/sec. Flow velocity; due to adjustment differences during installation, actual valves may vary.
3: Gallons per minute at 1 psi pressure drop. Valves calculated from laying length, based on derivative of Hazen-Williams equation with surface roughness factor of C=150.