





Position	Count	Description	Unit price
	-1	<p><b>UP 26-99 F</b></p>  <p>Product photo could vary from the actual product</p> <p>Product No.: 52722351</p> <p>The pump is of the canned rotor type, i.e. pump and motor form an integral unit without shaft seal and with only two gaskets for sealing. The bearings are lubricated by the pumped liquid. The pump is characterized by:</p> <ul style="list-style-type: none"> <li>* Ceramic shaft and radial bearings.</li> <li>* Carbon axial bearing.</li> <li>* Stainless steel rotor can and bearing plate.</li> <li>* Corrosion-resistant impeller, Composite, PES.</li> <li>* Cast iron pump housing.</li> </ul> <p>The motor is a 1-phase motor. No additional motor protection is required.</p> <p><b>Liquid:</b></p> <p>Liquid temperature range: 32 .. 230 °F Density: 62.4 lb/ft³</p> <p><b>Technical:</b></p> <p>Actual calculated flow: 30.9 US gpm Resulting head of the pump: 3.6 ft Approvals on nameplate: UL, CSA</p> <p><b>Materials:</b></p> <p>Pump housing: Cast iron EN-JL1030 ASTM 30 B</p> <p>Impeller: Composite, PES</p> <p><b>Installation:</b></p> <p>Maximum ambient temperature: 104 °F Ambient max at 176°F liquid: 176 °F Maximum operating pressure: 145 psi Flange standard: USA Oval Type of connection: C.I. Flange Pipe connection: 2 - Bolt Flange Pressure stage: 10 Port-to-port length: 6 1/2 in</p>	On request

Position	Count	Description	Unit price
		<b>Electrical data:</b> Number of poles: 2 Max. power input: 245 W Rated power - P2: 0.161 HP Main frequency: 60 Hz Rated voltage: 1 x 230 V Current in speed 3: 1.07 A Capacitor size - run: 2.5 µF/380 V Insulation class (IEC 85): F  <b>Others:</b> Gross weight: 11.5 lb	

52722351 UP 26-99 F 60 Hz



Note! All units are in [mm] unless others are stated.  
Disclaimer: This simplified dimensional drawing does not show all details.