

LabWasteTM

CPVC Corrosive Waste Drainage Systems



**ECHNICAL INFORMATION & INSTALLATION GUIDE

August 1, 2011
SUPERSEDES ALL PREVIOUS EDITIONS

U.S. Patent No. 7,178,557

Manufactured to ASTM F 2618

NSF_® cw Certified For

Corrosive Waste





Visit our web site www.spearsmfg.com

LW-4-0811



Additional LabWaste™ Publications

Spears® LabWaste ™ CPVC Corrosive Waste Drainage Systems in Price	e Schedule SSB-1
Spears® LabWaste ™ CPVC Corrosive Waste Drainage Systems – Gene	eral Data Sheet LW-2
Spears® LabWaste™ Standard CPVC & HDPE Neutralization Tanks in F	Price Schedule SSB-1
(Includes technical	information)

This manual provides basic technical information, dimensions and installation guidelines for Spears® **LabWaste™** CPVC Corrosive Waste Drainage Systems that are designed for commercial, industrial, and institutional drainage system applications. This unique product developed by Spears® has been awarded a U.S. Patent, No. 7,178,557 and is manufactured to ASTM F 2618 *Standard Specification for Chlorinated Poly (Vinyl Chloride) (CPVC) Pipe and Fittings for Chemical Waste Drainage Systems* developed for this system. Spears® **LabWaste™** CPVC Corrosive Waste Drainage Systems carries a limited Lifetime Warranty. Please refer to the above publications or contact Spears® Technical Services for additional information not covered.

Laboratory Applications

Its broad range of resistance to chemical and corrosive wastes make Spears® **LabWaste™** CPVC systems very well suited for commercial, institutional and academic laboratory drainage installations. These applications are best characterized as the routine disposal of a wide variety of hot and cold chemicals in relatively small quantities accompanied by water for the purpose of dilution and flushing. Due to the interactions potentially encountered in multi-chemical laboratory drainage disposal, Spears® recommends routine flushing of the system with water during disposal as a part of prudent laboratory practices. A properly designed and installed **LabWaste™** CPVC system provides total dilution and disposal need for years of dependable service.

Industrial & Commercial Special Waste Applications

Spears® **LabWaste™** CPVC products can be used in a very broad variety of dedicated waste applications with proper evaluation of waste medium and service conditions. **DO NOT** follow Chemical Resistance Tables recommendations in this manual for these applications. For non-laboratory applications, refer to CPVC pressure system resistance data for appropriate chemical resistance guidelines. Please contact Spears® Technical Services for additional information.

Chemical Resistance Overview

Spears® **LabWaste™** CPVC systems are inert to most mineral acids, bases, salts and aliphatic hydrocarbons, and compares favorably to other non-metals in these chemical environments.

General Chemical Resistance Overview:

Weak Acids	Excellent	Salts	Excellent
Strong Acids	Excellent	Aliphatic Solutions	Good
Weak Bases	Excellent	Halogens	Good-Fair
Strong Bases	Excellent	Strong Oxidants	Good-Fair

Refer to Chemical Resistance Information section at the end of this manual for Chemical Resistance Tables and additional information and detail.



Applicable Conformance Standards & Certifications

Spears® **LabWasteTM** CPVC Corrosive Waste Drainage System is a complete system of pipe, fittings and solvent cement independently (3rd party) tested, evaluated and certified by the following laboratories and agencies. Each of these approvals is routinely monitored through an ongoing program of periodic inspection and testing by the certifying agency.

- **ASTM F 2618** Certified for corrosive waste end use by NSF_® International (NSF_® cw) in accordance with ASTM F 2618, *Standard Specification for Chlorinated Poly (Vinyl Chloride) (CPVC) Pipe and Fittings for Chemical Waste Drainage Systems.*
- NSF ORD 1022 Certified as an Other Recognized Document (ORD) that defines the product specific requirements for Chlorinated Poly Vinyl Chloride (CPVC) Chemical Waste Systems in accordance with the requirements of ASTM F 2618 for use in Canada.
- Uniform Plumbing Code Certified for use in accordance with the Uniform Plumbing Code (UPC) by NSF_® International as specified in IAPMO IGC 210, *Interim Guide Criteria for Chlorinated Poly (Vinyl Chloride) (CPVC) Pipe and Fittings for Limited Chemical Waste Drainage System.* (NSF_®-U.P.Code).
- International Plumbing Code Approved for use in accordance with the International Plumbing Code (IPC) by the International Codes Council
 Evaluation Services (ICC ES) in accordance with ICC ES PMG Listing PMG 1018 for Spears® LabWaste™ CPVC Corrosive Waste
 Drainage System (See ICC ES PMG Listing PMG 1018 at www.icc-es-pmg.org.)

Typical Physical Properties of Spears® LabWaste™ CPVC Material

Property	Test Method	Typical Value
Mechanical Properties @ 73°F Specific Gravity Tensile Strength, psi Tensile Modulus, psi Flexural Strength Izod Impact (notched @73°F) Fittings	ASTM D 792 ASTM D 638 ASTM D 638 ASTM D 790 ASTM D 256	1.49 9000 420,000 12,000
Pipe Thermal Properties Heat Deflection Temperature 264 psi Fitting Pipe Thermal Conductivity, BTU/hr/sq ft/°F/in Coefficient of Linear Expansion, in/in/°F	ASTM D 648 ASTM C 177 ASTM D 696	5.5 214°F 230°F .95 3.2 x 10 ⁻⁵
Flammability Limiting Oxygen Index UL 94 Rating	ASTM D 2863 UL 94	60 V-0, 5VB
Flame & Smoke Rating¹ Flame Spread Smoke Developed	CAN/ULC S 102.2 UL 723/ASTM E 84	<25 <50
Solvent Cement	ASTM F 2618/ASTM F 493	Heavy Body; Mustard Yellow Color

Typical Physical Properties data is based on information from material suppliers. It is provided as a guideline for service and is not to be considered a warranty of performance.

1- Based on test of physical product, including solvent cement welded pipe and fittings assemblies, as opposed to test of material only.

Fire Resistance

Material used in Spears® **LabWaste™** CPVC systems has a UL 94 flammability rating of V-0, 5VB. Pipe and fittings have been Listed and rated based on *finished product* tests, as opposed to a material test only, for surface burning characteristics of flame spread and smoke density developed by Underwriters Laboratories of Canada under standard test method CAN/ULC S102.2-M88. Additional test of **LabWaste™** pipe with dry fit caps was conducted by Southwest Research Institute (SwRI) Department of Fire Technology under UL 723/ASTM E 84 (modified to test finished product). Pipe and fitting components ratings are below the 25 maximum flame spread and 50 maximum smoke density developed typically required for exposed air plenum installation. Check local codes for acceptability. Use of approved plenum wrap or transition connectors to other material may be used if required.



Pipe & Fittings

Spears® **LabWaste™** CPVC pipe and fittings are produced to the dimensional and performance requirements of ASTM F 2618, *Standard Specification for Chlorinated Poly (Vinyl Chloride) (CPVC) Pipe and Fittings for Chemical Waste Drainage Systems.* **LabWaste™** CPVC fitting configurations are produced to applicable DWV patterns of ASTM D 3311, *Standard Specification for Drain, Waste, and Vent (DWV) Plastic Fittings Patterns,* plus various specialty patterns and manufactured specified configurations not included in D 3311. All drainage fittings with 90° angles (sanitary tees, elbows, etc.) have socket pitch to maintain approximately 1/4" per foot drainage. **LabWaste™** CPVC pipe is produced to dimensions specified in ASTM F 2618 with sizes greater than 12" produced to Schedule 40 dimensions of ASTM F 441, *Standard Specification for Chlorinated Poly (Vinyl Chloride) (CPVC) Plastic Pipe, Schedule 40 and 80.*

Schedule 40 CPVC Pipe Dimensions (inch)

Pipe Diameter	1-1/2	2	3	4	6	8	10	12	14	16	18	20	24
Avg. O.D.	1.900	2.375	3.500	4.500	6.625	8.625	10.750	12.750	14.000	16.000	18.000	20.000	24.000
Avg. I.D.	1.592	2.049	3.042	3.998	6.031	7.943	9.976	11.889	13.073	14.940	16.809	18.743	22.544
Min. Wall	.145	.154	.216	.237	.280	.322	.365	.406	.437	.500	.562	.593	.687

Expansion & Contraction

Spears® **LabWaste**™ CPVC products, like all piping materials, expand and contract with changes in temperature. If the coefficient of linear expansion is 3.2 x 10⁻⁵ in./in. °F, a 25°F change in temperature will cause an expansion of 1 inch for a 100-foot straight length. For most operating and installation conditions, expansion and contraction can be accommodated at changes of direction, or simple expansion loops can be used. For underground installations, snaking the pipe in the trench can be used where necessary to accommodate expansion and contraction.

Thermal expansion change in length is calculated from Length of Run in feet, expected Change in Temperature and given Coefficient of Linear Thermal Expansion of 3.2 x 10⁻⁵ in./in. °F for CPVC:

 $\Delta L = 12eL (\Delta T)$

Where:

 $e = 3.2 \times 10^{-5} \text{ in./in. } ^{\circ}\text{F}$

L = Length of Run in feet

 ΔT = Temperature Change in °F

Example:

How much will a 50 ft. run Spears® **LabWaste™** pipe expand if the expected ambient temperature will range from 45°F to 85°F?

 $\Delta L = 12eL (\Delta T)$

 $\Delta L = 12 \times .000032 \times 50 \times 40$

 $\Delta L = .768$ inches

The following table provides quick reference in identifying expansion length change for different run lengths of pipe at various anticipated temperature changes.

Thermal Expansion Table

			Length Chang	Change in Temperature (△T)					
Length of Run (L) in feet	20°F	30°F	40°F	50°F	60°F	70°F	80°F	90°F	100°F
10	.08	.12	.15	.19	.23	.27	.31	.35	.38
20	.15	.23	.31	.38	.46	.54	.61	.69	.77
40	.31	.46	.61	.77	.92	1.08	1.23	1.38	1.54
50	.38	.58	.77	.96	1.15	1.34	1.54	1.73	1.92
70	.54	.81	1.08	1.34	1.61	1.88	2.15	2.42	2.69
90	.69	1.04	1.38	1.73	2.07	2.42	2.76	3.11	3.46
120	.92	1.38	1.84	2.30	2.76	3.23	3.69	4.15	4.61



Joining Methods

Spears® **LabWaste**™ CPVC pipe and fittings are easily joined using Spears® LW-5 One-Step Solvent Cement that has been specially formulated for corrosive/acid waste applications and manufactured in accordance with ASTM F 493, *Standard Specification for Solvent Cements for Chlorinated Poly (Vinyl Chloride) (CPVC) Plastic Pipe and Fittings*, as specified in ASTM F 2618. When cured, this cement provides a fused joint that maintains the same physical and chemical resistance properties as the CPVC components in the system. Spears® LW-5 is a "one-step" cement and does not require the use of primer. Spears® **LabWaste**™ CPVC systems may be additionally joined using threaded (NPT) or flanged connections where removal or connection to supplementary equipment is required. Special transition couplings are available for joining to Polypropylene, PVDF, glass or Duriron systems.

Solvent Cement Joints – Store below 90°F (33°C). Stir and use as is. If jelled, replace. Use within 2 years of date stamped on can. This cement is designed for use without a Primer. Check local code requirements before using Spears® LW - 5 cement.

- 1. Cut pipe square, deburr and chamfer (bevel 10° to 15°). Clean and dry joining surfaces.
- 2. Check dry fit. For interference fit, pipe should push 1/4 to 3/4 way into fitting snugly.
- 3. Use a suitable applicator at least 1/2 size of pipe diameter; for larger sizes use brush or roller.
- 4. Apply a full even layer of cement on the pipe equal to the socket depth. Coat the fitting socket with a medium layer. Avoid excess and puddling. If necessary, apply a second full layer on pipe.
- 5. Assemble while cement is wet. If not wet, recoat all parts before assembly. Assure pipe bottoms into fitting socket using a 1/8 to 1/4 turns twist. To avoid push out and allow for initial set, hold for about 30 seconds. Wipe off excess. Handle newly assembled joints carefully.

An Initial Set time is recommended to provide good handling strength after which the joint will handle normal stresses of installation. Cure Time is the recommended waiting period prior to placing the joint into service and before any pressure testing of the system. Set and cure times are relative to temperature at time of installation. Best results are obtained at temperatures between 40° and 110°F. Due to the many field variables, these should be used as a general guide only.

Recommended Set & Cure Times

Temperature	Initial Set	Cure
60°F - 100°F	30 min.	1 hr.
40°F - 60°F	1 hr.	2 hrs.
0°F	2 hrs.	4 hrs.

In moist or humid conditions (relative humidity above 60%) allow 50% more cure time.

Average Number of Joints per Quart of LW-5 One-step Cement

Pipe Diameter	1-1/2	2	3	4	6	8	10	12	14	16
No. of Joints	90	60	40	30	10	5	2-3	1-2	3/4	1/2-3/4

Estimate based on laboratory tests. Due to many field variables, these figures should be used as a general guide only.



Threaded Joints - Spears® Manufacturing Company highly recommends the use of Spears® BLUE 75™ thread sealant, which has been tested for compatibility with Spears® products. Please follow the sealant Manufacturer's Application/Installation instructions. Choice of another appropriate thread sealant is at the discretion of the installer.

WARNING: Some pipe joint compounds or pastes may contain substances that could cause stress cracks in CPVC. For transitions to metal threaded systems, all cutting oils must be removed and the metal pipe thoroughly flushed and degreased prior to assembly with CPVC systems.

- 1. Apply joint sealant to the male pipe threads ONLY.
- 2. Thread joint hand tight for initial assembly.
- 3. Using commercial strap wrenches tighten 1 to 2 turns beyond hand tight; avoid over tightening. **DO NOT** use conventional pipe wrenches that can damage plastic fittings.

If a tape sealant is used:

- 1. Use TFE tape no less than 25 mil thick.
- 2. Initial wrap must fully cover the thread end.
- 3. Wrap clockwise with standard pipe threads.
- 4. Use only 2-3 wraps of tape.

DO NOT use combination of paste and tape sealants.

Flanged Connections - Solvent cement flange hub to pipe according to preceding instructions. Use full faced, 1/8" thick gaskets of a material suitable for the intended application having a Shore "A" durometer of approximately 60. Use of well lubricated bolts and flat washers is required. Bolts must be tightened in a 180° opposing pattern to the recommended torque values.

Flange Size (in.)	Bolt Torque (ftlb.)	Torque Sequence
1-1/2	12	11 15 1 -
2-4	25	$\begin{bmatrix} 3 \\ 1 \end{bmatrix}$ $\begin{bmatrix} 5 \\ 1 \end{bmatrix}$ $\begin{bmatrix} 11 \\ 7 \end{bmatrix}$ $\begin{bmatrix} 11 \\ 5 \end{bmatrix}$ $\begin{bmatrix} 11 \\ 7 \end{bmatrix}$ $\begin{bmatrix} 5 \\ 9 \end{bmatrix}$
6-8	40	$3 \leftarrow 3 \leftarrow 3 \leftarrow 9 \rightarrow 9 \rightarrow 13$
10	64	10 4 14
12	95	2 - 4 $2 - 6$ $6 - 12 - 8$ $10 - 6 - 12 - 8$
14-16	110	2 16

LabWaste™ Transitions To Other Systems – Spears® **LabWaste™** Corrosive Waste Drainage System provides a complete line of transition fittings for use with other corrosive waste piping materials for system additions and retrofits.

P099 Transition Coupling: Hub X Compression. Allows connection of **LabWaste**[™] to Polypropylene or PVDF pipe and solvent cement socket connection to CPVC system. A safety groove must be cut into the Polypropylene or PVDF pipe to resist pull out. A groove cutting tool is available from Spears[®]

P093 Elastomer Transitions Coupling For Glass: IPS Clamp Joint X Glass Clamp Joint. Allows mechanical connection of **LabWaste**™ CPVC pipe to plain end Kimax[®] glass pipe. Consists of high performance fluoroelastomer (FKM) sleeve, an outer stainless steel shear ring and two AISI 301 stainless steel clamping bands.

P098 Glass Transition Coupling: Spigot X Bead Clamp. Allows mechanical connection of **LabWaste™** to beaded-end glass drainage pipe. Coupling consists of a CPVC beaded-end matching glass pipe bead and CPVC pipe diameter spigot end for solvent cement connection. This requires a glass system's mechanical connector, available from Schott Scientific Glass, part# 6650-XXXXX Bead-to-Bead end.

P094 Elastomer Transitions Coupling For Duriron®: IPS Clamp Joint X Duriron® Clamp Joint. Allows mechanical connection of **LabWaste™** CPVC pipe to plain end Duriron® pipe. Consists of high performance fluoroelastomer (FKM) sleeve, an outer stainless steel shear ring and two AISI 301 stainless steel clamping bands.

P095 Duriron® Mechanical Transition Fitting: Mechanical Joint X CPVC Pipe Size. Allows mechanical connection of **LabWaste™** to Duriron (siliconized iron) pipe. Fitting consists of Duriron pipe diameter spigot (male pipe end) and CPVC pipe diameter spigot end for solvent cement connection. Requires use of Duriron Mechanical Joint Coupling that consists of an inner sleeve of PTFE surrounded by an outer sleeve of Neoprene rubber held in place by a stainless steel coupling. Duriron® Mechanical Joint Coupling available through Flowserve.

P097 Duriron® Caulk Transition Coupling: Spigot x Caulk Joint. Allows caulk-joint connection of **LabWaste™** pipe to Duriron borosilicate systems. Coupling consists of Duriron pipe diameter male end for mating to Duriron belled pipe end and CPVC pipe diameter spigot end for solvent cement connection. This requires use of special chemical acid-resistant oakum packing available from Flowserve (Red Stripe Sealite A312 Rope) and plastic lead/caulk purchased from others. DO NOT use hot lead or oiled Oakum for this type of caulk-joint.



6

P096 Grooved Coupling Adapter: Groove X Socket. Allows connection of the **LabWaste**[™] to grooved metal piping systems. Requires use of a Metal Grooved Coupling with gasket. A flexible style grooved coupling must be used for plastic only. **Do not use rigid style couplings.** Use either Victaulic Flexible Grooved Couplings Part # 75 & 77 or Gruvlok Flexible Grooved Couplings Part # 7001 & 7000.

Please contact Spears® for special construction of any system transition connection needs not specified.

Support Spacing

Spears[®] **LabWaste**[™] CPVC systems should be properly supported to avoid stress caused by sagging and system component loads. Support should be given to concentrated system loads, such a flanges and where changes in direction occur. Such support should be made as close to fittings as possible, yet allow for movement due to expansion and contraction.

Conventional pipe hangers and brackets can be used. However, hangers must **NOT** be used to pull the piping system into position or over tightened to either restrict necessary movement or cut into pipe. Hangers should be smooth, free of burrs and provide as much load-bearing surface as possible.

Systems should be supported in accordance with applicable plumbing codes. Check local codes for additional requirements. The following chart shows recommended horizontal support spacing for un-insulated continuous spans with no concentrated loads. This information is provided as a general guideline. Local codes, engineering specifications, and system installation conditions may require significant variations.

Recommended Hanger Spacing (feet)

Pipe Diameter	1-1/2	2	3	4	6	8	10	12	14	16
Hanger Spacing	6	6	7	7-1/2	8	9	10	10-1/2	11	12

Underground Installation

Spears® **LabWaste**™ CPVC systems may be installed underground in a smooth, uniform trench bottom that supports the pipe over its entire length, free of rocks and debris. Subsoil should be stable to provide physical protection for the pipe and fittings. Where large boulders are not removed, trench should be padded with sand or fine-grained soil. Trench should be wide enough to provide room for joining pipe in the trench and to allow snaking from side-to-side to provide slack for future expansion-contraction. Install a larger size pipe as a sleeve where piping must pass through masonry walls. Use only solvent cement connection in underground piping. System should be tested in accordance with local plumbing codes prior to back filling. Pipe should be surrounded with an initial backfill material having a particle size of 1/2" or less, free of sharp rock or debris and uniformly compacted in layers. Refer to ASTM D 2321, *Underground Installation of Thermoplastic Pipe for Sewer and Other Gravity-Flow Applications*, for additional information on underground installations.

Acid Neutralization/Dilution Tanks for Use With LabWaste™ CPVC Systems

Neutralization or dilution tanks are required by codes for the purpose of neutralizing corrosive wastes. Corrosive liquids, spent acids or other harmful chemicals that destroy or injure a drain, sewer, soil or waste pipe, or create noxious or toxic fumes or interfere with sewage treatment processes are prohibited from discharge into the plumbing system without being neutralized or treated. A variety of system designs and treatment methods can be used for neutralization and dilution. For proper performance, Spears® recommends use of professional assistance in analysis of the application, neutralization system design, equipment selection, and specific maintenance requirements.

Spears® offers a standard selection of HDPE in 5 gallon to 3000 gallon capacities and CPVC tanks in 5 gallon to 55 gallon capacities with a variety of connection and vent options, plus convenient 1-gallon Dilution Tank designed for under-sink installation. Tanks can also be custom produced in virtually any size, shape, or connection configuration, including custom double-containment tanks. Contact Spears® Technical Services with desired specifications for custom quotation. See Price Schedule LWNT-1, "Spears® **LabWaste**™ Standard CPVC & HDPE Neutralization Tanks", for pricing, additional information, selection detail and available options such as venting, tank extensions, manhole ports, pedestrian and traffic covers.

Installation Considerations - Except for under-sink installations, tank should be located on the lowest floor or basement room. It is recommended that the tank be in a concrete vault on a smooth flat surface. Where necessary, tanks may be installed on sturdy sheeting or directly into the ground. In all cases, the surface must be capable of uniformly supporting the tank weight, including effluent and neutralization medium.

Neutralization tanks and tank extensions are not warranted for direct burial applications. Tanks must be properly placed and secured with no applied stresses, within a dry concrete vault. However, if direct burial is used without warranty, custom centerlines must be furnished from top of cover down to fitting centerline instead of specified tank bottom to fittings centerline since tank heights can vary. The top of the tank must remain accessible for servicing and clean out either directly or by manhole cover. Tanks may be installed under foot or light vehicle traffic with use of appropriate covers and support. Tanks themselves are not to be used to support traffic loading.

Avoid strain when installing the pipe to tank fitting connections. Tanks must NOT be supported by the inlet, outlet, or vent piping.



The following recommendation from the American Society of Plumbing Engineers (ASPE) may be used as a guideline for sizing tanks according to the number of lab sinks.

Neutralization Tank Sizing Table

Newshan of Lab Cinter	Tank	Size
Number of Lab Sinks	Gallons	Liters
2	5	18.9
4	15	56.8
8	30	113.6
16	55	208.2
22	75	283.9
27	90	340.7
30	108	408.8
40	150	567.8
50	175	662.4

Noveles et la la Circles	Tank	Size
Number of Lab Sinks	Gallons	Liters
60	200	757
75	275	1040.9
110	360	1362.6
150	500	1898.5
175	550	2081.8
200	650	2460.3
300	1200	4542
500	2000	7570
600	3000	11355

Limestone Chips for Acid Neutralization Tanks - Most state and local codes require the addition of a neutralization medium in acid waste tanks with the addition of water for dilution prior to discharge into a sanitary sewer system. Limestone must be 1" to 3" in diameter with a calcium carbonate content of at least 90%. Spears® offers high grade Limestone Chips having a calcium carbonate content of approximately 95%. The use of Limestone Chips is generally one of the best and least expensive means of acid neutralization, but may be used in conjunction with more sophisticated chemical treatments if necessary.

How Much Limestone to Use - The following is a guideline for pounds of Limestone Chips to use for one (1) tank filling (charge). It is recommended that sufficient quantity be ordered for more than one filling.

Tank Size Gallons	Approx. Pounds
5	50
15	100
30	200
55	500
100	1,000
150	1,750
175	1,900
200	2,500
275	3,200

Tank Size Gallons	Approx. Pounds
300	3,200
350	4,000
500	5,000
550	7,500
650	9,000
1200	11,000
2000	16,000
3000	25,000

General Tank Maintenance Guidelines -Tanks should be inspected routinely for accumulation of precipitated sludge and debris that must be cleaned out (usually scooped out) and for periodic addition of limestone and water if necessary. While once every one to three months may be sufficient, professional assistance should be sought to establish a proper schedule based on actual use. **Note:** Tank must be filled with water prior to carefully adding Limestone Chips to charge the system. Request instruction sheet.



System Pressure Testing

Spears® **LabWaste™** CPVC systems should be tested with water as follows, or according to local plumbing codes. Test only after sufficient joint cure (see "Recommended Set & Cure Time"). The system may be tested in its entirety or isolated at each floor or in sections for testing.

Close all openings tight except the highest opening and fill the system to the point of overflow. Fill the system slowly, being sure to allow all air to escape. A minimum of ten (10) foot (3048 mm) head should be used for entire system or section tested. Allow the system/section under test to set 15 minutes before inspection for leaks.

Drain each section after inspection. Any leaking solvent cement joints should be cut from the system, replaced and retested after proper joint cure. Check any leaking mechanical joints for proper installation, applicable tightening, and presence of any debris in the joint. Reassemble and retest.

Supplemental Equipment Not Specified in this Manual

A variety of supplemental equipment including, pump stations, laboratory workstations, and fume hoods are built to customer specifications. Standard Laboratory fixtures, floor drains, wall drains and traps plus manual or actuated valves are also available. Spears[®] can custom fabricate virtually any **LabWaste**™ system component. Contact Spears[®] for additional needs or a custom quotation.

System Integrity

Spears® **LabWaste**™ products have been developed and designed to be used as a total system consisting of pipe, fittings, accessories, solvent cement and thread sealant. All-Spears® **LabWaste**™ components should be used in order to insure a sound piping system. Substitution of other products for Spears® **LabWaste**™ pipe, fittings, or solvent cement may be detrimental to system integrity and is not recommended. The Spears® Limited Warranty (located on the back cover of this manual) does not cover problems occurring within the piping system as the direct result of non-use of Spears® **LabWaste**™ system products.


Sample Engineering Specification

Special drainage systems for corrosive chemical or acid waste shall be manufactured from CPVC Type IV, ASTM Cell Classification 23447. All pipe, fittings and solvent cement shall be manufactured in accordance with ASTM F 2618 and certified by NSF_® International for corrosive waste end use (NSF_® cw). All pipe and molded fittings shall be CAN/ULC S102.2 Listed for Surface Burning Characteristics with a flame spread of less than 25 and a smoke development of less than 50 as designated on the original package labeling for fittings and on the pipe print string marking. All pipe markings shall be accompanied by a yellow stripe for identification of CPVC chemical waste system. All fittings shall be CPVC drainage patterns meeting the requirements of ASTM D 3311 and specialty patterns according to the manufacturer's specifications. Joining method for pipe and fittings shall be solvent cement welding. Solvent cement shall be a "one-step" primerless type CPVC cement designated by the system manufacturer, specially formulated for resistance to corrosive chemicals and manufactured in accordance with ASTM F 493, as specified in ASTM F 2618. Mechanical connections for special equipment connection or transition to other system materials shall be as specified by the CPVC system manufacturer. All pipe, fittings, and cement shall be supplied together as a complete system. Installation shall be in accordance with the manufacturer's instructions and all applicable codes. Special drainage system to be Spears® LabWaste™ CPVC Corrosive Waste Drainage Systems manufactured by Spears® Manufacturing Company.



P095 Duriron Transition Fitting

Mechanical Joint x Pipe Size




For connection to Duriron system. Requires duriron mechanical joint coupling.

Part Number	Size	Α	L	w
P095-015C	1-1/2	1-3/16	4	1-3/8
P095-020C	2	2-5/8	4	1-1/2
P095-030C	3	3-3/4	4	1-7/8
P095-040C	4	4-3/4	4	2-5/16

P096 Grooved Coupling


Grv x Soc



Part Number	Size	L	N
P096-015C	1-1/2	2-15/16	1-1/2
P096-020C	2	3-1/16	1-9/16
P096-030C	3	3-9/16	1-11/16
P096-040C	4	4-1/2	2-1/4
P096-060C	6	5-3/8	2-3/8

P097 Duriron Transition Coupling

Spig x Caulk Joint




For connection to Duriron system. Requires packing and plastic lead. **Warning:** Do not use hot lead or oiled Oakum.

Part Number	Size	Α	L	W
P097-015C	1-1/2	2-1/4	12	1/2
P097-020C	2	2-7/8	12	1/2
P097-030C	3	4-3/16	12	1/2
P097-040C	4	5-1/4	12	1/2

P097 Duriron Transition Coupling (continued)

Spig x Caulk Joint




For connection to Duriron system. Requires packing and plastic lead. **Warning:** Do not use hot lead or oiled Oakum.

Part Number	Size	Α	L	W
P097-060C	6	7-9/16	12	1/2
P097-080C	8	9-11/16	12	1/2

P098 Glass Transition Coupling

Spig x Clamp




For connection to glass system. Requires use of clamp from glass system manufacturer.

,				
Part Number	Size	Α	L	W
P098-015C	1-1/2	2-1/16	4	1/4
P098-020C	2	2-1/16	5	1/4
P098-030C	3	3-11/16	6	5/16
P098-040C	4	4-27/32	6	5/16
P098-060C	6	7-1/8	6	1/2

P099 Transition Coupling

H x Compression




For connection to PP or PVDF systems. Requires Safety Retaining Groove Tool. Contact Spears®.

3				
Part Number	Size	С	L	N
P099-015C	1-1/2	1-3/8	5-1/8	3/32
P099-020C	2	1-1/2	5-3/4	1/8
P099-030C	3	1-7/8	10-5/16	3/16
P099-040C	4	2-1/4	11-5/32	7/32
P099-060C	6	3	13-3/8	9/32




P100 Coupling НхН




Part Number	Size	N
P100-015C	1-1/2	1/8
P100-020C	2	1/8
P100-030C	3	3/16
P100-040C	4	1/4
P100-060C	6	1/4
P100-080C	8	1/4
P100-100C	10	3/8
P100-120C	12	3/8
P100-140C	14	3/8


P101 Female Adapter


FPT x H




Part Number	Size	N
P101-015C	1-1/2	1/4
P101-020C	2	1/4
P101-030C	3	5/16
P101-040C	4	3/8
P101-060C	6	15/32



















P104X Trap Adapter - Female


H x Slip w/ Chrome Nut & Washer






8

13/32





P105-080C







Part Number	Size	N
P109-169C	1-1/4x1-1/2	3/16
P109-015C	1-1/2	3/16
P109-020C	2	3/16
P109-030C	3	3/8
P109-040C	4	3/8
P109-060C	6	11/16











For connection to Cast Iron system. Requires packing and plastic lead. **Warning:** Do not use hot lead or oiled Oakum.


Part Number	Size	N
P123-020C	2	4-5/8
P123-030C	3	5-5/8










Part Number	Size	G
P300-015C	1-1/2	1-11/16
P300-020C	2	2-3/16
P300-030C	3	3
P300-040C	4	3-7/8
P300-060C	6	5
P300-080C	8	6
P300-100C	10	9-29/32
P300-120C	12	10-29/32












P309 Long Sweep 1/4 Bend, Street (90° LS Street Ell)


H x Spig



Part Number	Size	G	Н
P309-015C	1-1/2	2-3/4	3-11/32
P309-020C	2	3-9/32	4-3/32
P309-030C	3	4-1/8	5-23/32
P309-040C	4	5-1/32	6-7/16

P319 1/6 Bend (60° EII)


НхН



Part Number	Size	G
P319-015C	1-1/2	1-1/16
P319-020C	2	1-3/8
P319-030C	3	1-11/16
P319-040C	4	2-5/32
P319-060CF	6	4-9/16

P320 1/6 Bend, Street (60° Street EII)

H x Spig




Part Number	Size	G	Н
P320-015C	1-1/2	1-1/16	1-3/4
P320-020C	2	1-5/8	2-1/4
P320-030C	3	1-11/16	3-1/16
P320-040C	4	2-5/32	3-19/32

P321 1/8 Bend (45° EII) H x H

Part Number	Size	G
P321-015C	1-1/2	1-1/8
P321-020C	2	1-9/16
P321-030C	3	1-23/32
P321-040C	4	2-1/8
P321-060C	6	2-1/16
P321-080C	8	2
P321-100C	10	2-5/8
P321-120C	12	3-1/8


P323 1/8 Bend, Street (45° Street Ell)

H x Spig




Part Number	Size	G	Н	
P323-015C	1-1/2	31/32	1-13/16	
P323-020C	2	1-1/2	2-7/16	
P323-030C	3	1-11/16	3-1/4	
P323-040C	4	2-3/16	3-15/16	
P323-060C	6	1-29/32	5-1/16	
P323-080C	8	3-1/8	6-1/2	






Part Number	Size	G
P324-015C	1-1/2	1/2
P324-020C	2	11/16
P324-030C	3	13/16
P324-040C	4	1
P324-060C	6	1-5/16
P324-080C	8	1-11/32


P326 1/16 Bend, Street (22-1/2° Street EII) H x Spig




David November	0:	0	
Part Number	Size	G	Н
P326-015C	1-1/2	1/2	1-1/4
P326-020C	2	11/16	1-1/2
P326-030C	3	13/16	2-5/16
P326-040C	4	1	2-3/4
P326-060C	6	1-3/8	4-1/2
P326-080C	8	1-3/4	5-5/8



Part Number	Size	G1	G2
P327-015C	1-1/2	1-3/4	1-3/4
P327-020C	2	2-5/16	2-5/16
P327-030C	3	3-1/16	3-1/16
P327-040C	4	3-29/32	3-29/32
P327-241C	2x1-1/2x1-1/2	1-3/8	4-1/2




Part Number	Size	G
P331-015C	1-1/2	1-3/16
P331-020C	2	1-1/2
P331-030C	3	1-7/8
P331-040C	4	2-5/16
P331-060C	6	3-15/32





P400 Sanitary Tee


All Hub



Part Number	Size	G1	G2	G3
P400-015C	1-1/2	25/32	1-9/16	1-9/16
P400-020C	2	1-3/8	2-5/16	2-5/16
P400-030C	3	1-13/16	2-7/8	2-7/8
P400-040C	4	2-1/32	3-11/16	3-11/16
P400-060C	6	3-7/16	5-1/32	5-1/32
P400-080C	8	4-13/32	6-1/16	6-1/16
P400-100C	10	5-17/32	9-31/32	9-29/32
P400-120C	12	6-1/2	10-31/32	11-1/32

P401 Sanitary Tee, Reducing


All Hub



Part Number	Size	G1	G2	G3
P401-241C	2x1-1/2x1-1/2	1-3/16	1-15/16	2-3/16
P401-251C	2x2x1-1/2	1-1/4	1-27/32	2-3/16
P401-257C	2x1-1/2x2	1-3/8	2-5/16	2-5/16
P401-337C	3x3x1-1/2	15/16	1-3/4	2-1/2
P401-338C	3x3x2	31/32	1-29/32	2-13/16
P401-420C	4x4x2	7/8	1-27/32	3-5/32
P401-422C	4x4x3	1-11/16	3	3-1/2
P401-532C	6x6x4	2-1/8	3-19/32	4-11/16
P401-582C	8x8x4	4-17/32	5-7/8	8-7/8

P403 Sanitary Tee, Street


SxHxH



Part Number	Size	G1	G2	Н
P403-015C	1-1/2	13/16	1-17/32	2-7/16
P403-030C	3	1-7/8	2-15/16	4-3/8
P403-040C	4	2-1/4	3-7/8	5-5/8
P403-080C	8	4-3/8	5-31/32	9-13/32
P403-100C	10	5-19/32	9-1/2	14-19/32
P403-120C	12	6-15/32	11-1/32	16-9/32

P404 Sanitary Tee, Street, Reducing


SxHxH



Part Number	Size	G1	G2	Н
P404-241C	2x1-1/2x1-1/2	1-7/32	2-7/32	2-9/16
P404-251C	2x2x1-1/2	1-9/32	2-3/16	2-1/2
P404-337C	3x3x1-1/2	13/16	2-15/32	2-15/16
P404-338C	3x3x2	1-1/16	2-3/4	3-7/32

P428 Double Sanitary Tee

All HUB




Part Number	Size	G	G1	G2
P428-015C	1-1/2	1-3/4	1	1
P428-020C	2	2-7/8	1-25/32	1-25/32
P428-030C	3	3-1/16	1-13/16	1-13/16
P428-040C	4	3-7/8	2-1/4	2-1/4



P429 Double Sanitary Tee, Reducing


All Hub



Part Number	Size	G1	G2	G3
P429-241C	2x1-1/2x1-1/2x1-1/2	1-3/16	1-7/8	2-1/16
P429-251C	2x2x1-1/2x1-1/2	1-3/16	1-15/16	2-3/16
P429-337C	3x3x1-1/2x1-1/2	15/16	1-3/4	4
P429-338C	3x3x2x2	1-3/16	2-1/8	2-7/8
P429-419C	4x4x1-1/2x1-1/2	1-1/16	2	5-1/16
P429-420C	4x4x2x2	1-1/8	2-1/16	5-1/16
P429-422C	4x4x3x3	1-3/4	3	5-1/16

P441 Vent Tee


All Hub




Part Number	Size	G
P441-015C	1-1/2	1-5/32
P441-030C	3	1-29/32
P441-040C	4	2-3/8
P441-060C	6	3-5/8

P444X Cleanout Tee w/Plug

H x H x FPT




SEE PART NO. P445 AND P106



Part Number	Size	G	I
P445-015C	1-1/2	1-1/16	5/8
P445-020C	2	1-13/32	5/8
P445-030C	3	1-7/8	3/4
P445-040C	4	2-7/16	7/8
P445-060C	6	3-1/2	1

P445X Cleanout Tee with Counter Sunk Plug


H x H x FPT



SEE PART NO. P445 AND P110

P500 Double Fixture Fitting

All Hub




Part Number	Size	G	G1	G2	G3
P500-020C	2x2x2x2	9/16	3-9/16	3-5/16	3-5/16
P500-241C	2x1-1/2x1-1/2x1-1/2	3/8	3-1/8	2-7/8	2-7/8
P500-251C	2x2x1-1/2x1-1/2	1/8	3-1/4	2-25/32	2-25/32
P500-338C	3x2x3x3	1/2	6-9/32	4-7/8	4-7/8
P500-030C	3x3x3x3	1/2	6-9/32	4-29/32	4-29/32



P501 Combination Wye and 1/8 Bend (Long Turn Tee Wye)


Àll Hub



Part Number	Size	G1	G2	G3	N
P501-015C	1-1/2	3/8	3-7/8	3-7/8	3-1/2
P501-020C	2	5/32	4-1/2	5-1/8	4-13/32
P501-030C	3	1-1/16	7-9/16	7-9/16	6-1/2
P501-040C	4	1/4	8-1/2	9-13/16	8-1/16

P502 Combination Wye and 1/8 Bend, Reducing (Long Turn Tee Wye)


All Hub



Part Number	Size	G1	G2	G3	N
P502-251C	2x2x1-1/2	7/16	3-15/16	4-3/16	3-1/2
P502-337C	3x3x1-1/2	7/16	3-15/16	4-3/4	3-1/2
P502-338C	3x3x2	11/16	5-1/8	5-11/16	4-7/16
P502-420C	4x4x2	5/8	5-1/8	6-1/8	4-1/2
P502-422C	4x4x3	1-1/16	7-9/16	8-1/16	6-1/2

P503 Combination Wye and 1/8 Bend (Two Piece)


All Hub



Part Number	Size	G1	G2	G3	N
P503-060C	6	31/32	10-31/32	11-11/32	10
P503-080C	8	1-1/2	16	16	14-1/2
P503-100C	10	2-1/2	21-7/8	17-15/16	16-9/16

P504 Combination Wye and 1/8 Bend, Reducing (Two Piece)


All Hub



Part Number	Size	G1	G2	G3	N
P504-241C	2x1-1/2	3/32	4-7/16	4-15/32	4-5/16
P504-528C	6x2	15/32	7-9/16	8-27/32	7-3/32
P504-530C	6x3	5/8	7-1/4	8-29/32	7-3/32
P504-532C	6x4	1-5/16	8-3/32	10-3/32	6-27/32
P504-582C	8x4	1-1/4	9-1/4	11-1/8	8
P504-585C	8x6	1	11-5/16	12-7/16	10-7/16
P504-623C	10x3	2-3/8	11-1/16	13-15/16	11-1/16
P504-624C	10x4	1-3/8	12-3/16	14-5/8	10-13/16
P504-626C	10x6	2-1/2	11-3/4	14-1/16	10-13/16
P504-628C	10x8	2-1/2	14-1/2	15-1/2	13-9/16
P504-668C	12x8	3	20-1/8	19-1/8	19-1/8
P504-670C	12x10	3	19-13/16	19-1/2	19-1/8


P507 Double Combination Wye and 1/8 Bend

All Hub





Part Number	Size	G1	G2	G3
P507-020C	2	11/16	5-9/16	5-13/16
P507-030C	3	27/32	7-11/32	7-11/32
P507-040C	4	1-1/8	8-31/32	9-7/32
P507-060C	6	1	11-1/32	11-13/32
P507-338C	3x3x2x2	29/32	5-3/4	6-1/2
P507-422C	4x4x3x3	1-1/16	7-1/2	8-1/8
P507-530C	6x6x3x3	1-1/32	10-7/8	10-7/8
P507-532C	6x6x4x4	1-23/32	11-5/8	12-5/32






Size	G	G1
1-1/2	2-7/8	1-3/32
2	3-5/8	7/8
3	5	1-5/8
4	6-1/4	1-7/8
6	8	1-3/8
8	11-5/16	2
10	14-1/32	2-7/16
12	16-7/16	2-5/32
	1-1/2 2 3 4 6 8	1-1/2 2-7/8 2 3-5/8 3 5 4 6-1/4 6 8 8 11-5/16 10 14-1/32





Part Number	Size	G1	G2	G3
P601-241C	2x1-1/2x1-1/2	3/4	2-15/16	2-15/16
P601-251C	2x2x1-1/2	13/16	3-15/32	3-17/32
P601-337C	3x3x1-1/2	1/2	3-25/32	4-3/8
P601-338C	3x3x2	7/8	4-3/32	4-17/32
P601-419C	4x4x1-1/2	3/8	3-9/32	4-3/8
P601-420C	4x4x2	9/32	4-1/4	5-5/16
P601-422C	4x4x3	21/32	5-1/2	5-29/32
P601-528C	6x6x2	7/32	6-7/8	8-3/8
P601-530C	6x6x3	1-1/8	6	6-7/8
P601-532C	6x6x4	23/32	6-3/16	7-1/8
P601-578C	8x8x2	3/8	7-5/8	9-13/16
P601-580C	8x8x3	7/32	9-1/8	7-11/32
P601-582C	8x8x4	3/8	6-31/32	8-5/16
P601-585C	8x8x6	1	9-1/2	9-13/16
P601-626C	10x10x6	9/32	10-31/32	11-31/32




Part Number	Size	G	G1
P611-015C	1-1/2	2-7/8	1-1/8
P611-020C	2	3-9/16	1-3/8
P611-030C	3	4-15/16	1-5/8
P611-040C	4	6-11/32	1-27/32
P611-060C	6	8-5/16	1-25/32



P612 Double Wye, Reducing


All Hub




Part Number	Size	G1	G2	G3
P612-241C	2x1-1/2x1-1/2x1-1/2	25/32	3-3/8	4-3/16
P612-251C	2x2x1-1/2x1-1/2	1-1/16	3-5-16	3-7/16
P612-337C	3x3x1-1/2x1-1/2	1/2	3-3/4	4-5/16
P612-338C	3x3x2x2	7/8	4-1/16	4-5/8
P612-420C	4x4x2x2	3/8	4-5/8	5-17/32
P612-422C	4x4x3x3	1-1/2	5-1/32	5-9/32
P612-532C	6x6x4x4	3/16	6-11/16	7-7/16

P700 Return Bend

НхН




Part Number	Size	G
P700-015C	1-1/2	1-13/32
P700-020C	2	2-3/8
P700-030C	3	3
P700-040C	4	3-7/16
P700-060C	6	5



Part Number	Size	L
P704P-015C	1-1/2	2-1/2




НхН



Part Number	Size	G	G1	G2
P705-015C	1-1/2	7-1/2	1-3/4	2-3/8
P705-020C	2	14-1/2	2-3/8	3-13/32
P705-030C	3	15-1/2	3-3/16	4-7/16
P705-040C	4	19-1/16	3-7/8	5-9/16


P705R Running Trap

НхН





Part Number	Size	G	G1
P705R-015C	1-1/2	8	3-3/4
P705R-020C	2	12-1/2	5-7/16
P705R-030C	3	17-1/8	7-21/32
P705R-040C	4	20-7/8	9-9/32








Part Number	Size	G	G1	G2
P706X-015C	1-1/2	4-3/16	3-29/32	1-13/32
P706X-020C	2	6-7/16	4-21/32	2-11/32
P706X-030C	3	8-11/16	6-15/16	3-1/32
P706X-040C	4	11-1/32	8-1/8	3-23/32
P706X-060C	6	18-25/32	14-3/4	5-13/16
P706X-080C	8	22	17	6-3/4















Flange - Van Stone Style




Part Number	Size	L	M	N	R	No. of Bolt Holes	Bolt Circle Dia.	Bolt Size	Min. Bolt Length	Max O.D.
854-015C	1-1/2	1-17/32	2-7/16	3/16	3/4	4	3-7/8	1/2	2-1/2	5
854-020C	2	1-11/16	2-15/16	3/16	13/16	4	4-3/4	5/8	3	6
854-030C	3	2-1/8	4-1/4	1/4	1-1/16	4	6	5/8	3-1/4	7-1/2
854-040C	4	2-1/2	5-1/4	1/4	1-1/8	8	7-1/2	5/8	3-1/2	9
854-060C	6	3-3/8	7-9/16	7/16	1-9/32	8	9-1/2	3/4	4	11
854-080C	8	4-3/8	9-5/16	9/32	1-3/8	8	11-3/4	3/4	4-1/2	13-1/2
854-100C	10	5-11/16	11-3/4	21/32	1-5/8	12	14-1/4	7/8	5	16
854-120C	12	7-1/4	13-3/4	5/8	1-1/2	12	17	7/8	5	19
854-140C	14	7-1/2	15-1/2	1/2	2	12	18-3/4	1	5-1/2	21
854-160C	16	8-3/4	17-3/4	3/4	2-3/8	16	21-1/4	1	6-1/2	23-1/2

P720 Drum Trap H x H




Part Number	Size	G	G1	L
P720-015C	1-1/2	3-5/8	5-11/16	10-5/8
P720-020C	2	3-7/8	5	10-3/8
P720-030C	3	4-1/2	6-3/4	13-7/16
P720-040C	4	4-3/8	8-1/4	15-11/16






LW1500 Floor Drain with CPVC Adjustable Top w/5" Round Grate




Part Number Regular	Size	IPS	С
LW1500-015C	1-1/2x5	1-1/2	4-3/16
LW1500-020C	2x5	2	4
LW1500-030C	3x5	3	4
LW1500-040C	4x5	4	3-3/4

LW150M Floor Drain with CPVC Adjustable Top w/5" Round Grate & Membrane Collar




Part Number Membrane Plate	Size	С
LW150M-015C	1-1/2x5	4-3/16
LW150M-020C	2x5	4
LW150M-030C	3x5	4
LW150M-040C	4x5	3-3/4

LW1520 Floor Drain with CPVC Adjustable Top w/5" Round Grate & Strainer



Part Number	Size	IPS	С
LW1520-015C	1-1/2x5	1-1/2	4-3/16
LW1520-020C	2x5	2	4
LW1520-030C	3x5	3	4
LW1520-040C	4x5	4	3-3/4


LW152M Floor Drain with CPVC Adjustable Top w/5" Round Grate, Strainer & Membrane Collar



Part Number Regular	Size	IPS	C
LW152M-015C	1-1/2x5	1-1/2	4-3/16
LW152M-020C	2x5	2	4
LW152M-030C	3x5	3	4
LW152M-040C	4x5	4	3-3/4




Floor Drain with Stainless Steel Adjustable Top w/Round Grate



Part Number Regular	Size	A, Nom	IPS	С
LW1500-015S	1-1/2x5	5	1-1/2	4-3/16
LW1600-015S	1-1/2x6	6	1-1/2	4-3/16
LW1700-015S	1-1/2x7	7	1-1/2	4-3/16
LW1800-015S	1-1/2x8	8	1-1/2	4-3/16
LW1500-020S	2x5	5	2	4
LW1600-020S	2x6	6	2	4
LW1700-020S	2x7	7	2	4
LW1800-020S	2x8	8	2	4
LW1500-030S	3x5	5	3	4
LW1600-030S	3x6	6	3	4
LW1700-030S	3x7	7	3	4
LW1800-030S	3x8	8	3	4
LW1500-040S	4x5	5	4	3-3/4
LW1600-040S	4x6	6	4	3-3/4
LW1700-040S	4x7	7	4	3-3/4
LW1800-040S	4x8	8	4	3-3/4


Floor Drain with Stainless Steel Adjustable Top w/Round Grate & Membrane Collar



Part Number Membrane	Size	A, Nom	IPS	С
LW150M-015S	1-1/2x5	5	1-1/2	4-3/16
LW160M-015S	1-1/2x6	6	1-1/2	4-3/16
LW170M-015S	1-1/2x7	7	1-1/2	4-3/16
LW180M-015S	1-1/2x8	8	1-1/2	4-3/16
LW150M-020S	2x5	5	2	4
LW160M-020S	2x6	6	2	4
LW170M-020S	2x7	7	2	4
LW180M-020S	2x8	8	2	4
LW150M-030S	3x5	5	3	4
LW160M-030S	3x6	6	3	4
LW170M-030S	3x7	7	3	4
LW180M-030S	3x8	8	3	4
LW150M-040S	4x5	5	4	3-3/4
LW160M-040S	4x6	6	4	3-3/4
LW170M-040S	4x7	7	4	3-3/4
LW180M-040S	4x8	8	4	3-3/4




LW1510 Floor Cleanout w/Stainless Steel Adjustable Round Top & Solid Access Cover



Part Number Regular	Size	IPS	С
LW1510-015S	1-1/2x5	1-1/2	4-3/16
LW1510-020S	2x5	2	4
LW1510-030S	3x5	3	4
LW1510-040S	4x5	4	3-3/4

LW151M Floor Cleanout w/Stainless Steel Adjustable Round Top, Solid Access Cover & Membrane Collar



Part Number Membrane Plate	Size	IPS	С
LW151M-015S	1-1/2x5	1-1/2	4-3/16
LW151M-020S	2x5	2	4
LW151M-030S	3x5	3	4
LW151M-040S	4x5	4	3-3/4

LW LabWaste Pipe 10' Lengths



Part Number	Pipe Dia. (inches)	Avg. O.D.	Avg. I.D.	Min. Wall
LW-015	1-1/2x10	1.900	1.592	.145
LW-020	2x10	2.375	2.049	.154
LW-030	3x10	3.500	3.042	.216
LW-040	4x10	4.500	3.998	.237
LW-060	6x10	6.625	6.031	.280
LW-080	8x10	8.625	7.943	.322
LW-100	10x10	10.750	9.976	.365
LW-120	12x10	12.750	11.890	.406

Solvent Cement Yellow-Heavy Bodied



Part Number	Size			
LW5-030	Quart			
LW5-040	Gallon			

Average Number of Joints per Quart of Solvent Cement

Pipe Diameter	Number of Joints
1-1/2"	90
2"	60
3"	40
4"	30
6"	10
8"	5
10"	2 - 3
12"	1 - 2

Note: These figures are based on laboratory tests. Due to many field variations, these should be used as a general guide only.



Standard HDPE Round Neutralization/Dilution Tanks

Construction: HDPE - High Density Polyethylene

Tank	Approx. Capacity, U		Inside Dimension	Wall	Approx.	Standard Inlet & Outlet	Standard	LabWaste™ Transition	Optional Vent	Approx	Centerlin	e Height
Capacity US Gallions	Without Liimestone	With Limestone	Dia x Ht. Thickness Weight (lbs.) Connection Size Connection	•	Connection Fitting	Connection Size (in.)	Inlet	Outlet	Vent			
5	3	1	11 x 14	3/16	10	1-1/2 or 2	Mipt	P101	1-1/2 or 2	11	8	12
15	7	2	18 x 15	3/16	20	1-1/2 or 2	Mipt	P101	1-1/2 or 2	11	8	12
30	19	6	18 x 29	3/16	35	3	Mipt	P101	2 or 3	23	19	25
55	35	12	22 x 36	3/16	50	4	Mipt	P101	3 or 4	27	23	31
100	77	26	28 x 42	1/4	85	4	Mipt	P101	3 or 4	35	31	37
150	105	35	31 x 48	1/4	100	4	Mipt	P101	3 or 4	38	34	42
175	135	45	30 x 60	1/4	125	4	Mipt	P101	3 or 4	51	47	54
200	137	46	36 x 48	1/4	125	4 or 6	Mipt/Flange	P101/854	4 or 6	38	34	42
275	186	62	42 x 48	1/4	160	4 or 6	Mipt/Flange	P101/854	4 or 6	38	34	42
300	230	76	36 x 74	5/16	175	4 or 6	Mipt/Flange	P101/854	4 or 6	61	56	65
350	243	81	48 x 48	5/16	200	4 or 6	Mipt/Flange	P101/854	4 or 6	38	34	42
500	395	132	52 x 60	3/8	225	4 or 6	Mipt/Flange	P101/854	4 or 6	51	47	54
550	447	149	48 x 72	3/8	275	4 or 6	Mipt/Flange	P101/854	4 or 6	64	60	67
650	548	183	48 x 84	3/8	375	4 or 6	Mipt/Flange	P101/854	4 or 6	75	71	76
1200	1052	351	69 x 84	3/8	600	4 or 6	Mipt/Flange	P101/854	4 or 6	74	68	76
2000 ¹	1559	521	84 x 84	1/2	850	4 or 6	Mipt/Flange	P101/854	4 or 6	74	68	76
3000 ¹	2203	735	95 x 97	1/2	1350	4 or 6	Mipt/Flange	P101/854	4 or 6	87	83	91

Standard CPVC Round Neutralization/Dilution Tanks

Construction: Chlorinated Polyvinyl Chloride (CPVC)


Tank		Useable US Gallons	Inside Dimension	Wall Thickness	Approx. Weight	Standard ² Inlet & Outlet	Standard Fitting	LabWaste ™ Transition	Optional⁴ Vent		ox. Cent leight (in	
Capacity US Gallions	Without Limestone	With Limestone	Dia. x Ht. (in.)	(in.)	(lbs.)	Connection Size (in.)	Connection	Connection Fitting ³	Connection Size (in.)	Inlet	Outlet	Vent
5	5	3	12-3/8 x 14-11/16	3/16	20	1-1/2 or 2	Socket	Direct	1-1/2 or 2	11	8	12
15	15	7	17-11/16 x 17-1/4	3/16	35	1-1/2 or 2	Socket	Direct	1-1/2 or 2	11	8	12
30	30	18	17-5/8 x 33	3/16	54	3	Socket	Direct	2 or 3	23	18	25
55	55	35	23-1/2 x 38-1/2	1/4	70	4	Socket	Direct	3 or 4	27	23	31


Important Notes

- 1 Larger HDPE tanks may include exterior steel banding or fiberglass reinforcement for additional strength. Special ordered optional inspection manhole ports are recommended for larger tanks (includes cover with neoprene gasket, stainless steel nuts, bolts, and washers).
- 2 All tanks can be special ordered with Mipt, Flanged (CL150), and Fipt connections or varying combinations other than standard connections specified. Inlets or vents may also be custom ordered for installation in covers instead of tank sides.
- 3 For transitions from Mipt HDPE tank connections to **LabWaste™** piping use part numbers P101-xxxC, Female Adapter. CPVC tank sockets can be cemented directly to **LabWaste™** piping. For transitions from ALL flanged connections to **LabWaste™** piping use part numbers 854-xxxC, Flange (xxx = size code).
- 4 Venting is required by codes but may be accomplished either at the tank or in-line.
- 5 Neutralization tanks and tank extensions are not warranted for direct burial applications. Tanks must be properly placed and secured with no applied stresses, within a dry concrete vault with use of a protective traffic cover as deemed appropriate. However, if direct burial is used without warranty, custom centerlines must be furnished from top of cover down to fitting centerline instead of specified tank bottom to fitting centerline since tank heights can vary.



HDPE Tanks







TOP VIEW STANDARD FITTING LOCATIONS



Standard Locations Changed)


CPVC Tanks







1-Gallon CPVC Dilution Tanks

Provides chemical dilution from water rinse during use. Designed for under-sink installations. CPVC construction with Glass or PP Jar type tank.









Chemical Resistance Information

CPVC is inert to most acids, bases, salts, plus a wide variety of organic compounds. Application conditions including chemical concentration and temperature must be taken into consideration. Due to the many variables involved, final suitability often must be based on in-service testing.

The following Chemical Resistance Table recommendations apply only to non-pressure, laboratory drainage applications, which are those characterized as the routine disposal of a wide variety of hot and cold chemicals in relatively small quantities accompanied by water for the purpose of dilution and flushing. For use of **LabWaste**TM CPVC products in continuous or dedicated chemical waste drainage systems, chemical resistance data for pressure applications must be followed. Contact Spears® Technical Services for additional information.

In many cases compatibility or solubility data is not available. While specific data may not be available, please note that virtually all aqueous solutions of chemicals used in a laboratory can be safely used with proper dilution and flushing. This includes chemicals that readily disperse in water (such as many fat-soluble vitamins and oils) that can be flushed during disposal.

This information is compiled from commercially available industry sources. It is offered in good faith and believed to be accurate at the time of its preparation, but is offered without any warranty, expressed or implied, by information sources or Spears® Manufacturing Company. These recommendations are guidelines for use and the final decision regarding material suitability must rest with the end-user.

Noted Caution Areas for CPVC

- Disposed chemicals must be properly diluted. Chemicals that individually have no affect may have an affect when used in combination. Due to the wide variety of potential chemical concentrations and combinations, testing under actual service conditions is highly recommended.
- CPVC is not recommended for use with chlorinated solvents. Most solvents are prohibited by law from disposal in drainage systems.
- Chemicals that do not normally affect CPVC may cause cracking when excessive stress is applied. Tests under applied adverse stress conditions indicate that environmental stress cracking may occur when exposed to surfactants, certain oils, or grease. Such stresses include external stresses from expansion/contraction and installation. Special consideration should be taken during design and installation to avoid unusual stresses in the piping system.
- Chemical resistance of plastics tends to decrease with an increase in chemical concentration and/or temperature. As a result, various chemicals may be safely handled in limited concentrations or within certain temperature limits. Most all aqueous solutions of water-soluble chemical not specified in the Chemical Resistance Tables can be used in CPVC drainage systems.
- While **LabWaste**TM CPVC products are suitable for many continuous commercial and industrial chemical waste applications, the following Chemical Resistance Tables should **NOT** be used for these applications. Consult chemical resistance data for CPVC pressure piping to determine suitability for continuous chemical waste drainage applications.

WARNING: Hazardous material (including certain solvents and high concentrations of certain acids), are typically not discharged into lab waste piping. Laboratories routinely have specialized collection equipment and contracted disposal services for waste considered "hazardous". Proper laboratory protocols on handling materials identified by OSHA and EPA as "hazardous" must be established and followed. Such requirements typically specify special storage and disposal apart from drainage disposal via dilution or neutralization. Even improper handling and disposal of HAZARDOUS materials by accident are subject to heavy fines by Federal, State and Local Authorities.



Chemical Resistance Tables

Resistance Rating Codes

 $\mathbf{R} = \text{Recommended}$

 \mathbf{C} = Use with Caution.

N = Not Recommended.

--- = No data available

RATING

CHEMICAL

CHEMICAL

IMPORTANT NOTE: Chemical Resistance data is provide for material compatibility information purposes only and in no way addresses the legal discharge of chemicals into any waste system, some of which may be prohibited by law. Nor does the data address the compatibility of chemical mixtures, issues of hazardous decomposition, or other potentially dangerous circumstances that might be involved. Data is applicable to laboratory drainage systems only and may not be suitable for continuous service or pressure applications.

RATING

HEWICAL	KATING	CHEWICAL	KATING	CHEWICAL	KATINO
A		Ammonium Nitrate	R	Bromphenol Blue	R
A		Ammonium Persulfate	R	Bromthymol Blue	R
		Ammonium Phosphate		Butadiene	R
cacia, Gum Arabic	R	Monbasic/Dibasic	R	Butane	R
etaldehyde	R		R		C
etamide	R	Ammonium Sulfate		Butyl Acetate	
		Ammonium Sulfide	R	Butyl Alcohol	С
etic Acid Vapor 25%	R	Ammonium Sulfite	R	Butyl Cellosolve	R
etic Acid 60%	R	Ammonium Thiocyanate	R	n-Butyl Chloride	
etic Acid 85%	R	Amyl Acetate	C	Butylene (C)	
ectic Acid Glacial	R	Amyl Alcohol 1%	R	Butyl Phenol	С
etic Anhydride	R				
etone	R	Amyl Alcohol >1%	С	Butyl Phthalate	
		n-Amyl Chloride	С	Butyl Stearate	
cetophenone	С	Aniline	С	Butynediol	
cetyl Chloride	R	Aniline Chlorohydrate	С	Butyric Acid	R
cetylene	N	Aniline Hydrochloride	С	Ċ	
etylnitrile	R	Anthraguinone	Ř		
etylsalicylic acid, aspirin	R		K		
	R	Anthraquinone	_	Cadium Cyanide	R
rylic Acid		Sulfonic Acid	R	Calcium Acetate	R
rylonitrile	R	Antimony Trichloride	R		
lenine, 6-aminopurine	R	Agua Regia	R	Calcium Bisulfide	R
denosine Triphosphate	R	Argon		Calcium Bisulfate	R
dipic Acid	R	Arsenic Acid	R	Calcium Carbonate	R
garose	R			Calcium Chlorate	R
	п	Aryl Sulfonic Acid	R	Calcium Chloride	R
izarin stain		Asorbic Acid	R		R
Mordant Red 11	R	L-Asparagine	R	Calcium Fluoride	
izarin Red S		Asphalt	N	Calcium Hydroxide	R
Mordant Red 3	R			Calcium Hypochlorite	R
zarin Yellow R		В	5	Calcium Nitrate	R
Mordant Orange 1	R			Calcium Oxide	R
		Barium Acetate	R	Calcium Sulfate	R
yl Alcohol	R				
yl Chloride	N	Barium Carbonate	R	Camphor	
uminum Acetate	R	Barium Chloride	R	Cane Sugar Liquors	R
uminum Ammonium	R	Barium Hydroxide	R	Caprylic Acid	
uminum Chloride	R	Barium Nitrate	R	Carbitol	
uminum Fluoride	R	Barium Sulfate	R	Carbolic Acid	R
		Barium Sulfide	R	Carbon Dioxide Dry	R
uminum Hydroxide	R				
uminum Nitrate	R	Beer	R	Carbon Dioxide Wet	R
uminum Oxychloride	R	Beer Sugar Liquors	R	Carbon Disulfide	C
uminum Potassium	R	Benzaldehyde	R	Carbon Monoxide	R
uminum Potassium Sulfate, Alum	R	Benzene	С	Carbon Tetrachloride	N
	R	Benzene Sulfonic Acid	Ř	Carbonic Acid	R
uminum Sulfate					
nmonia Anhydrous	R	Benzoic Acid	R	Castor Oil	C
nmonia Gas	R	Benzyl Alcohol	R	Caustic Potash	R
nmonia Liquid	R	Bismuth Carbonate	R	Caustic Soda	R
nmonia Acetate	R	Biuret	R	Cellosolve	С
nmonium Bicarbonate	R	Black Liguor	R	Cellosolve Acetate	R
		Bleach 5%	R		R
nmonium Biflouride	R			Chloral Hydrate	
nmonium Bisulfide	R	Bleach 12%	R	Chloramine	R
nmonium Bromide	R	Blood	R	Chloric Acid	R
mmonium Carbonate	R	Borax	R	Chloric Acid 20%	R
mmonium Chloride	R	Boric Acid	R	Chlorine, Aqueous	R
mmonium Citrate	R	Brake Fluid		Chlorinated Water 10 PPM	R
		Brine	 R	Chlorinated Water Sat'd	R
nmonium Dichromate	R				
nmonium Dihydrogen		Brilliant Blue G-250	R	Chloroacetic Acid	R
Phosphate	R	Brilliant Blue R-250	R	Chloroacetyl Chloride	
nmonium Ferric Sulfate	R	Brilliant Cresyl Blue	R	Chlorobenzene	N
monium Ferrous Sulfate	R	Brilliant Green	R	Chlorobenzyl Chloride	N
			R		N N
mmonium Fluoride 10%	R	Bromcresal Green		Chloroform	
nmonium Fluoride 25%	R	Bromcresal purple	R	Chlorophenol Red	R
mmonium Hydroxide		Bromic Acid	R	Chloropicrin	
10% - 28%	R	Bromine Liquid	R	Chlorosulfonic Acid	R
mmonium Hydroxide	1.	Bromine Vapor	R	Chromic Acid 10%	R
	R	Bromine Water			R
		promine vyater	R	Chromic Acid 30%	R
100% nmonium lodide	R	Bromotoluene		Chromic Acid 40%	R

RATING

CHEMICAL



CHEMICAL	RATING	CHEMICAL	RATING	CHEMICAL	RATING
Ob	0	Ethyl Ether	R	Hydrogen Sulfide Dry	R
Chromic Acid 50%	C R	Ethyl Formate	R	Hydrogen Sulfide Wet	R
Chromium Tetroxide	R R	Ethylene Glycol	R	Hydrogen Sulfide, aqueous	R
Citric Acid	R R	2- Ethylhexanol	R	Hydroquinone, aqueous	R
Clayton Yellow	R	Ethyl Mercaptan	R	Hydroxylamine Hyrochloride	R
Coconut Oil	С	Ethyl Oxalate	R	Hydroxylamine Sulfate	R
Coffee	R	F		Hypochlorous Acid	R
Congo Red solution	R	·			
Copper Acetate	R	Fast Green FCF	R		
Copper Carbonate	R	Fatty Acids	R	Indigo Carmine	R
Copper Chloride	R	Fehlings solution A	R	Inks	R
Copper Cyanide	R	Fehlings solution B	R	lodine	R
Copper Fluoride	R R	Ferric Ammonium Sulfate	R	lodine solution, Lugol's	R
Copper Nitrate Copper Sulfate	R	Ferric Chloride	R	Iron Phosphate	
Corn Oil	C	Ferric Hydroxide	R	Isobutane	С
Corn Syrup	Ř	Ferric Nitrate	R	Isobutyl Alcohol	R
Cottonseed Oil	C	Ferric Sulfate	R	Isooctane Isopropyl Acetate	R R
m-Cresal Purple	R	Ferrous Chloride	R	Isopropyl Alcohol	R
Cresal Red	R	Ferrous Hydroxide Ferrous Nitrate	R R	Isopropyl Chloride	N
Creosote	N	Ferrous Sulfate	R	Isopropyl Ether	R
Cresol	N	Fish Oil	R	Isophorone	R
Cresylic Acid	R	Fluoboric Acid	R	J	
Croton Aldehyde	R	Fluorine Gas (Dry)	R		·
Crude Oil	R	Fluorine Gas (Wet)	R	larena C	
Cumene Cunria Chlorida	С	Fluosilicic Acid 30%	R	Janus Green	R
Cupric Chloride Cupric Fluoride	R R	Fluosilicic Acid 50%	R	JP-3 Fuel JP-4 Fuel	R R
Cupric Nitrate	R R	Flormaldehyde Dilute	R	JP-4 Fuel JP-5 Fuel	R R
Cupric Sulfate	R	Flormaldehyde 35%	R	JP-6 Fuel	R R
Cuprous Chloride	R	Flormaldehyde 37%	R	K	
Cyclohexane	R	Flormaldehyde 50%	C	N	\
Cyclohexanol	R	Formic Acid	R		
Cyclohexanone	R	Freon Freon 12	R R	Kerosene	R
D		Freon 21		Ketchup	R
		Freon 22	R	Kraft Liquors	R
Decahydronapthalene	R	Freon 113	C	L	-
Detergents	R	Freon 114			
Dexin	R	Fructose	R	Lactic Acid 25%	R
Dextrose	R	Furfural	R	Lactic Acid 80%	R
Diacetone Alcohol	R	G		Lactose	R
Diastase of malt	R			Lard Oil	С
Dibutoxyethyl Phthalate	N	Gallic Acid	R	Latex	
Dibutyl Ether	R	Gasoline	R	Lauric Acid Lauryl Chloride	R R
Dibutyl Phthalate	N	Gasohol	R	Lead Acetate	R R
Dibutyl Sebacate	N	Gelatin	R	Lead Chloride	R
Dichlorobenzene	R	Glauber's Salt		Lead Nitrate	R
Dichloroethylene 2,6 – Dichloroindophenal	N R	Glucose	R	Lead Sulfate	R
Diesel Fuels	R	Glue, PVA	R	Lemon Oil	R
Diethylamine	R	Glutathione	R	Ligroin	R
Diethyl Cellosolve	R	Glycerine	R	Limonene	R
Diethyl Ether	R	Glycine	R	Lime Slurry	R
Diglycolic Acid	R	Glycogen	R	Lime Sulfur	R
Dimethylamine	R	Glycol	С	Linoleic Acid	С
Dimethyl Formamide	R	Glycol Amine Glycolic Acid	 R	Linoleic Oil	
Dimethylhydrazine	R	Glyoxal	R R	Linseed Oil	C R
Dimethyl Phthalate	N	Grape Sugar	R	Liqueurs Lithium Bromide	R R
Dimethyl Sulfoxide	R	Grease		Lithium Bromide Lithium Carbonate	R R
Dioctyl Phthalate	N R	Green Liquor	R	Lithium Chloride	R
Dodecyl Alcohol Dodecyl Sulfate	R R	Н		Lithium Hyrdroxide 50%	R
Dioxane	R R			Lithium Nitrate	R
Diphenyl Oxide		Heptane (Type 1)	R	Lithium Sulfate	R
Disodium Phosphate	R	n-Hexane	R R	Lubricating Oil #1	R
Drierite	R	Hexamethylenediamine	R	Lubricating Oil #2	R
E		Hexanol, Tertiary	R	Lubricating Oil #3	R
		Hydraulic Oil		Ludox	
Ecoin V	п	Hydrazine	R	Luminol 3-amino	Б
Eosin Y Eriochrome Black T	R R	Hydrobromic Acid 20%	R	Phthalhydrazide DL-lysine Hydrochloride	R R
Ether	R R	Hydrobromic Acid 50%	R	Lysozyme	R R
Ethyl Acetate	R	Hydrochloric Acid 10%	R		
Ethyl Acetoacetate	R	Hydrochloric Acid 30%	R	N	1
Ethyl Acrylate	R	Hydrocyanic Acid	R		
Ethyl Alcohol	R	Hydrofluoric Acid Dilute	R	Magnesium Acetate	R
Ethyl Benzene	C	Hydrofluoric Acid 50%	R	Magnesium Bromide	R
Ethyl Chloride	N	Hydrofluoric Acid 50%	R R	Magensium Carbonate	R
Ethyl Chloroacetate	N	Hydrofluoric Acid 100% Hydrofluosilic Acid 50%	R R	Magnesium Chloride	R
Ethylene Bromide	N	Hydrogen	R R	Magnesium Citrate	R
Ethylene Chloride	N	Hydrogen Cyanide	R	Magnesium Hydroxido	 R
Ethylene Chlorohydrin	N	Hydrogen Fluoride	C	Magnesium Hydroxide	R R
Ethylenediamine	R	Hydrogen Peroxide 50%	R	Magnesium Nitrate	
Ethylene Dichloride	N	Hydrogen Peroxide 90%	R	Magnesium Oxide Magnesium Sulfate	 R
Ethylene Glycol	С	Hydrogen Phosphide	R	Malachite Green	R R
Ethylene Oxide	R			manasino ordon	11



CHEMICAL	RATING	CHEMICAL	RATING	CHEMICAL	RATING
Maleic Acid	R	Orange IV - acid orange 5	R	Potassium Nitrite	R
Malic Acid	R	Orcinol	R	Potassium Perborate	R
Maltose	R	Osmium Tetroxide	R	Potassium Perchlorate	R
Manganese Chloride	R	Oxalic Acid	R	Potassium Permanganate 10%	R
Manganese Nitrate	R	Oxygen Gas	R	Potassium Permanganate 25%	R
Manganese Sulfate	R	Ozone	R	Potassium Persulfate	R
Menthol	R	Ozonized Water	R	Potassium Phosphate	R
Mercuric Chloride	R	P		Potassium Sodium Tartrate	R
Mercuric Cyanide	R	-		Potassium Sulfate	R
Mercuric Sulfate	R	Palm Oil	R	Potassium Sulfide	R
Mercurous Nitrate	R	Palmitic Acid 10%	R	Potassium Sulfite	R
Mercury	R	Palmitic Acid 70%	R	Potassium Thiocyanate	R
Methane Methanol	R	Pancreatin	R	Propane	R R
DL-methionine	R R	Papain	R	Propargyl Alcohol Propionic Acid	R R
Methoxyethyl Oleate		Paraffin	R	Propyl Acetate	
Methyl Acetate	R	Peanut Oil	С	Propyl Alcohol	R
Methyl Acetone	R	Pectin	R	N-Propyl Bromide	
Methyl Acrylate		n-Pentane	С	Propylene Dichloride	N
Methyl Amine	R	Pepsin	R R	Propylene Glycol	R
Methyl Bromide	N	Peracetic Acid Perchloric Acid 15%	R R	Propylene Oxide	R
Methyl Cellosolve	R	Perchloric Acid 15% Perchloric Acid 70%	R	Pyridine	R
Methyl cellulose	R	Perchloroethylene	C	Pyrogallic Acid	R
Methyl Chloride	N	Periodic Acid	R	Pyrrole	R
Methyl Chloroform	N	Perphosphate	R	Q	
Methyl Ethyl Ketone	R R\	Phenol	R		
Methyl Formate Methyl Green	R R	Phenolphthalein	R	Quinine Sulfate	R
Methyl Isobutyl Carbinol	R R	Phenyl Salicylate	R	Quinine Chloride Dihydrate	R
Methyl Isobutyl Ketone	R	Phenylhydrazine	С	Quinone	
Methyl Isopropyl Ketone	R	Phosphate Esters		R	
Methyl Methacrylate	R	Phosphoric Acid 10%	R		
Methyl Red	R	Phosphoric Acid 50%	R	Rayon Coagulating Bath	R
Methyl Sulfate	R	Phosphoric Acid 85%	R R	Rennin	R
Methyl Violet-2B	R	Phosphoric Anhydride Phosphorous (Red)	C	Resazurin	R
Methyl Violet-6B	R	Phosphorous (Yellow)	C	Ringers Solution	R
Methylene Blue	R	Phosphorous Pentoxide	Ř	Rose Bengal Acid Red 94	R
Methylene Bromide	N	Phosphorous Trichloride	R	•	
Methylene Chloride	N N	Photographic Solutions	R	S	
Methylene Chlorobromide Methylene Iodine	N N	Phthalic Acid	R		
Methysulfuric Acid	R	Picric Acid	R	Safranin O	R
Milk	R	Pine Oil	С	Salicylaldehyde	N
Mineral Oil	R	Plating Solutions Brass	R	Salicylic Acid	R
Molasses	R	Plating Solutions Cadium	R	Selenic Acid, Aq.	R
Monochloroacetic Acid	R	Plating Solutions Chrome	R	Silicic Acid	R
Monochlorobenzene	N	Plating Solutions Copper Plating Solutions Gold	R R	Silicone Oil	R
Monoethanolamine	R	Plating Solutions Lead	R	Silver Acetate	R
Monosodium Glutamate	R	Plating Solutions Nickel	R	Silver Chloride	R
Motor Oil	R	Plating Solutions Rhodium	R	Silver Cyanide	R
Morpholine	R	Plating Solutions Silver	R	Silver Nitrate Silver Sulfate	R R
N		Plating Solutions Tin	R	Soaps	R
		Plating Solutions Zinc	R	Sodium Acetate	R
Naphtha	R	Polyvinyl Acetate		Sodium Alum	R
Naphthalene	С	Polyvinyl Alcohol	R	Sodium Aluminate	R
Natural Gas	R	Potash	R	Sodium Arsenate	R
Neutral Red	R	Potassium Acetate Potassium Alum	R R	Sodium Benzoate	R
Nickel Acetate	R	Potassium Alum Potassium Aluminum		Sodium Bicarbonate	R
Nickel Ammonium Sulfate Nickel Chloride	R	Potassium Bicacbonate	R R	Sodium Bichromate	R
Nickel Nitrate	R	Potassium Bichromate	R	Sodium Bisulfate	R
Nickel Sulfate	R	Potassium Bisulfate	R	Sodium Bisulfite Sodium Borate	R R
Nicotine	R	Potassium Bitartrate	R	Sodium Borate Sodium Bromide	R R
Nicotinic Acid	R	Potassium Borate	R	Sodium Bromide Sodium Carbonate	R R
Nitric Acid 10%	R	Potassium Bromate	R	Sodium Carbonate Sodium Chlorate	R
Nitric Acid 30%	R	Potassium Bromide	R	Sodium Chloride	R
Nitric Acid 40%	R	Potassium Carbonate	R	Sodium Chlorite	R
Nitric Acid 50%	R	Potassium Chlorate	R	Sodium Chromate	R
Nitric Acid 70%	R	Potassium Chromete	R	Sodium Citrate	R
Nitric Acid 100% Nitrobenzene	R	Potassium Chromate Potassium Citrate	R R	Sodium Cyanide	R
Nitrobenzene Nitroethane	N C	Potassium Citrate Potassium Cyanide	R R	Sodium Dichromate	R
Nitroetnane Nitrogen Gas		Potassium Dichromate	R	Sodium Diphenylamine	_
Nitroglycerine	C	Potassium Ethyl Xanthate		Sulfonate	R
Nitroglycol		Potassium Ferricyanide	R	Sodium Dithionite	R R
Nitromethane	С	Potassium Ferroycanide	R	Sodium Ferricyanide Sodium Ferrocyanide	R R
		Potassium Fluoride	R	Sodium Fluoride	R
Nitrous Acid	R				
	R R	Potassium Hydrogen			
Nitrous Acid		Potassium Hydrogen Phosphate	R	Sodium Hexametaphosphate	R
Nitrous Acid Nitrous Oxide		Potassium Hydrogen Phosphate Potassium Hydrogen			
Nitrous Acid Nitrous Oxide	R	Potassium Hydrogen Phosphate Potassium Hydrogen Phthalate	R	Sodium Hexametaphosphate Sodium Hydroxide 15%	R R
Nitrous Acid Nitrous Oxide O n-Octane	R C	Potassium Hydrogen Phosphate Potassium Hydrogen Phthalate Potassium Hydroxide	R R	Sodium Hexametaphosphate Sodium Hydroxide 15% Sodium Hydroxide 30% Sodium Hydroxide 50% Sodium Hydroxide 70%	R R R R
Nitrous Acid Nitrous Oxide	R	Potassium Hydrogen Phosphate Potassium Hydrogen Phthalate Potassium Hydroxide Potassium Hyprochlorite	R R R	Sodium Hexametaphosphate Sodium Hydroxide 15% Sodium Hydroxide 30% Sodium Hydroxide 50% Sodium Hydroxide 70% Sodium Hydroxide 70%	R R R R R
Nitrous Acid Nitrous Oxide On-Octane Octanol	R C R	Potassium Hydrogen Phosphate Potassium Hydrogen Phthalate Potassium Hydroxide Potassium Hyprochlorite Potassium lodate	R R R R	Sodium Hexametaphosphate Sodium Hydroxide 15% Sodium Hydroxide 30% Sodium Hydroxide 50% Sodium Hydroxide 70% Sodium Hypochlorite Sodium Hodate	R R R R R R
Nitrous Acid Nitrous Oxide O n-Octane Octanol Oleic Acid	R C R R	Potassium Hydrogen Phosphate Potassium Hydrogen Phthalate Potassium Hydroxide Potassium Hyprochlorite	R R R	Sodium Hexametaphosphate Sodium Hydroxide 15% Sodium Hydroxide 30% Sodium Hydroxide 50% Sodium Hydroxide 70% Sodium Hydroxide 70%	R R R R R



CHEMICAL	RATING
Sodium Metaphosphate	R
Sodium Nitrate	R
Sodium Nitrite	R
Sodium Palmitrate	R
Sodium Perborate	R
Sodium Perchlorate	R
Sodium Periodate	R
Sodium Peroxide	R
Sodium Phosphate Acid	R
Sodium Phosphate Alkaline	R
Sodium Phosphate Neutral	R
Sodium Propionate	R
Sodium Silicate	R
Sodium Sulfate	R
Sodium Sulfide	R
Sodium Sulfite	R
Sodium Thiousulphate	R
Sour Crude Oil	R
Soybean Oil	С
Stannic Chloride	R
Stannous Chloride	R
Stannous Sulfate	R
Starch	R
Stearic Acid	R
Streptomycin Sulfate	R
Strontium Bromide	R
Strontium Chloride	R
Styrene	N
Succinic Acid	R
Sugar	R
Sulfamic Acid	R
Sulfate Liquors	R
Sulfite Liquors	R
Sulfur	R
Sulfur Chloride	R
Sulfur Dioxide Gas Dry	R
Sulfur Dioxide Gas Wet	R
Sulfur Trioxide Gas Dry	
Sulfur Trioxide Gas Wet	N
Sulfuric Acid Up to 30%	R
Sulfuric Acid 50%	R
Sulfuric Acid 60%	R
Sulfuric Acid 70%	R
Sulfuric Acid 80%	R
Sulfuric Acid 90%	R
Sulfuric Acid 93%	R
Sulfuric Acid 94%	R
Sulfuric Acid 95%	R
Sulfuric Acid 96%	R
Sulfuric Acid 98%	R
Sulfuric Acid 100%	R
Sulfurous Acid	R
т	

CHEMICAL		RATING
	U	
Urea Urease Urine	٧	R R R
Varnish Vaseline Vegetable Oil Vinegar Vinyl Acetate	W	C C R R
Water, Acid Mine Water, Deionized Water, Distilled Water, Potable Water, Salt Water, Salt Water, Salt Water, Soft Water, Waste Whiskey White Liquor Wine	X	R R R R R R R R R R R R R R R R R R R
Xylene	Z	С
Zinc Acetate Zinc Carbonate Zinc Chloride Zinc Nitrate Zinc Stearate Zinc Sulfate		R R R R R R

I	
Tall Oil	R
Tannic Acid	R
Tanning Liquors	R
Tar	С
Tartaric Acid	R
Terpineol	
Tetrachloroethane	N
Tetrachloroethylene	N
Tetracycline hydrochloride	
Tetraethyl Lead	R
Tetrahydrofuran	R
Tetralin	N
Thiamine Hydrochloride	R
Thionin	R
Thionyl Chloride	R
Thymol	R
Titanium Dioxide	R
Titanium Tetrachloride	R
Toluene	С
Tomato Juice	R
Transformer Oil	R
Transformer Oil DTE/30	R
Tributyl Citrate	
Tributyl Phosphate	R
Trichloroacetic Acid	R
Trichloroethylene	N
Triethanolamine	R
Triethylamine	R
Trimethylpropane	R
Trisodium Phosphate	R
Trypsin	R
Tung Oil	С
Turpentine	С

SPEARS® MANUFACTURING COMPANY PRODUCT LIMITED LIFETIME WARRANTY

Except as otherwise specified for certain products, mandated by law or herein provided, Spears® Manufacturing Company ("Company") warrants Standard Catalog Products ("Products") which have been directly manufactured by them to be free from defects in material and workmanship for as long as the original intended end user of the Products ("End User") retains ownership and possession of the Products and complies with this Warranty ("Warranty Period"). Each other person or entity acquiring or employing the Products, including buyers, contractors and installers ("Buyer") and End Users ("Buyer/End User") agrees that this Warranty shall be effective only during the Warranty Period so long as the Products are used solely for the normal purposes for which they are intended and in conformance with industry established standards, engineering, installation, operating, and maintenance specifications, recommendations and instructions including explicit instructions by the Company; the Products are properly installed, operated and used, and have not been modified; and all the other terms of this Warranty are complied with. Any violation thereof shall void this Warranty and relieve Company from all obligations arising from this Warranty and the Products.

Upon receipt or discovery of any Products that appear questionable or defective each Buyer/End User shall promptly inspect and return any such Product to the Company at 15853 Olden Street, Sylmar, California 91342, accompanied by a letter stating the nature of any problems. If the Products are determined by Company to be defective in materials or workmanship directly provided by Company, Company, at its sole option, may either repair or replace the defective Products, or reimburse applicable Buyer/End User for the cost of such Products. The applicable Buyer/End User shall bear all applicable shipping costs. THIS SHALL BE BUYERS/END USERS' SOLE REMEDY. EACH BUYER/END USER AGREES THAT COMPANY WILL NOT BE RESPONSIBLE FOR ANY OTHER OBLIGATIONS RELATING TO THE PRODUCTS, INCLUDING ANY OTHER MATERIALS OR LABOR COSTS, LOSS OF USE OR ANY OTHER ITEM OR FOR ANY DELAYS IN COMPLYING WITH THIS WARRANTY BEYOND COMPANY'S REASONABLE CONTROL.

COMPANY SHALL NOT BE LIABLE FOR, DOES NOT ASSUME, AND EXPRESSLY DISCLAIMS, ANY LIABILITY, RESPONSIBILITY AND DAMAGES: DUE TO ANY BUYER/END USER'S FAILURE TO COMPLY WITH THIS WARRANTY, INCLUDING IMPROPER INSTALLATION, USE OR OPERATION; USE WITH PRODUCTS FROM OTHER MANUFACTURERS THAT DO NOT MEET ASTM OR OTHER APPLICABLE PRODUCT STANDARDS; IMPROPER CONTROL OF SYSTEM HYDRAULICS, IMPROPER WINTERIZATION PROCEDURES, IMPROPER VOLTAGE SUPPLY, CONTACT WITH INCOMPATIBLE MATERIALS OR CHEMICALS, EXCAVATION/DIGGING, EXCESSIVE WEIGHT, AND VANDALISM; DUE TO REASONABLE WEAR AND TEAR AND DUE TO ANY ACTS OF NATURE, INCLUDING LIGHTNING, EARTHQUAKES, GROUND MOVEMENT, FROST HEAVE, OR FLOODS.

COMPANY EXTENDS ONLY THIS WARRANTY AND EXPLICITLY DISCLAIMS ALL OTHER WARRANTIES, WHETHER IMPLIED OR OTHERWISE EXPRESSED, WHETHER ORAL, STATUTORY OR OTHERWISE, INCLUDING ANY IMPLIED WARRANTIES OR AFFIRMATIONS FOR SUITABILITY, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. NO AFFIRMATION BY COMPANY OR ANY OF ITS REPRESENTATIVES, BY WORDS, CONDUCT OR OTHERWISE, SHALL CONSTITUTE A WARRANTY. THIS WARRANTY MAY NOT BE TRANSFERRED, EXTENDED, ALTERED OR OTHERWISE MODIFIED IN ANY MANNER, EXCEPT BY WRITTEN AGREEMENT SIGNED BY COMPANY.

BY ITS ACCEPTANCE OF THE PRODUCTS, EACH BUYER/END USER EXPRESSLY WAIVES ALL OTHER LIABILITY OR OBLIGATION OF ANY KIND OR CHARACTER OF COMPANY, INCLUDING LIABILITY PREDICATED UPON CONTRACT, TORT, STRICT LIABILITY OR OTHER LEGAL OR EQUITABLE GROUNDS, AND ALL, IF ANY, DAMAGES AND LOSSES AS A RESULT THEREOF, INCLUDING ALL, IF ANY, COMPENSATORY, GENERAL, SPECIAL, CONSEQUENTIAL, INCIDENTAL, OR PUNITIVE DAMAGES. WITH RESPECT TO SUCH WAIVERS, EACH BUYER/END USER EXPLICITLY WAIVES CALIFORNIA CIVIL CODE §1542 WHICH STATES "A GENERAL RELEASE DOES NOT EXTEND TO CLAIMS WHICH THE CREDITOR DOES NOT KNOW OR SUSPECT TO EXIST IN HIS FAVOR AT THE TIME OF EXECUTING THIS RELEASE, WHICH IF KNOWN BY HIM MUST HAVE MATERIALLY ADVERSELY AFFECTED HIS SETTLEMENT WITH DEBTOR" AND ALL OTHER SIMILAR STATUTORY. COMMON AND CASE LAW RIGHTS. DEFENSES AND LIMITATIONS.

Having previously independently inspected the Products, or a sample, as fully as desired, or having the opportunity to and having not done so, upon acceptance of delivery of the Products, and except as otherwise herein explicitly provided, each Buyer/End User by acceptance or use of the Products accepts them in their "AS IS" and "WITH ALL FAULTS" condition without any other warranty, expressed, implied or otherwise, and accepts and assumes the entire risk and cost of all servicing, remediation and consequences thereof. This Warranty shall be governed by California law and any unenforceable provisions severed without affecting the remaining provisions. As used herein, "including" includes "without limitation."



SPEARS® MANUFACTURING COMPANY

Corporate Office 15853 Olden Street • Sylmar, CA 91342 PO Box 9203 • Sylmar, CA 91392 (818) 364-1611 • http://www.spearsmfg.com

