

Position Switches ACTUATION ACCESSORIES

MARK 4 QUARTER-TURN POSITION INDICATION SWITCH

Features:

The Mark 4 Rotary Valve Position Indicators are produced by Proximity with up to six individual mechanical or proximity switches (standard with 2 mechanical switches). The Mark 4 is also available with potentiometer or transmitter feedback, or AS-interface (AS-i).

- · UL and CSA rated
- · Bushing & o-ring sealed switch compartment
- · Set screw cams for infinite adjustment
- Flexible design allows multiple mechanical or proximity switch and transmitter option(s)
- Adjustable stainless steel visual indicator with scale is standard for quarter turn direct drive applications
- Housing options include 1(standard), 2 or 3 conduit entrances, junction package, terminal strip and solenoid valve(s)
- High temperature to 600°F for limited duration consult factory for available options

Applications:

The Mark 4 position indicators are designed for maximum reliability in explosion-proof environments. Applications include:

- · Rotary and Linear Valves and Actuators
- Manual Valves
- · Gear Operators
- Positioners







Technical Specifications

Min. Rotation Travel – Switches Only	5°
Max. Rotation Travel – Switches Only	360°
Operational Life	10,000,000 Cycles Minimum
Temperature Limits (Standard)	–58°F to 176°F (–50°C to 80°C)
Mounting Orientation	Not Position Sensitive
Electrical Switch Ratings	
SPDT Mech. Snap Action (Standard)	15A @ 125/250/480 VAC, 1/8 hp @ 125 VAC, 1/4 hp @ 250 VAC, 1/2A @ 125 VDC, 1/4A @ 250 VDC
DPDT Snap (Optional)	10A @ 125/250 VAC, 0.3A @ 125 VDC, 0.15A @ 250 VDC
SPDT Mech. Gold Contact (Optional)	1A @ 125 VAC
SPDT Hermetically Sealed Snap (Optional)	1A @ 125 VAC
SPDT Hermetically Sealed Reed Switch (Optional)	2A @ 125 VAC, 2A @ 30 VDC
NAMUR Inductive Sensor (Optional)	15mA @ 5-25 VDC
Inductive Sensor (Optional)	10-30 VDC, Load: 0.1A
SPDT High Temp Snap (Optional)	350°F (176°C) for 600 hours, 15.1A @ 125/250/277 VAC
SPDT Mech. Snap Action (Optional)	10A @ 125/250 VAC, 1/3 hp @ 125/250 VAC
Enclosure Material	Aluminum (Epoxy Coated)
Conduit Entrance	One 3/4"-14 NPT (Options Available)
Enclosure Rating (Standard)	NEMA 1, 2, 3, 3R, 4, 4X, 6, 7, 9, 12, 13
Explosion-proof (Standard)	Class I Grp C, D; Class II, Groups E, F&G
Maximum Altitude	6560 Ft. (2000m)
Agency Approvals	CSA, UL
Weight	4 to 6 lb

ACTUATION ACCESSORIES



MARK 4 QUARTER-TURN POSITION INDICATION SWITCH

