

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L3 and L3R.

CONSTRUCTION

All finishes have white integral flange.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTINGS

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

Pull on clip Patent # (U.S.) 5707143, (Canada) 2193902.



NOTE: Specifications subject to change without notice.

Catalog Number	
Notes	Type

3" Finishing Trim

301

OPEN SHALLOW
Narrow Flange



Specifications

Height: 4-3/4 (12.1)

Lamp opening: 3-1/2 (8.9)

Diameter: 4-7/8 (12.4)

All dimensions are inches (centimeters) unless otherwise specified.

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: **301**

301	
Series	Finish
301	(blank) White
	MW Matte white
	BN Brushed nickel
	BZA Antique bronze
	ORB Oil-rubbed bronze
	<u>Anodized finish</u>
	A Clear diffuse
	AZ Clear specular
	BLZ Black specular

Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	35 PAR20	L3, L3R
		30 R20	L3, L3R
Non-IC	Incandescent	50 PAR20	L3, L3R

NOTES:

1 Available with anodized finishes only.

301 3" Open Shallow Full Reflector Trim

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.

