For Residential and Commercial Applications			
Job Name	Engineer / Architect		
Job Location	Wholesaler		
Submittal Date	Contractor		

50 Series Flare x Female Iron Pipe Elbow

Use: For use with fuel, oil, liquefied petroleum (LP) and natural gas lines. Designed for use with aluminum, copper, brass and welded steel tubing that can be flared

Design Features:

- Recommended for higher pressures than those covered by compression fittings
- Resist mechanical pull out
- Available in a broad range of sizes


Operating Specifications:

Temperature:	-65°- 250° F at maximum operating pressures
Working Pressure:	See chart below
Vibration:	Good vibration resistance*

*Recommend long flare nuts when greater vibration resistance is required

MAXIMUM WORKING PRESSURES											
Comico	Tube O.D.	Type of Tubing and Wall Thickness (Inches)									
Service Conditions		Copper – Dead Soft (Seamless)				Copper – Half Hard (Seamless)					
conditions		.030″	.032″	.035″	.049"	.065"	.032″	.035″	.042″	.049″	.065″
Safety Factor 4-1	1/8	4300		5000			5000				
	3/16	2850		3300			3400				
	1/4	2100	2250	2500			2500				
	5/16		1800	2000			2000				
	3/8		1500	1650			1700	1850			
	1/2		1100	1250		2000	1250	1400			2600
	5/8			1000	1400	1800	1000			1500	2000
	3/4			850	1150	1500			1100		1700
	7/8									1100	1500
	1/8	2800		3350			3400				
	3/16	1900		2200			2250				
	1/4	1430	1500	1650			1700				
	5/16		1200	1300			1350				
Safety Factor 6-1	3/8		100	1100			1100	1200			
	1/2		750	825		1550	850	925			1750
	5/8			650	930	1200	675			1000	1350
	3/4			550	775	1000			725		1100
	7/8									750	1000

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.








50 Series Flare x Female Iron Pipe Elbow

MATERIAL SPECIFICATIONS					
Fitting Body	C36000 brass				
PART DIMENSIONS (Inches)					
Model	Straight Thread DIM. A D		DIM. B		
50-6-6	5/8-18	1.14	.67		
50-6-8	5/8-18	1.22	.86		
50-8-6	3/4-16	1.28	.75		
50-10-8	7/8-14	1.48	.98		
50-10-12	7/8-14	1.64	.98		



Part Listing:

-	
50-6-6	3/8" OD Tube x 3/8" F.I.P.
50-6-6 B	3/8" OD Tube x 3/8" F.I.P., bulk
50-6-8	3/8" OD Tube x 1/2" F.I.P.
50-6-8 B	3/8" OD Tube x 1/2" F.I.P., bulk
50-8-6 B	1/2" OD Tube x 3/8" F.I.P., bulk
50-10-8	5/8" OD Tube x 1/2" F.I.P.
50-10-8 B	5/8" OD Tube x 1/2" F.I.P., bulk
50-10-12	5/8" OD Tube x 3/4" F.I.P.
50-10-12 B	5/8" OD Tube x 3/4" F.I.P., bulk

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

