

ProMax

TALL, SHORT AND LOWBOY (TOP CONNECT) MODELS AVAILABLE

DYNACLEAN™ DIFFUSER DIP TUBE

Helps reduce lime and sediment buildup while maximizing hot water output. Made from longlasting PEX cross-linked polymer.

COREGARD™ ANODE ROD

Aluminum anode with stainless steel core protects tank against corrosion longer than ordinary steel anodes.

DURABLE, TAMPER-RESISTANT BRASS DRAIN VALVE

PERMAGLAS® GLASS COATING

Protects steel tank from corrosion and maximizes tank life.

CSA/ASME CERTIFIED T&P RELIEF VALVE

Top-mounted T&P Relief Valve available as option on select models.

CODE COMPLIANCE:

Meets the Federal Energy Efficiency Standards according to the current edition of the National Appliance Energy Conservation Act (NAECA) of 1992. And also Meets the standby loss requirements of the U.S. Department of Energy and Current Edition of ASHRAE/IESNA 90.1 and ICC and HUD Standards.

CERTIFIED TO UL 174 FOR HOUSEHOLD ELECTRIC WATER HEATERS

6-YEAR LIMITED TANK AND PARTS WARRANTY

For complete information consult written warranty or A. O. Smith

UPGRADE TANK WARRANTY TO 10 YEARS

See details on page 2.












ProMax®

MODEL NUMBER		FIRST HOUR RATING GALLONS	ENERGY FACTOR	GAL. CAP.	ELEMENT WATTAGE 240 VAC		RECOVERY	_	DIMENSIONS IN INCHES			APPROX.
					STANDARD	MAXIMUM	90°F RISE GALLON PER HOUR	R VALUE	Α	В	С	SHIPPING WEIGHT (LBS)
TALL MODELS											, ,	
ECT-30	200	43	.93	30	4500	6000	21	16	46-1/2	18	39-1/2	90
ECT-40	200	52	.92	40	4500	6000	21	16	59-1/2	18	53-1/2	106
ECT-52	210	60	.91	50	4500	6000	21	16	54	20	47-1/2	116
ECT-55	210	67	.90	55	4500	6000	21	16	60-1/4	20	52-3/4	134
ECT-66	210	72	.88	66	4500	6000	21	16	60-1/4	20-1/2	53	178
ECT-80	210	81	.86	80	4500	6000	21	16	60-1/2	22-1/2	52	208
ECT-120+	200	112	.81	119	4500	6000	21	16	64-1/4	28	54-1/4	336
SHORT MODELS												
ECS-30	200	43	.93	30	4500	6000	21	16	36-1/2	20-1/2	28	90
ECS-40	200	52	.92	40	4500	6000	21	16	44	20-1/2	37-3/4	103
ECS-50	210	60	.90	50	4500	6000	21	16	48	21-1/2	40-1/2	121
LOWBOY MODELS												
ECL-30	200	40	.93	28	4500	6000	21	16	30	22	22-1/2	91
ECLB-30*+	100	40	.93	28	4500	6000	21	12	30	20	22-1/2	90
ECLN-40	200	48	.92	38	4500	6000	21	12	31-1/4	23	24-5/8	113
ECLB-40*	200	48	.93	38	4500	6000	21	16	32-1/4	24	24-5/8	118
ECL-50	200	55	.91	50	4500	6000	21	16	34	26-1/2	25	164

Recovery capacity is based on actual performance tests.

For 10-year tank warranty, change "E" to "P" in model number (PCT-40). + This model is not available with top T&P Valve.



For Technical Information and Automated Fax Service, call 800-527-1953. A. O. Smith Corporation reserves the right to make product changes or improvements without prior notice

¹⁰⁻year tank warranty and top T&P Valve option combo not available on ECLN-40 and ECL-50.

^{*}Heater ships with supplied insulation blanket