

Valves Technical

True Union 2000 Industrial Ball Check Valves



All thermoplastic check valves shall be True Union 2000 Industrial Ball Check

type manufactured to ASTM F 1970 and constructed from PVC Type I, ASTM D 1784, Cell Classification 12454 or CPVC Type IV, ASTM D 1784 Cell

Classification 23447. All O-rings shall be EPDM or FKM. All valve union nuts

shall have Buttress threads. All valve seats shall be a standard O-ring type. All

seal carriers shall be Safe-T-Blocked®. All valve components shall be

replaceable. All EPDM valves shall be listed by NSF® for use in potable water

service. All PVC and CPVC 1/2" through 4" valves shall be pressure rated to

235 psi, all 6" and 8" Venturied and all flanged valves shall be pressure rated to 150 psi for water at 73°F as manufactured by Spears® Manufacturing Company.

Features — PVC, CPVC

Flow tested design provides quick response with positive seal for prevention of system backflow in industrial and chemical processing applications. Valves are available in IPS sizes 1/2" through 6" with socket/regular thread, SR threaded (Special Reinforced), flanged or spigot end connectors and 8" venturied valve with socket or flanged ends. Also available in metric socket and BSP thread sizes 1/2" through 2".

- Chemical & Corrosion Resistant PVC or CPVC Construction
 - Also Available in Spears[®] High Purity, Low Extractable PVC Material
 - Strong, Buttress Thread Union Nuts
 - Schedule 80 Full-Port Design
- Spears® Safe-T-Blocked® Seal Carrier
- · Uses Standard O-ring Seat
- EPDM or FKM O-rings
- · Fully Serviceable, Replaceable Components
- Sizes 1/2" 4" Pressure Rated to 235 psi @ 73°F, Sizes 6" and 8" Venturied and all Flanged Pressure Rated to 150 psi @ 73°F
- Suitable for Either Horizontal or Vertical Installations
- EPDM valves NSF_® Certified for Potable Water use
- Suitable for Vacuum Service
- Assembled with Silicone-Free, Water Soluble Lubricants
- Manufactured to ASTM F 1970

Quick-View Valve Selection Chart

Sample Engineering Specification

| Valve | 0-ring | | Pressure | | | | |
|-------|----------|----------|----------|-------------|----------|----------|---------------------|
| Size | Material | Socket | Threaded | SR Threaded | Flanged | Spigot | Rating |
| 1/2 | EPDM | 4529-005 | included | 4521-005SR | 4523-005 | 4527-005 | |
| 1/2 | FKM | 4539-005 | included | 4531-005SR | 4533-005 | 4537-005 | |
| 3/4 | EPDM | 4529-007 | included | 4521-007SR | 4523-007 | 4527-007 | |
| 3/4 | FKM | 4539-007 | included | 4531-007SR | 4533-007 | 4537-007 | |
| 1 | EPDM | 4529-010 | included | 4521-010SR | 4523-010 | 4527-010 | |
| ' | FKM | 4539-010 | included | 4531-010SR | 4533-010 | 4537-010 | 235 psi |
| 1-1/4 | EPDM | 4529-012 | included | 4521-012SR | 4523-012 | 4527-012 | Non-Shock Water |
| 1-1/4 | FKM | 4539-012 | included | 4531-012SR | 4533-012 | 4537-012 | @ 73°F |
| 1-1/2 | EPDM | 4529-015 | included | 4521-015SR | 4523-015 | 4527-015 | - 70 . |
| 1-1/2 | FKM | 4539-015 | included | 4531-015SR | 4533-015 | 4537-015 | (Flanged |
| 2 | EPDM | 4529-020 | included | 4521-020SR | 4523-020 | 4527-020 | 150 psi |
| 2 | FKM | 4539-020 | included | 4531-020SR | 4533-020 | 4537-020 | Non-Shock) Water |
| 2-1/2 | EPDM | 4522-025 | 4521-025 | 4521-025SR | 4523-025 | 4527-025 | @ 73°F |
| 2-1/2 | FKM | 4532-025 | 4531-025 | 4531-025SR | 4533-025 | 4537-025 | |
| 3 | EPDM | 4522-030 | 4521-030 | 4521-030SR | 4523-030 | 4527-030 | |
| 3 | FKM | 4532-030 | 4531-030 | 4531-030SR | 4533-030 | 4537-030 | |
| 4 | EPDM | 4522-040 | 4521-040 | 4521-040SR | 4523-040 | 4527-040 | |
| 4 | FKM | 4532-040 | 4531-040 | 4531-040SR | 4533-040 | 4537-040 | |
| 6 | EPDM | 4522-060 | 4521-060 | 4521-060SR | 4523-060 | 4527-060 | 150 psi |
| 0 | FKM | 4532-060 | 4531-060 | 4531-060SR | 4533-060 | 4537-060 | Non-Shock |
| 82 | EPDM | 4522-080 | _ | _ | 4523-080 | _ | Water |
| 82 | FKM | 4532-080 | _ | | 4533-080 | | @ 73°F |

Optional Accessories*

- Retro-Fit End Connector Sets for Valve Replacement
- Split-Nut Repair Kits for Union Nut Replacement
- Supplemental End Connectors
- See "BALL VALVE ACCESSORIES" section for details of individual products.

Ball Check Foot Valves




Spears® Ball Check Valves easily convert to foot valves utilizing optional Foot Valve Screen adapters found in Ball Valve Accessories section.

^{1:} For CPVC valve, add the letter "C" to the part number (e.g., 4529-005**C**, 4521-005**C**SR)

^{2: 8&}quot; Venturied Valves are 6" ball valves fitted with 6x8 end connector adapters

Valves Technical True Union 2000 Industrial Ball Check Valves





Replacement Parts

| No. | Component | Qty. | Material |
|-----|----------------------|------|----------|
| 1 | Seal Carrier | 1 | PVC/CPVC |
| 2 | Seal Carrier Nut | 1 | PVC/CPVC |
| 3 | Carrier O-ring | 1 | EPDM/FKM |
| 4 | Seat Plate | 1 | PVC/CPVC |
| 5 | Seat O-ring | 1 | EPDM/FKM |
| 6 | Body | 1 | PVC/CPVC |
| 7 | Ball | 1 | PVC/CPVC |
| 8 | Union Nut | 2 | PVC/CPVC |
| 9 | End Connector O-ring | 2 | EPDM/FKM |
| 10 | End Connector | 2 | PVC/CPVC |

Dimensions, Weights, & C_v Values

| Nominal Size | | Dimensions Reference (inches, ± 1/16) | | | | | | | | ox. Wt. bs.) | C _v ² Values | | | Horizontal Closing | |
|-----------------|--------|---------------------------------------|---------|----------|---------|---------|--------|----------|-------|-----------------|------------------------------------|--------|--------|-----------------------|-----------|
| | А | B ¹ | | С | | | F | G | PVC | CPVC | Soc/Thd | Flange | Spigot | Feet of Head | GPM |
| | | Soc/Thd | Spigot | Socket | Thread | Spigot | | Ü | ' ' | 3. 10 | Jocatha | liange | Spigot | (water) | (minimum) |
| 1/2 | 1-7/8 | 2-7/16 | 2-7/8 | 4-3/16 | 3-13/16 | 4-5/8 | 3-1/2 | 2-31/32 | .30 | .33 | 6.3 | 6 | 6.3 | 1.6 | .10 |
| 3/4 | 2-1/4 | 2-3/4 | 3-1/4 | 4-3/4 | 4-1/4 | 5-1/4 | 3-7/8 | 3-5/16 | .46 | .50 | 17 | 16 | 17 | 1.6 | .10 |
| 1 | 2-1/2 | 2-7/8 | 3-1/2 | 5-1/8 | 4-11/16 | 5-3/4 | 4-1/4 | 3-5/8 | .70 | .74 | 25 | 24 | 25 | 1.6 | .25 |
| 1-1/4 | 3-1/16 | 3-1/4 | 3-3/16 | 5-3/4 | 5-3/16 | 6-5/16 | 4-5/8 | 3-31/32 | 1.04 | 1.09 | 65 | 61 | 65 | 1.6 | .40 |
| 1-1/2 | 3-1/2 | 3-1/2 | 4 | 6-1/4 | 5-7/16 | 6-3/4 | 5 | 4-3/8 | 1.37 | 1.45 | 86 | 82 | 86 | 1.6 | .75 |
| 2 | 4-5/16 | 4-25/32 | 5-3/16 | 7-3/4 | 7-27/32 | 8-1/4 | 6 | 5-1/4 | 2.47 | 2.62 | 130 | 125 | 130 | 1.6 | .75 |
| 2-1/2 | 6-3/16 | 5-7/8 | 7-13/16 | 9-5/16 | 8-1/2 | 11-3/8 | 7-1/2 | 6 | 6.80 | 7.25 | 200 | 193 | 200 | 1.0 | 1.50 |
| 3 | 6-3/16 | 6-7/8 | 7-13/16 | 10-11/16 | 9-3/4 | 11-9/16 | 7-1/2 | 6-13/16 | 6.98 | 7.35 | 275 | 268 | 275 | 1.0 | 4.00 |
| 4 | 7-3/4 | 7-5/16 | 8-1/4 | 11-13/16 | 10-1/4 | 12-3/4 | 9 | 7-1/2 | 12.13 | 12.96 | 500 | 489 | 500 | 1.0 | 5.50 |
| 6 | 11-5/8 | 11-1/6 | 13 | 17-1/16 | 15-3/4 | 18-1/2 | 11-1/4 | 10-3/16 | 37.07 | 39.98 | 800 | 794 | 800 | N/A | N/A |
| 83 | 11-5/8 | 23-3/16 | | 31-7/8 | | | 13-1/2 | 17-13/16 | 50.84 | 55.92 | N/A | N/A | N/A | N/A | N/A |

^{1:} Valve Lay Length

Temperature Pressure Rating

| Sy Ten | 100 (38) | 110 (43) | 120 (49) | 130 (54) | 140 (60) | 150 (66) | 160 (71) | 170 (77) | 180 (82) | 190 (88) | 200 (93) | 210 (99) | | |
|---|-------------|-------------|---------------|---------------|---------------|---------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|
| Valve Pressure Rating psi (MPa) | 1/2" - 4" | PVC | 235 (1.62) | 211 (1.45) | 150 (1.03) | 75 (.52) | 50 (.34) | -0- (-0-) |
| | | CPVC | 235 (1.62) | 219 (1.51) | 170 (1.17) | 145 (1.00) | 130 (.90) | 110 (.76) | 90 (.62) | 80 (.55) | 70 (.48) | 60 (.41) | 50 (.34) | -0- (-0-) |
| | 6" and 8" | PVC | 150 (1.03) | 135 (.93) | 110 (.76) | 75 (.52) | 50 (.34) | -0- (-0-) |
| | | CPVC | 150 (1.03) | 140 (.97) | 130 (.90) | 120 (.83) | 110 (.76) | 100 (.70) | 90 (.62) | 80 (.55) | 70 (.48) | 60 (.41) | 50 (.34) | -0- (-0-) |

NOTE: Flanged valves have a base pressure rating of 150 psi

General Installation Information: Ball check valves may be installed in either horizontal or vertical position. A minimum of ten (10) pipe diameters distance maintained from any pump or other source of turbulence. Check valves MUST be installed with the valves FLOW arrow pointing in the direction of flow.

^{2:} Gallons per minute at 1 psi pressure drop. Valves calculated from laying length, based on derivative of Hazen-Williams equation with surface roughness factor of C=150.

^{3: 8&}quot; Venturied Valves are 6" ball valves fitted with 6x8 end connector adapters