



Measurements:

Height	Width
5.00"	6.50"
Max OAH	Min OAH
52.50"	10.50"
Hanging Weight	
2.43 lb	

Lamping:

Incandescent MB	1,150 Rated Lumens
1.00 60W MB	2700 Color Temperature
60 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

Carton Weight	Carton Width	Carton Height	Carton Length
3.31 lb	9.33"	6.30"	14.45"
Master Pack Qty	UPC	UPS	
1.0000	783209019997	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Wilshire WS

Material:

Iron

Certification:

Dry Location
Location

Additional:

MB (Not Included)
Slope: 120