



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
25.00"	6.00"	7.00"
<u>BP Height</u>	<u>BP Width</u>	
7.75"	4.50"	
<u>Hanging Weight</u>		
4.63 lb		

Lamping:

Incandescent MB	1,150 Rated Lumens
1.00 60W MB	Color Temperature
60 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
6.00 lb	7.13"	7.75"	26.38"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209006621	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Vintage Amber VA

Material:

Steel

Certification:

Dry Location  
Location

Additional:

MB (Not Included)  
Lighting Direction: Both