


# SUBMITTAL INFORMATION

## Stainless Steel Tapping Sleeve - (FAST-xxxx-x style)



### STAINLESS STEEL TAPPING SLEEVE

Flange - 18-8 stainless steel with recess per MSS SP-60 to accept standard tapping valves. Flange conforms to AWWA C228 Class D ANSI 150# drilling. Optional carbon steel flange, per AWWA C207, is available.

Lifter bar - Type 304 stainless steel provides a heavy bearing surface for nuts.

Studs, nuts, & washers - Type 304 stainless steel. Nuts and washers are coated to prevent galling.

Outlet Pipe - Schedule 5. ASTM A240 type 304 stainless steel except 4" is Schedule 10

3/4-14 No-Lead Brass Test Plug

Armors - Heavy gage Type 304 stainless steel are vulcanized to gasket to bridge the gap between lugs.



Outlet Gasket - Virgin Buna-N compounded for water service, per ASTM D2000. Outlet gasket assures complete seal of outlet area.

Body & Strap — Type 304, stainless steel all welds are fully passivated to restore stainless characteristics.

Full Gasket - Gridded Virgin SBR compounded for water service, per ASTM D2000. Full gasket gives 360° pipe coverage.

NOM. PIPE SIZE	SLEEVE O.D. RANGE	BY	SS ** FLANGE SIZE	APPROX. WT.	NOMINAL DIMENSIONS - INCHES				SADDLE THICKNESS (GAGE)	STRAP THICKNESS (GAGE)	STUD SIZE	No. STUDS	CATALOG NUMBER**	3 SUBMITTED ITEM(S)
					A	B	C	D						
16"	17.40-17.80 17.75-18.15 18.60-19.00		3	70	4-1/64	3-1/4	5-3/16	16	.105" (12)	.063" (16)	5/8"	15	FAST-1780 - FAST-1815 - FAST-1900 -	
			4	75	5-1/64	4-1/4	5-3/16	16			5/8"	15		
			6	79	7-1/64	6-13/32	5-1/2	16			5/8"	15		
			8	100	9-1/64	8-13/32	5-5/8	20			5/8"	18		
			10	105	11-1/64	10-31/64	6-1/8	20			3/4"	18		
			12	141	13-1/64	12-27/64	6-1/4	24			3/4"	21		
18"	19.50-19.92 19.80-20.20		3	72	4-1/64	3-1/4	5-3/16	16	.105" (12)	.063" (16)	5/8"	15	FAST-1992 - FAST-2020 -	
			4	77	5-1/64	4-1/4	5-3/16	16			5/8"	15		
			6	81	7-1/64	6-13/32	5-1/2	16			5/8"	15		
			8	103	9-1/64	8-13/32	5-5/8	20			5/8"	18		
			10	108	11-1/64	10-31/64	6-1/8	20			3/4"	18		
			12	144	13-1/64	12-27/64	6-1/4	24			3/4"	21		
20"	20.20-20.60 21.20-21.60 21.40-21.80 21.86-22.26		3	83	4-1/64	3-1/4	5-3/16	16	.105" (12)	.063" (16)	5/8"	15	FAST-2060 - FAST-2160 - FAST-2180 - FAST-2226 -	
			4	87	5-1/64	4-1/4	5-3/16	16			5/8"	15		
			6	91	7-1/64	6-13/32	5-1/2	16			5/8"	15		
			8	115	9-1/64	8-13/32	5-5/8	20			5/8"	18		
			10	120	11-1/64	10-31/64	6-1/8	20			3/4"	18		
			12	158	13-1/64	12-27/64	6-1/4	24			3/4"	21		
24"	23.80-24.20 25.60-26.00		3	87	4-1/64	3-1/4	5-3/16	16	.105" (12)	.063" (16)	5/8"	15	FAST-2420 - FAST-2600 -	
			4	94	5-1/64	4-1/4	5-3/16	16			5/8"	15		
			6	100	7-1/64	6-13/32	5-1/2	16			5/8"	15		
			8	116	9-1/64	8-13/32	5-5/8	20			5/8"	18		
			10	124	11-1/64	10-31/64	6-1/8	20			3/4"	18		
			12	160	13-1/64	12-27/64	6-1/4	24			3/4"	21		

\*\* To order: Add flanged outlet size to catalog number. Example: The complete FAST catalog number for an 20" pipe (21.60 O.D.) with a 12" stainless steel flange is FAST-2160-12. For a carbon steel flange, add "A" to the catalog number. Example: FAST-2160-12A

#### FEATURES

- Body, straps and UNC threaded studs are made of 18-8 Type 304 stainless steel
- Flange can be either type 304 stainless steel or ASTM A36 carbon steel
- All sleeves are fully passivated for corrosion resistance
- Outlet Gasket is Buna-N rubber per ASTM D2000
- UL Classified to ANSI/NSF Standard 61

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



**The Ford Meter Box Company, Inc.**  
P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443  
Phone: 260-563-3171 / Fax: 800-826-3487  
Overseas Fax: 260-563-0167  
www.fordmeterbox.com

04/04/16

Submitted By: