



# PRODUCT DATA SHEET

Controlled Document - Engineering Drive

1530 Shields Drive  
Waukegan, IL 60085  
Toll-Free (800) 323-9355  
Fax: (847) 689-1192

**PART NUMBER:** 55269  
**DESCRIPTION:** 12 AWG 2/C STRANDED UNDERGROUND LOW ENERGY CIRCUIT LIGHTING CABLE  
**CONSTRUCTION:** This cable consists of two bare copper conductors with integral insulation and jacket in an SPT style construction.  
**APPROVALS:** UL Misc. Wire - Low Energy Circuit Cable  
**APPLICATION:** Low Voltage Underground Lighting Applications

---

## Construction Parameters:

Conductor	12 AWG Bare Copper
Stranding	65/30
Insulation/Jacket Material	PVC
Insulation/Jacket Thickness	0.047" Nom.
Overall Dimensions	0.186" x 0.417" Nom.

---

## Electrical Properties:

Temperature Rating	-20°C to 60°C
Operating Voltage	150 V Max.
DC Resistance per Conductor @ 20°C	1.59 Ohms/1M' Nom.

---

Insulation/Jacket Colors	Black
Legend (Surface Ink Print)	COLEMAN CABLE E32389712 AWG 2/C UNDERGROUND LOW ENERGY CIRCUIT CABLE SUNLIGHT RESISTANT 60C (UL) 150V -- C(UL) 30V FT2

This product complies with European Directive 2002/95/EC (RoHS)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

The jacket is sequentially footmarked.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name \_\_\_\_\_  
Customer Approval \_\_\_\_\_

Specification Issue Date: August 24, 2011