



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
9.50"	28.00"	6.50"
<u>BP Height</u>	<u>BP Width</u>	
4.50"	4.50"	
<u>Hanging Weight</u>		
10.50 lb		

Lamping:

Incandescent MB	4,600 Rated Lumens
4.00 60W MB	Color Temperature
240 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
14.19 lb	7.50"	11.75"	27.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209007369	Yes	

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB (Not Included)
Lighting Direction: Both