Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

# Series 957RPDA, 957NRPDA, 957ZRPDA

### Reduced Pressure Detector Assemblies

#### Sizes: 21/2" - 10"

Series 957RPDA, 957NRPDA, 957ZRPDA Reduced Pressure Detector Assemblies provide protection to the potable water system from contamination in accordance with national plumbing codes. The 957RPDA, 957NRPDA, 957ZRPDA are normally used in health hazard applications to protect against backsiphonage and backpressure. The Watts 957RPDA, 957NRPDA, 957ZRPDA are used to monitor unauthorized use of water from the fire protection system.

#### Features

- Extremely compact design
- 70% lighter than traditional designs
- 304 (Schedule 40) stainless steel housing & sleeve
- · Groove fittings allow integral pipeline adjustment
- Patented torsion spring check provides lowest pressure loss
- Unmatched ease of serviceability
- Replaceable check disc rubber
- Available with grooved butterfly valve shutoffs
- Bottom mounted cast stainless steel relief valve
- Metered bypass to detect leakage or theft of water from the fire sprinkler system

#### Specifications

The Reduced Pressure Detector Assembly shall consist of two independent torsion spring check modules, a differential pressure relief valve located between and below the two modules, two drip tight shutoff valves, and required torsion spring check modules and relief valve shall be contained within a sleeve accessible single housing constructed from 304 (Sch 40) stainless steel pipe with groove end connections. Torsion spring checks shall have reversible elastomer discs and in operation produce drip tight closure against reverse flow caused by backpressure or backsiphonage. The bypass line shall include a meter, small diameter reduced pressure zone assembly and isolation valves. Assembly shall be Watts Series 957RPDA, 957NRPDA, 957ZRPDA.

#### A WARNING

It is illegal to use this product in any plumbing system providing water for human consumption, such as drinking or dishwashing, in the United States. Before installing standard material product, consult your local water authority, building and plumbing codes.

#### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.





957NRPDAOSY

#### **Available Models**

Suffix:

- OSY UL/FM outside stem and yoke, resilient seated gate valves
- BFG UL/FM grooved gear operated butterfly valves with tamper switch
- \*OSY FxG Flanged inlet gate connection and grooved outlet gate connection
- \*OSY GxF Grooved inlet gate connection and flanged outlet gate connection
- \*OSY GxG –Grooved inlet gate connection and grooved outlet gate connection

Available with grooved NRS gate valves - consult factory\* Post indicator plate and operating nut available - consult factory\* \*Consult factory for dimensions

#### Materials

Housing & Sleeve: 304 (Schedule 40) Stainless Steel Elastomers: EPDM, Silicone and Buna 'N' Torsion Spring Checks: Noryl<sup>®</sup>, Stainless Steel Check Discs: Reversible Silicone or EPDM Test Cocks: Bronze Body Nickel Plated Pins & Fasteners: 300 Series Stainless Steel Springs: Stainless Steel

#### Pressure - Temperature


Temperature Range: 33°F – 140°F (0.5°C – 60°C) Maximum Working Pressure: 175psi (12.1 bar)

#### Approvals

• Approved by the Foundation for Cross-Connection Control and Hydraulic Research at The University of Southern California (FCCCHR-USC)


(Excluding 'N' Pattern - 10"'Z', Pattern - 6" and 10")


• AWWA C511-97




#### 957RPDA, 957NRPDA, 957ZRPDA

SIZE	ZE DIMENSIONS WEIGHT																					
	A		C (C	DSY)	D G H			l J		М		Р		957RPDA		957NRPDA						
in.	in.	mm	in.	тт	in.	тт	in.	тт	in.	mm	in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kgs.	lbs.	kgs.
<b>2</b> <sup>1</sup> / <sub>2</sub>	30¾	781	16¾	416	6½	165	<b>29</b> <sup>1</sup> /16	738	211/2	546	15½	393	<b>8</b> <sup>13</sup> ⁄16	223	211/4	540	<b>13</b> <sup>3</sup> ⁄16	335	142	64	150	68
3	31¾	806	181%	479	<b>6</b> <sup>11</sup> /16	170	30¼	768	221/4	565	171/%	435	<b>9</b> <sup>3</sup> /16	233	23	584	14½	368	162	73	175	79
4	33¾	857	<b>22</b> <sup>3</sup> ⁄4	578	7	178	33	838	<b>23</b> ½	597	18½	470	9 <sup>15</sup> ⁄16	252	26 <sup>1</sup> /4	667	<b>15</b> <sup>3</sup> ⁄16	386	178	81	201	91
6	43½	1105	30 <sup>1</sup> /%	765	8½	216	44¾	1137	33¼	845	<b>23</b> <sup>3</sup> ⁄16	589	13 <sup>1</sup> /16	332	321/4	819	19	483	312	142	353	160
8	49¾	1264	<b>37</b> ¾	959	<b>9</b> <sup>11</sup> / <sub>16</sub>	246	54½	1375	401/8	1019	<b>27</b> <sup>7</sup> /16	697	<b>15</b> <sup>11</sup> / <sub>16</sub>	399	367//8	937	<b>21</b> <sup>3</sup> ⁄16	538	497	225	572	
10	57¾	1467	45¾	1162	<b>23</b> <sup>13</sup> /16	605	<b>8</b> <sup>3</sup> ⁄16	208	66	1676	<b>49</b> <sup>1</sup> / <sub>2</sub>	1257	321/2	826	175/16	440	20	508	721	327	781	354







#### 957NRPDABFG, 957ZRPDABFG

SIZE	DIMENSIONS WEIGHT													
		G	Н		1		J		М		Р		957RPDABFG	
in.	in.	тт	in.	тт	in.	тт	in.	тт	in.	mm	in.	тт	lbs.	kgs.
<b>2</b> ½	<b>32</b> ½	826	23	584	15½	394	91⁄2	241	19¾	502	<b>15</b> <sup>13</sup> ⁄16	402	81	37
3	34	864	24	610	<b>16</b> 5⁄16	414	<b>10</b> <sup>1</sup> ⁄16	256	21¼	540	16½	410	84	38
4	35%	905	<b>25</b> ½	648	<b>17</b> <sup>3</sup> ⁄16	437	<b>10</b> <sup>15</sup> ⁄16	279	<b>23</b> ½	597	16%	422	101	46
6	<b>46</b> <sup>1</sup> / <sub>2</sub>	1181	35¼	895	<b>20</b> <sup>1</sup> / <sub>2</sub>	521	13½	343	271/4	692	19	483	174	79

Noryl® is a registered trademark of SABIC Innovative Plastics Holding BV.

#### Capacity

Series 957RPDA, 957NRPDA, 957ZRPDA flow curves as tested by Underwriters Laboratory.


Flow characteristics collected using butterfly shutoff valves


——— Horizontal ——— N-Pattern ..... Z-Pattern


**2<sup>1</sup>/2**"

## Flow capacity chart identifies valve performance based upon rated water velocity up to 25fps

- Service Flow is typically determined by a rated velocity of 7.5fps based upon schedule 40 pipe.
- Rated Flow identifies maximum continuous duty performance determined by AWWA.
- UL Flow Rate is 150% of Rated Flow and is not recommended for continuous duty.
- AWWA Manual M22 [Appendix C] recommends that the maximum water velocity in services be not more than 10fps.







#### NOTICE

Inquire with governing authorities for local installation requirements

