Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

LEAD FREE*

Series 2000SS

Double Check Valve Assemblies

Sizes: 2½" - 12" (65 - 300mm)

Features

- Cam-Check Assembly provides low head loss
- Short lay length is ideally suited for retrofit installations
- Stainless Steel body is half the weight of competitive designs reducing installation and shipping cost
- Stainless steel construction provides long term corrosion protection and maximum strength
- Single top access cover with two-bolt grooved style coupling for ease of maintenance
- No special tools required for servicing
- Compact construction allows for smaller vaults and enclosures
- May be installed in horizontal or vertical "flow up" position (ASSE Only)

Available Models

Suffix:

LG -

NRS non-rising stem resilient seated gate valves

OSY -UL/FM outside stem and yoke

resilient seated gate valves **OSY FxG flanged inlet gate connection

and grooved outlet gate connection

**OSY GxF grooved inlet gate connection and flanged outlet gate connection

**OSY GxG grooved inlet gate connection and grooved outlet gate

> connection less gates

Available with grooved NRS gate valves - consult factory**

Post indicator plate and operating nut available consult factory**

**Consult factory for dimensions

NOTICE

Inquire with governing authorities for local installation requirements

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.



Series 2000SS Double Check Valve Assemblies are designed to prevent the reverse flow of polluted water from entering into the potable water system. This series can be applied, where approved by the local authority having jurisdiction, on non-health hazard installations. Features short end-to-end dimensions, lightweight stainless steel body, and low head loss.

Specifications

A Double Check Valve Assembly shall be installed at each noted location to prevent the unwanted reversal of polluted water into the potable water supply. The main valve body shall be manufactured from 300 series stainless steel to provide corrosion resistance, 100% lead free through the waterway. The double check shall consist of two independently operated spring loaded cam-check valves, required test cocks, and optional inlet and outlet resilient seated shutoff valves. Each cam-check shall be internally loaded and provide a positive drip tight closure against the reverse flow of liquid caused by backsiphonage or backpressure. The modular cam-check includes a stainless steel spring and cam-arm, rubber faced disc and a replaceable seat. There shall be no brass or bronze parts used within the cam-check valve assembly. The valve cover shall be held in place through the use of a single grooved style two-bolt coupling. The main assembly shall consist of two independently operating torsion spring check assemblies, two resilient seated isolation valves, and four ball valve type test cocks. The assembly shall be an Ames Company Series 2000SS.

Materials

All internal metal parts: 300 Series

stainless steel

Main valve body: 300 Series stainless steel

Check assembly: Noryl®

Flange dimension in accordance with AWWA

Class D

Noryl® is a registered trademark of General Electric

Company.

Pressure — Temperature

Temperature Range: 33°F - 110°F (5°C - 43°C) Maximum Working Pressure: 175psi (12.06 bar)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



(OSY ONLY)

AWWA C510-92, CSA B64.5

Standards

Approvals




For 12" approvals consult factory





Ames Fire & Waterworks product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Ames Fire & Waterworks Technical Service. Ames Fire & Waterworks reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Ames Fire & Waterworks products previously or subsequently sold.


Capacities


Rated working pressure 175psi (12.06 bar) * Rated flow **UL Tested























	SIZE	(DN)			DIMENSIONS							WEIGHT						
_				A	C (0	OSY)	C(NRS)		D		L		S		w/Gates		w/o Gates	
	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lb.	kg.	lb.	kg.
	21/2	65	37	965	163//8	416	93//8	238	31/2	89	22	559	7	178	140	64	53	24
	3	80	38	965	187//8	479	101/4	260	33/4	95	22	559	71/2	191	215	98	55	25
	4	100	40	1016	223/4	578	123/16	310	41/2	114	22	559	9	229	225	102	58	26
	6	150	481/2	1232	301//8	765	16	406	51/2	140	271/2	699	11	279	375	170	105	48
	8	200	52½	1334	373/4	959	19 ¹⁵ / ₁₆	506	63/4	171	291/2	749	13½	343	561	254	169	77
	10	250	55½	1410	45¾	1162	2313/16	605	8	200	291/2	749	16	406	763	346	179	81
	12	300	57½	1461	531//8	1349	26¾	679	91/2	241	291/2	749	19	483	1033	469	209	95



A WATTS Brand

USA: Backflow T: (978) 689-6066 • F: (978) 975-8350 • AmesFireWater.com

USA: Control Valves T: (713) 943-0688 • F: (713) 944-9445 • AmesFireWater.com

Canada: T: (905) 332-4090 • F: (905) 332-7068 • AmesFireWater.ca