



**TRANE®**

# Upflow/Downflow Horizontal Right or Left Gas-Fired Furnace

---

## XT 80

**TUD1A040A9H21B, TUD1B060A9H31B**

**TUD1B080A9H31B, TUD1C080A9H41B**


**TUD1B100A9H31B, TUD1C100A9H51B**

**TUD1D120A9H51B, TUD1D140A9H51B**


**TDD1B060A9H31B, TDD1B080A9H31B**

**TDD1C100A9H51B, TDD1D120A9H51B**

**Single Stage, High Efficiency Motor**



**Upflow / Horizontal\***



**Downflow / Horizontal\***

\*Horizontal Conversion for these furnaces may be left or right side rotation.



# General Features

## Natural Gas Models

Central heating furnace designs are certified by the American Gas Association for both natural and L.P. gas. Limit setting and rating data were established and approved under standard rating conditions using American National Standards Institute standards.

## Safe Operation

The Integrated System Control has solid state devices, which continuously monitor for presence of flame, when the system is in the heating mode of operation. Dual solenoid combination gas valve and regulator provide extra safety.

## Quick Heating

Durable, cycle tested, heavy gauge **aluminized steel heat exchanger** quickly transfers heat to provide warm conditioned air to the structure.

## Burners

Multi-port In-shot burners will give years of quiet and efficient service. All models can be converted to **L.P. gas**.

## Integrated System Control

Exclusively designed operational program provides total control of furnace limit sensors, blowers, gas valve, flame control and includes self-diagnostics for ease of service. Also contains connection points for E.A.C./humidifier.

## Air Delivery

The multispeed, high efficiency, direct drive blower motor, with sufficient airflow range for most heating and cooling requirements, will switch from heating to cooling speeds on demand from room thermostat. The blower door safety switch will prevent or terminate furnace operation when the blower door is removed.

## Styling

Heavy gauge steel and "wrap-around" cabinet construction is used in the cabinet with baked-on enamel finish for strength and beauty. The heat exchanger section of the cabinet is completely lined with foil faced fiberglass insulation. This results in quiet and efficient operation due to the excellent acoustical and insulating qualities of fiberglass.

## Features And General Operation

The XT80 High Efficiency Gas Furnaces employ a Hot Surface Ignition system, which eliminates the waste of a constant burning pilot. The integrated system control lights the main burners upon a demand for heat from the room thermostat. Complete front service access.

- a. Low energy power venter.
- b. Vent proving differential switch.



# Contents

---

<b>General Features</b>	<b>2</b>
<b>Features and Benefits</b>	<b>4</b>
Standard Equipment	4
Optional Equipment	5
<b>General Data</b>	<b>6</b>
TUD1A040A9H21B	6
TUD1B060A9H31B	6
TUD1B080A9H31B	6
TUD1C080A9H41B	6
TUD1B100A9H31B	7
TUD1C100A9H51B	7
TUD1D120A9H51B	7
TUD1D140A9H51B	7
TDD1B060A9H31B	8
TDD1B080A9H31B	8
TDD1C100A9H51B	8
TDD1D120A9H51B	8
<b>Performance Data</b>	<b>9</b>
<b>Electrical Data</b>	<b>12</b>
<b>Field Wiring</b>	<b>16</b>
<b>Twining Field Wiring</b>	<b>17</b>
<b>Dimensions</b>	<b>18</b>



## Features and Benefits

---

### XT80 Upflow/Downflow Horizontal Right or Left Standard Equipment

- Convertible to horizontal with left or right airflow
- Power supply 115/1/60
- Silicon Nitride Hot surface igniter with adaptive heat up
- Integrated solid state control with self-diagnostics
- Single wire twinning
- Attractive color accents
- Hinged blower door
- Perfect Fit door latches
- Insulated blower door
- Gasketed blower door
- Internal filter rack
- Standard filter sizes
- Cleanable high velocity filters
- Heavy gauge aluminized steel heat exchanger
- Blower door safety switch
- Constant torque ECM blower motor
- Multi-port In-shot burners
- Complete front service access
- Alternate bottom/left/right return air
- Slide out blower assembly
- High efficiency direct drive 4 speed motor
- Adjustable fan off times
- Common vent capability
- Heavy gauge reinforced wrap-around steel cabinet
- Optional L.P. conversion kit
- Left/right gas connection
- Accessory hook-up capability
- Selectable cooling fan off eliminates need for BAY24X045 time delay relay
- 24 volt fuse
- Manual reset flame roll-out switches



## Features and Benefits

### Optional Equipment

#### OPTIONAL EQUIPMENT FOR CONDENSING UNITS (Check mark [✓] indicates accessories included).

For Comfort Controls, See price book pages .....	[ ]
CleanEffects™ Whole House Air Cleaner (14-1/2" Wide, Upflow / Side Return Furnace) .....	TFD145ALFR000A [ ]
CleanEffects™ Whole House Air Cleaner (17-1/2" Wide, Upflow / Side Return Furnace) .....	TFD175ALFR000A [ ]
CleanEffects™ Whole House Air Cleaner (21" Wide, Upflow / Side Return Furnace) .....	TFD210ALFR000A [ ]
CleanEffects™ Whole House Air Cleaner (24-1/2" Wide, Upflow / Side Return Furnace) .....	TFD245ALFR000A [ ]
CleanEffects™ Whole House Air Cleaner (14-1/2" Wide, Downflow Furnace) .....	TFD14DALFR000A [ ]
CleanEffects™ Whole House Air Cleaner (17-1/2" Wide, Downflow Furnace) .....	TFD17DALFR000A [ ]
CleanEffects™ Whole House Air Cleaner (21" Wide, Downflow Furnace) .....	TFD21DALFR000A [ ]
CleanEffects™ Whole House Air Cleaner (24-1/2" Wide, Downflow Furnace) .....	TFD24DALFR000A [ ]
Electronic Air Filter, "Perfect Fit" Super Efficiency (14-1/2" Wide Gas Furnace) .....	TFE145A9FRO [ ]
Electronic Air Filter, "Perfect Fit" Super Efficiency (17-1/2" Wide Gas Furnace) .....	TFE175A9FRO [ ]
Electronic Air Filter, "Perfect Fit" Super Efficiency (21" Wide Gas Furnace) .....	TFE210A9FRO [ ]
Electronic Air Filter, "Perfect Fit" Super Efficiency (24-1/2" Wide Gas Furnace) .....	TFE245A9FRO [ ]
Air Filter, "Perfect Fit" High Efficiency (14-1/2" Wide Gas Furnace) .....	TFM145A9FRO [ ]
Air Filter, "Perfect Fit" High Efficiency (17-1/2" Wide Gas Furnace) .....	TFM175A9FRO [ ]
Air Filter, "Perfect Fit" High Efficiency (21" Wide Gas Furnace) .....	TFM210A9FRO [ ]
Air Filter, "Perfect Fit" High Efficiency (24-1/2" Wide Gas Furnace) .....	TFM245A9FRO [ ]
Air Filter, "Perfect Fit" Standard Efficiency (14-1/2" Wide Gas Furnace) .....	TFP145A9FRO [ ]
Air Filter, "Perfect Fit" Standard Efficiency (17-1/2" Wide Gas Furnace) .....	TFP175A9FRO [ ]
Air Filter, "Perfect Fit" Standard Efficiency (21" Wide Gas Furnace) .....	TFP210A9FRO [ ]
Air Filter, "Perfect Fit" Standard Efficiency (24-1/2" Wide Gas Furnace) .....	TFP245A9FRO [ ]
Coil Enclosure (14-1/2" Wide Cabinets) .....	BAYCLE14A1422A [ ]
Coil Enclosure (17-1/2" Wide Cabinets) .....	BAYCLE17A1722A [ ]
Coil Enclosure (21" Wide Cabinets) .....	BAYCLE21A2130A [ ]
Coil Enclosure (24-1/2" Wide Cabinets) .....	BAYCLE24A2430A [ ]
High Altitude Switch .....	BAYHALT248 [ ]
Downflow Subbase .....	BAYBASE205 [ ]
Propane Conversion Kit .....	BAYLPKT210B [ ]
Propane Conversion Kit (With Stainless Steel burners) .....	BAYLPSS210B [ ]
Masonry Chimney Vent Kit (Upflow models only) .....	BAYVENT800B [ ]
Filter Access Door Kit (Downflow models) .....	BAYFLTR206 [ ]



# General Data

## TUD1-H Product Specifications ①

MODEL	TUD1A040A9H21B	TUD1B060A9H31B	TUD1B080A9H31B	TUD1C080A9H41B
<b>RATINGS②</b>				
Input BTUH	40000	60000	80000	80000
Capacity BTUH (ICS) ③	32000	47000	63000	64000
AFUE	80.0	80.0	80.0	80.0
Temp. Rise (Min.-Max.) °F.	30 - 60	30 - 60	30 - 60	30 - 60
<b>BLOWER DRIVE</b>	DIRECT	DIRECT	DIRECT	DIRECT
Dia.-Width (In.)	10 x 6	10 x 7	10 x 8	11 x 10
No. Used	1	1	1	1
Speeds (No.)	4	4	4	4
CFM vs. in. w.g.	SEE FAN PERF. TABLE	SEE FAN PERF. TABLE	SEE FAN PERF. TABLE	SEE FAN PERF. TABLE
Motor HP ④	1/2	1/2	1/2	3/4
R.P.M.	1080	1075	1075	1100
Volts/Ph/Hz	115/1/60	115/1/60	115/1/60	115/1/60
<b>COMBUSTION FAN — TYPE</b>	CENTRIFUGAL	CENTRIFUGAL	CENTRIFUGAL	CENTRIFUGAL
Drive - No. Speeds	DIRECT - 1	DIRECT - 1	DIRECT - 1	DIRECT - 1
Motor HP - RPM	1/50 - 3180	1/50 - 3180	1/50 - 3180	1/50 - 3180
Volts/Ph/Hz	115/1/60	115/1/60	115/1/60	115/1/60
FL Amps	1.09	1.09	1.09	1.09
<b>FILTER — Furnished?</b>	Yes	Yes	Yes	Yes
Type Recommended	High Velocity	High Velocity	High Velocity	High Velocity
Filter (No.-Size-Thk.)	1 - 14 X 25 - 1 IN.	1 - 17 X 25 - 1 IN.	1 - 17 X 25 - 1 IN.	1 - 20 X 25 - 1 IN.
<b>VENT — Size (In.)</b>	4 ROUND	4 ROUND	4 ROUND	4 ROUND
<b>HEAT EXCHANGER</b>				
Type - Fired	ALUMINIZED STEEL TYPE 1	ALUMINIZED STEEL TYPE 1	ALUMINIZED STEEL TYPE 1	ALUMINIZED STEEL TYPE 1
- Unfired				
Gauge (Fired)	20	20	20	20
<b>ORIFICES — Main</b>				
Nat. Gas. Qty. — Drill Size	2 - 45	3 - 45	4 - 45	4 - 45
L.P. Gas Qty. — Drill Size	2 - 56	3 - 56	4 - 56	4 - 56
<b>GAS VALVE</b>	REDUNDANT - SINGLE STAGE	REDUNDANT - SINGLE STAGE	REDUNDANT - SINGLE STAGE	REDUNDANT - SINGLE STAGE
<b>DIRECT IGNITION DEVICE</b>				
Type	HOT SURFACE	HOT SURFACE	HOT SURFACE	HOT SURFACE
<b>BURNERS — Type</b>	IN-SHOT	IN-SHOT	IN-SHOT	IN-SHOT
Number	2	3	4	4
<b>POWER CONN. — V/Ph/Hz④</b>	115/1/60	115/1/60	115/1/60	115/1/60
Ampacity (In Amps)	10.3	10.3	10.3	12.3
Max. Overcurrent Protection (Amps)	15	15	15	20
<b>PIPE CONN. SIZE (IN.)</b>	1/2	1/2	1/2	1/2
<b>DUCT CONN.</b>	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING
<b>DIMENSIONS</b>				
Crated (In.)	H X W X D 41-3/4 X 16-1/2 X 30-1/2	H X W X D 41-3/4 X 19-1/2 X 30-1/2	H X W X D 41-3/4 X 19-1/2 X 30-1/2	H X W X D 41-3/4 X 23 X 30-1/2
Uncrated	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING
<b>WEIGHT</b>				
Shipping (Lbs.)/Net (Lbs.)	119/110	136/126	142/132	162/151

① Central Furnace heating designs are certified by AGA and CSA.

② For U.S. applications, above input ratings (BTUH) are up to 2,000 feet, derate 4% per 1,000 feet for elevations above 2,000 feet above sea level.

For Canadian applications, above input ratings (BTUH) are up to 4,500 feet, derate 4% per 1,000 feet for elevations above 4,500 feet above sea level.

③ Based on U.S. government standard tests.

④ The above wiring specifications are in accordance with National Electrical Code; however, installations must comply with local codes.

⑤ Constant torque ECM blower motor.



# General Data

## TUD1-H Product Specifications ①

MODEL	TUD1B100A9H31B	TUD1C100A9H51B	TUD1D120A9H51B	TUD1D140A9H51B
<b>RATINGS<sup>②</sup></b>				
Input BTUH	100000	100000	120000	140000
Capacity BTUH (ICS) <sup>③</sup>	80000	79000	96000	111000
AFUE	80.0	80.0	80.0	80.0
Temp. Rise (Min.-Max.) °F.	40 - 70	30 - 60	30 - 60	40 - 70
<b>BLOWER DRIVE</b>	DIRECT	DIRECT	DIRECT	DIRECT
Dia.-Width (In.)	10 x 8	11 x 10	11 x 10	11 x 10
No. Used	1	1	1	1
Speeds (No.)	4	4	4	4
CFM vs. in. w.g.	SEE FAN PERF. TABLE			
Motor HP <sup>⑤</sup>	3/4	1	1	1
R.P.M.	1075	1075	1075	1075
Volts/Ph/Hz	115/1/60	115/1/60	115/1/60	115/1/60
<b>COMBUSTION FAN — TYPE</b>	CENTRIFUGAL	CENTRIFUGAL	CENTRIFUGAL	CENTRIFUGAL
Drive - No. Speeds	DIRECT - 1	DIRECT - 1	DIRECT - 1	DIRECT - 1
Motor HP - RPM	1/50 - 3180	1/50 - 3180	1/50 - 3180	1/50 - 3180
Volts/Ph/Hz	115/1/60	115/1/60	115/1/60	115/1/60
FL Amps	1.09	1.09	1.09	1.09
<b>FILTER — Furnished?</b>	Yes	Yes	Yes	Yes
Type Recommended	High Velocity	High Velocity	High Velocity	High Velocity
Filter (No.-Size-Thk.)	1 - 17 X 25 - 1 IN.	1 - 20 X 25 - 1 IN.	1 - 24 X 25 - 1 IN.	1 - 24 X 25 - 1 IN.
<b>VENT — Size (In.)</b>	4 ROUND	4 ROUND	4 ROUND	4 ROUND
<b>HEAT EXCHANGER</b>				
Type - Fired	ALUMINIZED STEEL TYPE 1			
- Unfired				
Gauge ( Fired)	20	20	20	20
<b>ORIFICES — Main</b>				
Nat. Gas. Qty. — Drill Size	5 - 45	5 - 45	6 - 45	7 - 45
L.P. Gas Qty. — Drill Size	5 - 56	5 - 56	6 - 56	7 - 56
<b>GAS VALVE</b>	REDUNDANT - SINGLE STAGE			
<b>DIRECT IGNITION DEVICE</b>				
Type	HOT SURFACE	HOT SURFACE	HOT SURFACE	HOT SURFACE
<b>BURNERS — Type</b>	IN-SHOT	IN-SHOT	IN-SHOT	IN-SHOT
Number	5	5	6	7
<b>POWER CONN. — V/Ph/Hz<sup>④</sup></b>	115/1/60	115/1/60	115/1/60	115/1/60
Ampacity (In Amps)	12.3	15.4	15.4	15.4
Max. Overcurrent Protection (Amps)	15	20	20	20
<b>PIPE CONN. SIZE (IN.)</b>	1/2	1/2	1/2	1/2
<b>DUCT CONN.</b>	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING
<b>DIMENSIONS</b>	H X W X D	H X W X D	H X W X D	H X W X D
Crated (In.)	41-3/4 X 19-1/2 X 30-1/2	41-3/4 X 23 X 30-1/2	41-3/4 X 26-1/2 X 30-1/2	41-3/4 X 26-1/2 X 30-1/2
Uncrated	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING
<b>WEIGHT</b>				
Shipping (Lbs.)/Net (Lbs.)	153/143	162/151	186/174	193/181

① Central Furnace heating designs are certified by AGA and CSA.

② For U.S. applications, above input ratings (BTUH) are up to 2,000 feet, derate 4% per 1,000 feet for elevations above 2,000 feet above sea level.

For Canadian applications, above input ratings (BTUH) are up to 4,500 feet, derate 4% per 1,000 feet for elevations above 4,500 feet above sea level.

③ Based on U.S. government standard tests.

④ The above wiring specifications are in accordance with National Electrical Code; however, installations must comply with local codes.

⑤ Constant torque ECM blower motor.



# General Data

## TDD1-H Product Specifications ①

MODEL	TDD1B060A9H31B	TDD1B080AH931B	TDD1C100A9H51B	TDD1D120A9H51B
<b>RATINGS<sup>②</sup></b>				
Input BTUH	60000	80000	100000	120000
Capacity BTUH (ICS) <sup>③</sup>	48000	64000	81000	96000
AFUE	80.0	80.0	80.0	80.0
Temp. Rise (Min.-Max.) °F.	25 - 55	35 - 65	30 - 60	35 - 65
<b>BLOWER DRIVE</b>				
Dia.-Width (In.)	DIRECT 10 x 7	DIRECT 10 x 8	DIRECT 11 x 10	DIRECT 11 x 10
No. Used	1	1	1	1
Speeds (No.)	4	4	4	4
CFM vs. in. w.g.	SEE FAN PERF. TABLE	SEE FAN PERF. TABLE	SEE FAN PERF. TABLE	SEE FAN PERF. TABLE
Motor HP <sup>④</sup>	1/2	1/2	1	1
R.P.M.	1075	1075	1075	1075
Volts/Ph/Hz	115/1/60	115/1/60	115/1/60	115/1/60
<b>COMBUSTION FAN — TYPE</b>				
Drive - No. Speeds	CENTRIFUGAL DIRECT - 1	CENTRIFUGAL DIRECT - 1	CENTRIFUGAL DIRECT - 1	CENTRIFUGAL DIRECT - 1
Motor HP - RPM	1/50 - 3180	1/50 - 3180	1/50 - 3180	1/50 - 3180
Volts/Ph/Hz	115/1/60	115/1/60	115/1/60	115/1/60
FL Amps	1.09	1.09	1.09	1.09
<b>FILTER — Furnished?</b>				
Type Recommended	Yes	Yes	Yes	Yes
Filter (No.-Size-Thk.)	High Velocity 2 - 14 X 20 - 1 IN	High Velocity 2 - 14 X 20 - 1 IN	High Velocity 2 - 16 X 20 - 1 IN	High Velocity 2 - 16 X 20 - 1 IN
<b>VENT — Size (In.)</b>				
	4 ROUND	4 ROUND	4 ROUND	4 ROUND
<b>HEAT EXCHANGER</b>				
Type - Fired	ALUMINIZED STEEL TYPE 1	ALUMINIZED STEEL TYPE 1	ALUMINIZED STEEL TYPE 1	ALUMINIZED STEEL TYPE 1
- Unfired				
Gauge (Fired)	20	20	20	20
<b>ORIFICES — Main</b>				
Nat. Gas. Qty. — Drill Size	3 - 45	4 - 45	5 - 45	6 - 45
LP. Gas Qty. — Drill Size	3 - 56	4 - 56	5 - 56	6 - 56
<b>GAS VALVE</b>				
	REDUNDANT - SINGLE STAGE	REDUNDANT - SINGLE STAGE	REDUNDANT - SINGLE STAGE	REDUNDANT - SINGLE STAGE
<b>DIRECT IGNITION DEVICE</b>				
Type	HOT SURFACE	HOT SURFACE	HOT SURFACE	HOT SURFACE
<b>BURNERS — Type</b>				
Number	IN-SHOT 3	IN-SHOT 4	IN-SHOT 5	IN-SHOT 6
<b>POWER CONN. — V/Ph/Hz<sup>④</sup></b>				
Ampacity (In Amps)	115/1/60	115/1/60	115/1/60	115/1/60
Max. Overcurrent Protection (Amps)	10.3	10.3	15.4	15.4
15	15	20	20	
<b>PIPE CONN. SIZE (IN.)</b>				
	1/2	1/2	1/2	1/2
<b>DUCT CONN.</b>				
	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING
<b>DIMENSIONS</b>				
Crated (In.)	H X W X D 41 X 19-1/2 X 29-1/2	H X W X D 41-3/4 X 18-1/2 X 29-1/2	H X W X D 41-3/4 X 22 X 29-1/2	H X W X D 41 X 25-1/2 X 29-1/2
Uncrated	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING	SEE OUTLINE DRAWING
<b>WEIGHT</b>				
Shipping (Lbs.)/Net (Lbs.)	136 / 126	146 / 135	167/155	189 / 176

① Central Furnace heating designs are certified by AGA and CSA.

② For U.S. applications, above input ratings (BTUH) are up to 2,000 feet, derate 4% per 1,000 feet for elevations above 2,000 feet above sea level.

For Canadian applications, above input ratings (BTUH) are up to 4,500 feet, derate 4% per 1,000 feet for elevations above 4,500 feet above sea level.

③ Based on U.S. government standard tests.

④ The above wiring specifications are in accordance with National Electrical Code; however, installations must comply with local codes.

⑤ Constant torque ECM blower motor.



# Performance Data

## TUD1-H Airflow

FURNACE AIRFLOW (CFM) VS. STATIC PRESSURE (ins.w.g.)										
MODEL	SPEED TAP	0.1	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9
TUD1A040A9H21B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	1121 926 761 750	1094 896 720 644	1067 866 678 538	1039 837 648 499	1011 808 617 459	983 783 583 415	955 757 548 371	929 723 514 337	902 689 479 303
TUD1B060A9H31B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	1360 1188 1040 942	1329 1152 1003 873	1298 1116 966 803	1268 1089 931 771	1238 1062 896 739	1208 1031 861 699	1178 1000 826 659	1147 962 787 619	1116 924 747 579
TUD1B080A9H31B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	1440 1249 1179 1048	1406 1219 1143 989	1372 1189 1106 929	1345 1158 1078 888	1318 1127 1050 847	1287 1091 1010 802	1255 1055 970 757	1219 1019 929 708	1183 982 887 658
TUD1C080A9H41B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	1755 1519 1369 1300	1717 1478 1265 1161	1678 1436 1161 1021	1639 1394 1115 965	1600 1351 1068 909	1561 1309 1023 860	1522 1267 978 810	1481 1225 925 754	1439 1182 871 697
TUD1B100A9H31B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	1380 1283 1176 1029	1355 1258 1142 996	1330 1232 1108 962	1305 1204 1081 928	1280 1176 1054 894	1248 1144 1019 855	1216 1112 983 816	1191 1084 947 756	1165 1056 911 696
TUD1C100A9H51B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	2195 1998 1813 1630	2154 1959 1778 1590	2113 1919 1742 1550	2076 1883 1703 1511	2038 1847 1664 1471	1992 1814 1630 1434	1945 1781 1595 1396	1876 1744 1560 1361	1807 1706 1525 1325
TUD1D120A9H51B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	2119 1963 1751 1579	2091 1929 1712 1541	2062 1895 1673 1502	2029 1857 1638 1459	1996 1818 1602 1416	1959 1785 1566 1378	1921 1751 1529 1340	1887 1716 1490 1293	1852 1681 1451 1246
TUD1D140A9H51B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	2130 1935 1752 1576	2096 1896 1711 1533	2062 1857 1669 1490	2023 1824 1632 1452	1984 1790 1594 1413	1952 1750 1551 1375	1919 1709 1507 1336	1884 1673 1472 1295	1849 1636 1436 1254

① Central Furnace heating designs are certified by AGA and CSA.

② For U.S. applications, above input ratings (BTUH) are up to 2,000 feet, derate 4% per 1,000 feet for elevations above 2,000 feet above sea level.

For Canadian applications, above input ratings (BTUH) are up to 4,500 feet, derate 4% per 1,000 feet for elevations above 4,500 feet above sea level.

③ Based on U.S. government standard tests.

④ The above wiring specifications are in accordance with National Electrical Code; however, installations must comply with local codes.



## Performance Data

### TUD1-H CFM

MODEL	CFM VS. TEMPERATURE RISE																			
	400	500	600	700	800	900	1000	1100	1200	1300	1400	1500	1600	1700	1800	1900	2000	2100		
TUD1A040A9H21B		59	49	42	37	33	30													
TUD1B060A9H31B			63	56	49	44	40	37	34	32	30									
TUD1B080A9H31B						59	54	49	46	42	40	37	35	33	31					
TUD1C080A9H41B						59	54	49	46	42	40	37	35	33	31					
TUD1B100A9H31B						74	67	62	57	53	49	46	44	41						
TUD1C100A9H51B								62	57	53	49	46	44	41	39	37	35			
TUD1D120A9H51B											59	56	52	49	47	44	42			
TUD1D140A9H51B											69	65	61	58	55	52	49			

### TDD1-H CFM

MODEL	CFM VS. TEMPERATURE RISE																			
	400	500	600	700	800	900	1000	1100	1200	1300	1400	1500	1600	1700	1800	1900	2000	2100		
TDD1B060A9H31B					56	49	44	40	37	34	32	30	28	26						
TDD1B080A9H31B						66	59	54	49	46	42	40	37	35						
TDD1C100A9H51B								62	57	53	49	46	44	41	39	37	35			
TDD1D120A9H51B									68	63	59	56	52	49	47	44	42			



## Performance Data


### TDD1-H Airflow

FURNACE AIRFLOW (CFM) VS. STATIC PRESSURE (ins.w.g.)										
MODEL	SPEED TAP	0.1	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9
TDD1B060A9H31B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	1449 1303 1182 1012	1415 1270 1150 974	1381 1236 1117 935	1345 1202 1080 904	1309 1167 1042 872	1265 1133 1005 835	1220 1099 968 798	1143 1054 933 760	1066 1009 897 721
TDD1B080A9H31B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	1450 1302 1190 1033	1417 1269 1153 992	1393 1235 1115 951	1349 1200 1079 912	1314 1164 1042 873	1272 1127 1009 832	1229 1089 976 791	1147 1041 934 729	1064 992 891 666
TDD1C100A9H51B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	2170 1971 1766 1579	2126 1932 1720 1537	2082 1893 1674 1495	2045 1855 1633 1447	2007 1816 1591 1399	1964 1771 1547 1352	1920 1726 1502 1304	1884 1688 1456 1250	1848 1649 1409 1196
TDD1D120A9H51B	4 - HIGH - Black 3 - MED-HIGH - Blue 2 - MED-LOW - Yellow 1 - LOW - Red	2171 1976 1770 1575	2128 1934 1730 1531	2085 1891 1690 1487	2048 1856 1652 1446	2010 1820 1614 1404	1968 1781 1575 1363	1925 1741 1535 1321	1893 1704 1493 1277	1861 1666 1450 1233



# Electrical Data

## TUD1-H Wiring Diagram For Gas Furnaces



From Dwg. D342489 Rev. 6



# Electrical Data

## TUD1-H Schematic Diagram For Gas Furnaces




TABLE "A"				
SPEED TAPS FOR I.D. FAN MOTOR				
MODEL	HEAT "A"	PARK "B"	PARK "C"	COOL "D"
*UD1A040A9H2B**	RD/WH	BK/WH	YL/WH	BL/WH
*UD1B060A9H3B**	RD/WH	BL/WH	YL/WH	BK/WH
*UD1B080A9H3B**	YL/WH	BL/WH	RD/WH	BK/WH
*UD1C080A9H3B**	YL/WH	BL/WH	RD/WH	BK/WH
*UD1B100A9H3B**	BL/WH	YL/WH	RD/WH	BK/WH
*UD1C100A9H5B**	RD/WH	BL/WH	YL/WH	BK/WH
*UD1D120A9H5B**	BL/WH	YL/WH	RD/WH	BK/WH
*UD1D140A9H5B**	BL/WH	YL/WH	RD/WH	BK/WH

\* PREFIX MAY BE "A" OR "T"  
\*\* SUFFIX MAY BE "A" THROUGH "Z"  
RD/WH = LOW=1      BL/WH = MED.HIGH=3  
YL/WH = MED. LOW=2      BK/WH = HIGH=4

<b>WARNING</b>	
HAZARDOUS VOLTAGE: DISCONNECT ALL ELECTRICAL POWER INCLUDING REMOTE DISCONNECTS BEFORE SERVICING.	
FAILURE TO DISCONNECT POWER BEFORE SERVICING CAN CAUSE SEVERE PERSONAL INJURY OR DEATH.	
<b>CAUTION</b>	
USE COPPER CONDUCTORS ONLY! UNIT TERMINALS ARE NOT DESIGNED TO ACCEPT OTHER TYPES OF CONDUCTORS. FAILURE TO DO SO MAY CAUSE DAMAGE TO THE EQUIPMENT.	

**INTEGRATED FURNACE CONTROL**  
REPLACE WITH PART CNT04711 OR  
EQUIVALENT  
INPUT: 25 VAC, 60 Hz.  
XFRMR SEC. CURRENT: 450 MA.  
MV OUTPUT: 1.5 A @ 24 VAC  
IND. OUTPUT: 2.2 FLA, 3.5 LRA @ 120 VAC  
CIRC. BLOWER OUTPUT: 14.5 FLA,  
14.5 LRA @ 120 VAC  
HUMIDIFER & AIR CLEANER  
MAX. LOAD: 1.0 A @ 120 VAC  
IGNITER OUTPUT: 2.0 A @ 120 VAC

**DIAGNOSTIC CODES**

FLASHING SLOW: NORMAL - NO CALL FOR HEAT	5 FLASHES: FLAME SENSED WHEN NO FLAME
FLASHING FAST: NORMAL - CALL FOR HEAT	SHOULD BE PRESENT
CONTINUOUS ON: REPLACE IFC	6 FLASHES: 115 VAC POWER REVERSED
CONTINUOUS OFF: CHECK POWER	POLARITY OR POOR GROUNDING
2 FLASHES: EXTERNAL LOCKOUT (RETRIES OR RECYCLES EXCEEDED)	7 FLASHES: GAS VALVE CIRCUIT ERROR
3 FLASHES: PRESSURE SWITCH ERROR	8 FLASHES: LOW FLAME SENSE SIGNAL
4 FLASHES: OPEN LIMIT DEVICE	9 FLASHES: CHECK IGNITER

TCO THERMAL CUT OUT	LINE } FACTORY	BK BLACK
PS PRESSURE SWITCH	— 24 v WIRING	WH WHITE
FRS FLAME ROLLOUT SWITCH	- - - LINE } FIELD	YL YELLOW
FP FLAME SENSOR	- - - 24 v WIRING	OR ORANGE
CHASSIS GROUND	♦ INTERNAL THERMAL PROTECTION	BR BROWN
HSI HOT SURFACE IGNITER	L LINE	GR GREEN
CF CAPACITOR	N NEUTRAL	RD RED
DOOR SWITCH	GND GROUND	BL BLUE
	B/C COMMON	
	MV MAIN GAS VALVE	
	TNS TRANSFORMER	
	HLO HIGH LIMIT OUTPUT	
	HLI HIGH LIMIT INPUT	

WIRE COLOR  
BK/L NUMBER ID (IF ANY)


### NOTES:

1. IF ANY OF THE ORIGINAL WIRING AS SUPPLIED WITH THIS FURNACE MUST BE REPLACED, IT MUST BE WITH WIRE HAVING A TEMPERATURE RATING OF AT LEAST 105°C.
2. THERMOSTAT HEAT ANTICIPATOR SETTING: .38 AMPS
3. FOR PROPER OPERATION OF COOLING SPEED, "Y" TERMINAL MUST BE CONNECTED TO THE ROOM THERMOSTAT.
4. THESE TERMINALS PROVIDE 120V POWER CONNECTIONS FOR ELECTRONIC AIR CLEANER (EAC) AND HUMIDIFIER (HUM). MAX. LOAD: 1.0 AMPS EACH.
5. WHEN TWINNING TWO FURNACES, BOTH UNITS MUST BE CONNECTED TO THE SAME 115 VAC PHASE. CONNECT THE TWO UNITS 'TWIN' TERMINALS WITH 14 TO 22 AWG. WIRE.
6. FOR MODELS USING 3/4 HP & 1 HP INDOOR FAN MOTOR, USE DETAIL A & TABLE A.



# Electrical Data

TDD1-H Wiring Diagram For Gas Furnaces



From Dwg. D342490 Rev. 4



# Electrical Data

## TDD1-H Schematic Diagram For Gas Furnaces




TABLE "A"				
MODEL	HEAT "A"	PARK "B"	PARK "C"	BLOWER HP
•DDIB060A9H31B**	RD/WH	BL/WH	YL/WH	1/2
•DDIB080A9H31B**	RD/WH	BL/WH	YL/WH	1/2
•DDIC100A9H51B**	YL/WH	BL/WH	RD/WH	1
•DDID120A9H51B**	YL/WH	BL/WH	RD/WH	1

\* PREFIX MAY BE "A" OR "T"  
\*\* SUFFIX MAY BE "A" THROUGH "Z"  
RD/WH = LOW=1      BL/WH = MED.HIGH=3  
YL/WH = MED.\_LOW=2      BK/WH = HIGH=4

**WARNING**  
HAZARDOUS VOLTAGE:  
DISCONNECT ALL ELECTRICAL POWER  
INCLUDING REMOTE DISCONNECTS BEFORE  
SERVICING.  
FAILURE TO DISCONNECT POWER BEFORE  
SERVICING CAN CAUSE SEVERE PERSONAL  
INJURY OR DEATH.

**CAUTION**  
USE COPPER CONDUCTORS ONLY!  
UNIT TERMINALS ARE NOT DESIGNED TO  
ACCEPT OTHER TYPES OF CONDUCTORS.  
FAILURE TO DO SO MAY CAUSE DAMAGE  
TO THE EQUIPMENT.

**INTEGRATED FURNACE CONTROL**  
REPLACE WITH PART CNT047II OR  
EQUIVALENT

FLASHING SLOW: NORMAL - NO CALL FOR HEAT	INPUT: 25 VAC, 60 Hz
FLASHING FAST: NORMAL - CALL FOR HEAT	XFMER SEC. CURRENT: 450 MA.
CONTINUOUS ON: REPLACE IFC	MV OUTPUT: 1.5 A @ 24 VAC
CONTINUOUS OFF: CHECK POWER	IND OUTPUT: 2.2 FLA, 3.5 LRA @ 120 VAC
2 FLASHES: EXTERNAL LOCKOUT (RETRIES	CIRC. BLOWER OUTPUT: 14.5 FLA,
OR RECYCLES EXCEEDED)	14.5 LRA @ 120 VAC
3 FLASHES: PRESSURE SWITCH ERROR	HUMIDIFIER & AIR CLEANER
4 FLASHES: OPEN LIMIT DEVICE	MAX. LOAD: 1.0 A @ 120 VAC
5 FLASHES: FLAME SENSED WHEN NO FLAME	IGNITER OUTPUT: 2.0 A @ 120 VAC
SHOULD BE PRESENT	
6 FLASHES: 115 VAC POWER REVERSED	
POLARITY OR GROUND PROUDNG	
7 FLASHES: GAS VALVE CIRCUIT ERROR	
8 FLASHES: LOW FLAME SENSE SIGNAL	
9 FLASHES: CHECK IGNITER	

TCO THERMAL CUT OUT	LINE } FACTORY WIRING	BK BLACK	GR GREEN
PS PRESSURE SWITCH	— — LINE } FIELD WIRING	WH WHITE	BR BROWN
FRS FLAME ROLLOUT SWITCH	- - - 24 V } FIELD WIRING	YL YELLOW	RD RED
FP FLAME SENSOR		OR ORANGE	BL BLUE
CHASSIS GROUND			
HSI HOT SURFACE IGNITER			
DOOR SWITCH			

\*\* INTERNAL THERMAL PROTECTION

BK/1 L NUMBER ID (IF ANY)

L LINE	24 VAC (HOT)
N NEUTRAL	TR 24 VAC (COMMON)
GND GROUND	MV MAIN GAS VALVE
B/C COMMON	TNS TRANSFORMER
HLO HIGH LIMIT OUTPUT	
HLI HIGH LIMIT INPUT	


### NOTES:

1. IF ANY OF THE ORIGINAL WIRING AS SUPPLIED WITH THIS FURNACE MUST BE REPLACED, IT MUST BE WITH WIRE HAVING A TEMPERATURE RATING OF AT LEAST 105°C.
2. THERMOSTAT HEAT ANTICIPATOR SETTING: .38 AMPS
3. FOR PROPER OPERATION OF COOLING SPEED, "Y" TERMINAL MUST BE CONNECTED TO THE ROOM THERMOSTAT.
4. THESE TERMINALS PROVIDE 120V POWER CONNECTIONS FOR ELECTRONIC AIR CLEANER (EAC) AND HUMIDIFIER (HUM). MAX. LOAD: 1.0 AMPS EACH.
5. WHEN TWINNING TWO FURNACES, BOTH UNITS MUST BE CONNECTED TO THE SAME 115 VAC PHASE. CONNECT THE TWO UNITS 'TWIN' TERMINALS WITH 14 TO 22 AWG. WIRE.
6. FOR MODELS USING 3/4 HP & 1 HP INDOOR FAN MOTOR, USE DETAIL A & TABLE A.




# Field Wiring

## FIELD WIRING DIAGRAM FOR 1 STAGE FURNACE 1 STAGE HEATING USING A 1 STAGE HEATING THERMOSTAT NO COOLING




### NOTES:

1. BE SURE POWER AGREES WITH EQUIPMENT NAMEPLATE(S).
2. LOW VOLTAGE (24V. WIRING) TO BE NO. 18 A.W.G. MIN.
3. GROUNDING OF EQUIPMENT MUST COMPLY WITH LOCAL CODES.
4. SET THERMOSTAT HEAT ANTICIPATOR PER UNIT WIRING DIAGRAM.
5. THESE LEADS PROVIDE 115 V. POWER FOR CONNECTION OF ELECTRONIC AIR CLEANER AND HUMIDIFIER MAX. LOAD 1.0 AMPS EACH.
6. THIS CONNECTION IS ONLY USED FOR THERMOSTATS REQUIRING CONNECTION TO THE 24 V. POWER SUPPLY. (COMMON)
7. SEE TWINNING CONNECTION DIAGRAMS FOR PROPER CONNECTIONS WHEN USING THIS FEATURE.




From Dwg. B341437 Rev. 1

## FIELD WIRING DIAGRAM FOR 1 STAGE FURNACE 1 STAGE HEATING, 1 STAGE COOLING USING A 1 STAGE HEATING, 1 STAGE COOLING THERMOSTAT (OUTDOOR SECTION WITHOUT TRANSFORMER)



### NOTES:



1. BE SURE POWER AGREES WITH EQUIPMENT NAMEPLATE(S)
2. LOW VOLTAGE(24 V. WIRING) TO BE NO. 18 A.W.G. MIN.
3. GROUNDING OF EQUIPMENT MUST COMPLY WITH LOCAL CODES.
4. SET THERMOSTAT HEAT ANTICIPATOR PER UNIT WIRING DIAGRAM.
5. THESE LEADS PROVIDE 115 V. POWER FOR CONNECTION OF ELECTRONIC AIR CLEANER AND HUMIDIFIER MAX. LOAD 1.0 AMPS EACH.
6. THE "Y" TERMINAL FROM THE THERMOSTAT MUST BE WIRED TO THE "Y" TERMINAL OF THE FURNACE CONTROL FOR PROPER BLOWER OPERATION DURING COOLING.
7. IGNITION CONTROL IS POLARITY SENSITIVE. HOT LEG OF 120 VOLT POWER SUPPLY MUST BE CONNECTED TO THE BLACK LINE POWER LEAD AS INDICATED ON THE WIRING DIAGRAM OR IGNITION LOCKOUT WILL OCCUR.
8. THIS CONNECTION IS ONLY USED FOR THERMOSTATS REQUIRING CONNECTION TO THE 24 V. POWER SUPPLY. (COMMON)



From Dwg. B340388 Rev. 2




# Twining Field Wiring





# Dimensions

## TUD1-H OUTLINE DRAWING (ALL DIMENSIONS ARE IN INCHES)



### MINIMUM CLEARANCE TO COMBUSTIBLE MATERIALS

	FRONT	BACK	TOP	IN.
VENT CLEARANCE	0	0	0	3 (SEE NOTE 1)
LEFT SIDE FLUE	*0	0	0	1 (SEE NOTE 1)
RIGHT SIDE FLUE	*0	0	0	1 (SEE NOTE 1)
HORIZONTAL CLOSET (SEE NOTE 2)	*2	3	0	0 (IN.)
TOP FLUE	*6	3	0	0 (IN.)
FRONT FLUE	*6	0	0	1 (IN.)
HORIZONTAL VENT (SEE NOTE 2)	18	0	0	1 (IN.)
TOP FLUE	11	0	0	1 (IN.)
FRONT FLUE	16	0	0	1 (IN.)

NOTES:  
 1. MAY BE USED WHEN TYPE B-1 VENT IS USED.  
 2. FOR 14-1/2" CABINETS, 3" WHEN SINGLE WALL VENT PIPE IS USED.  
 WHEN 14-1/2" CABINETS (ALL UD040C, UD040R, UD060C, AND UD060R36) ARE INSTALLED IN A HORIZONTAL POSITION AND A SINGLE WALL VENT TYPE IS USED, A 6 INCH CLEARANCE MUST BE SUPPLIED BETWEEN THE VENT PIPE AND COMBUSTIBLE FLOORING.

MINIMUM CLEARANCE TO FRONT ON  
 1) UD1A040A9H21 AND UD1A040H51 IS 6 INCHES.  
 2) MAY BE INSTALLED ON COMBUSTIBLE FLOOR WHEN TYPE B-1 VENT IS USED.


NOTES:

1. MINIMUM CLEARANCE TO FRONT ON  
 1) UD1B060A9H31 AND UD1B080A9H31 IS 6 INCHES.  
 2) MAY BE INSTALLED ON COMBUSTIBLE FLOOR WHEN TYPE B-1 VENT IS USED.

NOTES:

1. MINIMUM CLEARANCE TO FRONT ON  
 1) UD1B100A9H31 IS 6 INCHES.  
 2) MAY BE INSTALLED ON COMBUSTIBLE FLOOR WHEN TYPE B-1 VENT IS USED.

MODEL	DIM "A"	DIM "B"	DIM "C"	DIM "D"
TUD1A040A9H21B	14-1/2"	9-5/8"	13-1/4"	13"
TUD1B060A9H31B	17-1/2"	9-5/8"	16-1/4"	16"
TUD1B080A9H31B				
TUD1B100A9H31B				
TUD1C080A9H41B	21"	13-1/16"	19-3/4"	19-1/2"
TUD1C100A9H51B				
TUD1D120A9H51B	24-1/2"	15-5/16"	23-1/4"	23"
TUD1D140A9H51B				




From Dwg. 21C341699 Rev. 1



# Dimensions

## TDD1-H OUTLINE DRAWING (ALL DIMENSIONS ARE IN INCHES)



**MINIMUM CLEARANCE TO COMBUSTIBLE MATERIALS**

**CABINET**

FRONT: 6 IN. W/ANGLE WALL VENT - 0 IN. WHITE B-1 VENT FLUE 6 IN. W/ANGLE WALL VENT - 1 IN. WHITE B-1 VENT FROM 6 IN. HOLE ON BACK 14.5" DEBRIDES. 0 IN. TO LEFT SIDE 0 IN. FOR REMAINING CABINET SIZES (17.5" - 21.0") 24.5".

TOP: 3 IN. W/ANGLE WALL VENT - 2 IN. WHITE B-1 VENT FLUE 6 IN. W/ANGLE WALL VENT - 1 IN. WHITE B-1 VENT FROM TOP ONLY FOR 14.5" CABINETS. 2 IN. FOR REMAINING CABINET SIZES (17.5" - 21.0") 24.5".

**HORIZONTAL CLOSET FLUE DISCHARGE RECD**

TOP: 2 IN. W/ANGLE WALL VENT FLUE 6 IN. W/ANGLE WALL VENT - 1 IN. WHITE B-1 VENT FLUE 6 IN. W/ANGLE WALL VENT - 1 IN. WHITE B-1 VENT FOR INSTALLATION ON COMBUSTIBLE FLOORING ONLY WHEN B-1 VENT CONCTOR IS USED.

TOP: 3 IN. W/ANGLE WALL VENT FLUE 6 IN. W/ANGLE WALL VENT - 1 IN. WHITE B-1 VENT FLUE 6 IN. W/ANGLE WALL VENT - 1 IN. WHITE B-1 VENT FROM TOP ONLY FOR 14.5" CABINETS. 1 IN. FOR REMAINING CABINET SIZES (17.5" - 21.0") 24.5".

**HORIZONTAL ALCOVE FLUE DISCHARGE RECD**

TOP: 1 IN. W/ANGLE WALL VENT FLUE 6 IN. W/ANGLE WALL VENT - 1 IN. WHITE B-1 VENT FLUE 6 IN. W/ANGLE WALL VENT - 1 IN. WHITE B-1 VENT FRONT 18 IN. SWINGBACK 0 IN. STOSS 0 IN.

MODEL	DIM "A"	DIM "B"	DIM "C"	DIM "D"
TDD1B060A9H31B	17-1/2"	9-5/8"	16-1/4"	16"
TDD1B080A9H31B	21"	13-1/16"	19-3/4"	19-1/2"
TDD1C100A9H51B	24-1/2"	15-5/16"	23-1/4"	23"
TDD1D120A9H51B				



Trane  
6200 Troup Highway  
Tyler, TX 75707  
[www.trane.com](http://www.trane.com)

06/10

---

---

---

---

---

**Trane** has a policy of continuous product and product data improvement **and** it reserves the right to change design and specifications without notice.