

D U C T M A T E



Neoprene Gasket Tape



Rubber Based Sealing Tape

Ideal for Round and Flat-Oval Duct Connections

- Pressure sensitive adhesive backing
- Synthetic closed cell tape
- Simple and easy to install



DUCTMATE®

Industries, Inc.

Neoprene Gasket Tape

**Rubber Based
Sealing Tape**

DESCRIPTION

Neoprene Gasket Tape is a synthetic, closed cell, rubber-based sealing tape.

BASIC USE

Excellent for use between duct flanges to produce an airtight seal.

SPECIAL CHARACTERISTIC

Excellent for use when connecting ducts which must be disassembled periodically for cleaning purposes.
Recommended for use with Ductmate Spiralmate.

PACKAGING INFORMATION

50 ft. rolls/750 ft. per carton
15 lbs. per carton

TECHNICAL INFORMATION

COLOR:	Black
DENSITY:	8-12 (p.c.f.) average
WATER ABSORPTION BY WEIGHT (MAX.):	5%
COMPRESSION DEFLECTION:	2-5 psi
TEMPERATURE RANGE (°F):	
Low (Flex without cracking)	-40° F
High continuous	150° F
High intermittent	200° F
UL 94 HF-1:	Passes

LIMITED PRODUCT WARRANTY

Manufacturer is not liable for consequential, incidental or special damages. There are no statutory or implied warranties including the warranties of fitness for a particular purpose and merchantability. There are no warranties other than as set forth below and factory neither assumes nor authorizes any person to assume any liability or other obligation in connection with Neoprene Gasket Tape.

Neoprene Gasket Tape is warranted to be free from any and all defects in material and workmanship only at the time of shipment from our factory. If material is shown to be defective at the time of shipment from our factory, manufacturer will at its sole option, replace or issue credit for the original purchase price.

To determine the suitability of Neoprene Gasket Tape for each specific purpose the user must conduct his own test. Manufacturer does not guarantee the results from the use of Neoprene Gasket Tape because of the extreme differences in surface texture and porosity of available materials as well as the possibility of structural movement or externally caused damages.



DUCTMATE®
Industries, Inc.

E. MONONGAHELA, PA
R.D. #3, Box 113 (Route 136)
E. Monongahela, PA 15063-9709
800-245-3188
412-258-0500
FAX: 412-258-5494

LODI, CA
810 S. Cluff Avenue
Lodi, CA 95240-3141
800-344-3270
209-333-4680
FAX: 209-333-4678



Distributed By: