
TAG

Dimensional Data (inches and [mm]) are Subject to Manufacturing Tolerances and Change Without Notice



ENGINEERING SPECIFICATION: FD2321

Adjustable finished area floor drain with square top recomended for finished floor areas where a membrane is generally used. This drain is designed for foot traffic and light cart applications. Complete with cast iron body, clamping collar and adjustable nickel bronze strainer assembly. 1/2" [13mm] trap primer connection provided with plug.


OPTIONS (Check/specify appropriate options)

SUFFIXES

CP	Chrome Plated Strainer
PB	Polished Brass Strainer
R6	6" [152mm] Dia. Nickel Head Assembly
R7	7" [178mm] Dia. Nickel Head Assembly
R8	8" [203mm] Dia. Nickel Head Assembly
-VP	Vandal Proof

Product	Dimensions in Inches [mm]		
No.	Connection 'A'	'D'	
FD2321-NH2	2 [51] NO-HUB	2-1/2 [64]	
FD2321-NH3	3 [76] NO-HUB	2-1/2 [64]	
FD2321-NH4	4 [102] NO-HUB	2-1/2 [64]	
FD2321-PO2	2[51] PUSH-ON	3-3/8 [86]	
FD2321-PO3	3 [76] PUSH-ON	4-7/16 [113]	
FD2321-IP2	2 [51] IPS	1-29/32 [48]	
FD2321-IP3	3 [76] IPS	2-5/32 [55]	

TYPICAL INSTALLATION



^{*} Regularly furnished unless otherwise specified.

Zurn Industries, LLC | Specification Drainage Operation
1801 Pittsburgh Avenue, Erie, PA U.S.A. 16502 · Ph. 855-663-9876, Fax 814-454-7929
In Canada | Zurn Industries Limited
3544 Nashua Drive, Mississauga, Ontario L4V 1L2 · Ph. 905-405-8272, Fax 905-405-1292

Rev.

Date: 07/30/15 C.N. No. 132954

Prod. | Dwg. No. FD2321