


## Mirafi<sup>®</sup> HP370



Mirafi<sup>®</sup> HP370 geotextile is composed of high-tenacity monofilament polypropylene yarns, which are woven into a network such that the yarns retain their relative position. Mirafi<sup>®</sup> HP370 geotextile is inert to biological degradation and resistant to naturally encountered chemicals, alkalis, and acids.

TenCate Geosynthetics Americas is accredited by Geosynthetic Accreditation Institute – Laboratory Accreditation Program (<u>GAI-LAP</u>).

Mechanical Properties	echanical Properties Test Method Unit	Unit	Minimum Average Roll Value	
			MD	CD
Tensile Strength (at ultimate)	ASTM D4595	lbs/ft (kN/m)	3600 (52.5)	3240 (47.3)
Tensile Strength (at 5% strain)	ASTM D4595	lbs/ft (kN/m)	1500 (21.9)	1560 (22.8)
			Minimum Roll Value	
Flow Rate	ASTM D4491	gal/min/ft <sup>2</sup> (l/min/m <sup>2</sup> )	60 (2444)	
Permittivity	ASTM D4491	sec <sup>-1</sup>	0.8	
			Maximum O	pening Size
Apparent Opening Size (AOS)	ASTM D4751	U.S. Sieve (mm)	30 (0.600)	
			Minimum Test Value	
UV Resistance (at 500 hours)	ASTM D4355	% strength retained	80	

Physical Properties	Unit	Roll Size	
Roll Dimensions (width x length)	ft (m)	15 x 300 (4.5 x 91)	
Roll Area	yd² (m²)	500 (418)	

**Disclaimer:** TenCate assumes no liability for the accuracy or completeness of this information or for the ultimate use by the purchaser. TenCate disclaims any and all express, implied, or statutory standards, warranties or guarantees, including without limitation any implied warranty as to merchantability or fitness for a particular purpose or arising from a course of dealing or usage of trade as to any equipment, materials, or information furnished herewith. This document should not be construed as engineering advice.

Mirafi<sup>®</sup> is a registered trademark of Nicolon Corporation.

Copyright © 2015 Nicolon Corporation. All Rights Reserved.

365 South Holland Drive Pendergrass, GA 30567

Tel 706 693 2226 Tel 888 795 0808 Fax 706 693 4400 www.tencate.com



FGS000008 ETQR42

GAI-LAP-25-97