

The Next **Necessity**^{*}



Instant Hot Water Dispensers

Model F-601R **Replacement Filter Plus**

Submittal Sheet

- Includes 2 replacement filters for use with InSinkErator water filtration system
- · Reduces sediment, chlorine taste and odor, Plus cysts, lead, mercury, asbestos, benzene, atrazine, 2,4-D and other chemicals for healthier, safer water
- Sanitary, guick-change filter cartridge makes replacement easy. A simple twist is all it takes!
- 6 month recommended filter cartridge replacement

Specifications

Fi	Iter Capacity	500 gallons				
	emperature ange	Incoming cold water supply line can be from 33°F to 100°F (1°C to 38°C). Connect to cold water supply line only.				
Pr	ressure	20-125 psi				
FI	ow Rate	1.0 gpm				
Sł	nipping Weight	Approximately 2.5 lbs.				
Di	mensions	10-2/3"H installed, 3-1/4"W				

F-601R Chemical & Mechanical Reduction Filter Specifications: This cartridge provides mechanical and chemical reduction of dirt/rust, chlorine/taste/odor, particulates, cysts, asbestos, lead, mercury, lindane, benzene, carbofuran, p-dichlorobenzene, 2,4-D and Atrazine.

This system has been tested according to NSF/ANSI Standards 42 and 53 for the reduction of the substances listed below. The concentration of the indicated substances in water entering the system was reduced to a concentration less than or equal to the permissible limit for water leaving the system as specified in NSF/ANSI Standards 42 and 53.



Tested and Certified by NSF International against NSF/ANSI Standard 42 and 53 for use in the F-201 system for the reduction of Chlorine taste and odor, Nominal Particulate Class I, cysts, asbestos, lead, mercury, lindane, benzene, carbofuran, p-dichlorobenzene, 2,4-D and Atrazine. REPLACEMENT ELEMENT

Pressure: 20 -125 psi Temperature: 33-100°F Flow rate: 1.0 gpm Capacity: 500 gallons

Filter Capacity: 500 gallons, depending on local water conditions. Note that while the testing was performed under standard laboratory conditions, actual performance may vary. For cold water use only. Systems must be installed and operated in accordance with the Manufacturer's recommended procedures and guidelines. See warranty card for warranty. For service and parts, contact your local dealer or InSinkErator® directly at 1-800-558-5700.


Standard 42: Aesthetic Effects										
Substance	USEPA MCL	Influent Challenge concentration	Effluent Average	Effluent		% Reduction		Min. Required	NSF	
Substance		(mg/L)		Average	Maximum	Average	Maximum	Reduction	Report	
Chlorine Taste & Odor	~	2.0mg/L +10%	2.12 mg/L	0.05 mg/L	0.05 mg/L	97.66%	97.62%	>50%	J-00029741	
Nominal Particulate*	~	at least 10,000 particales/mL	10,566,667 #/ml	171,833 #/ml	360,000 #/ml	97.88%	95.10%	>85%	J-00029739	

	Standard 53: Health Effects									
	Substance USEPA MCL		Influent Challenge concentration	Influent	Effluent		% Reduction		Min. Required	NSF
	Substance	USEFANICE	(mg/L)	Average	Average	Maximum	Average	Maximum	Reduction	Report
	Cysts	99.95% reduction	Minimum 50,000 #L	127,000 #L	1 #L	1 #L	>99.99%	>99.99%	>99.95%	J-00031000
	Asbestos	99% reduction	10^7 to 10^8 fibers/L; fibers greater than 10 μm in length	140 MF/L	<1 MF/L	<1 MF/L	99.81%	99.72%	>99%	J-00029743
	Lead @ pH 6.5	0.015 mg/L	0.15 +10%	0.158 mg/L	<0.001 mg/L	<0.001 mg/L	99.37%	99.37%	0.010 mg/L	J-00031399
	Lead @ pH 8.5	0.015 mg/L	0.15 +10%	0.154 mg/L	<0.001 mg/L	<0.001 mg/L	99.34%	99.33%	0.010 mg/L	J-00029746
* Tested using a flow rate of 1.00 gpm;	Mercury @ pH 6.5	0.002 mg/L	0.006 ±10%	0.006 mg/L	0.000 mg/L	0.000 mg/L	94.35%	89.26%	0.002 mg/L	J-00029747
pressure of 60 psi; pH of 7.5 ± 0.5; temp. of 68° ± 5°F (20° ± 3°C)	Mercury @ pH 8.5	0.002 mg/L	0.006 ±10%	0.006 mg/L	0.000 mg/L	0.000 mg/L	85.27%	67.15%	0.002 mg/L	J-00029748
** Measurement in Particles/ml. Particles	Lindane	0.0002 mg/L	0.002 +10%	0.002 mg/L	<0.00002 mg/L	<0.00002 mg/L	99.03%	98.98%	0.0002 mg/L	J-00029753
 Base of the use of Cryptosporium parvum cyst. Do NOT use with water that is 	Benzene	0.005 mg/L	0.015 ±10%	0.014 mg/L	<0.005 mg/L	0.005 mg/L	96.32%	96.05%	0.005 mg/L	J-00029751
microbiologically unsafe or of unknown quality without adequate disinfection	Carbofuran	0.04 mg/L	0.08 ±10%	0.080 mg/L	1.063 mg/L	0.002 mg/L	98.74%	97.33%	0.04 mg/L	J-00029750
before or after the system. Systems	p-dichlorobenzene	0.075 mg/L	0.225 ±10%	0.240 mg/L	0.525 mg/L	0.800 mg/L	99.76%	99.64%	0.075 mg/L	J-00029749
certified for cyst reduction may be used on disinfected waters that may contain	2,4-D	0.07 mg/L	0.210 ±10%	0.190 mg/L	0.012 mg/L	0.071 mg/L	93.84%	62.63%	0.07 mg/L	J-00029754
filterable cysts. EPA Establishment #: 070595-CT-001	Atrazine	0.003 mg/L	0.009 ±10%	0.009 mg/L	0.0005 mg/L	0.0005 mg/L	94.77%	94.48%	0.003 mg/L	J-00029752
	-									

NSF is a trademark of NSF International.

Application guidelines/Water Supply Parameters for NSF Testing: Service flow of 1.0 gpm, community or private well water supply, water pressure of 20-125 psi, water temperature of 33°F-100°F. Except as noted, all testing performed at pH = 7.5 ± 0.5, Flow: 1.0 gpm, Pressure: 60 psi, Temp: 20°± 3°C.

Job Specifications





Canada 1-800-561-1700 www.insinkerator.ca



Commercial & Residential Solutions

The Emerson logo is a trademark and a service mark of Emerson Electric Co. InSinkErator may make improvements and/or changes in the specifications at any time, in its sole discretion, without notice or obligation and further reserves the right to change or discontinue models.

> ©2012 InSinkErator, a business unit of Emerson Electric Co. All Rights Reserved.

Printed in USA