



SUBMITTAL SHEET

System 3100M Uninsulated Flexible Connector

CORE TYPE	2 Ply, Polyester – Metalized Polyester	
TEMPERATURE RANGE	-20° F to 250° F.	
SIZES IN DIAMETER	2 / 3 / 4 / 5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 14 / 16 / 18 / 20	
LENGTH IN FEET	Standard 25ft; Custom 4ft -30ft	
INSIDE BEND RADIUS	2 / 3 / 4 / 5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 14 / 16 / 18 / 20	
STEEL WIRE	Zinc coated spring steel wire helix	
RATED VELOCITY	4000 fpm.	
MAX RATED PRESSURE	POSITIVE	6" W.C. (2" – 10" Dia.) 4" W.C. (12"–20" Dia.)
	NEGATIVE	½" W.C. (2" – 20" Dia.)



JOB _____	
LOCATION _____	JOB NO. _____
ENGINEER _____	JOB NO. _____
CONTRACTOR _____	REPRESENTATIVE _____
Certified Correct	
BY _____	BY _____
TITLE _____	TITLE _____
DATE _____	DATE _____

Insulation Solution

Flexible Duct System

Metal Building Insulation

(800) 837 - ANCO

2500 17th Street, Elkhart, Indiana 46517

www.AncoProductsInc.com